

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 3

Revision: 09.10.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name: SONAX Rubber Protectant

Article number: 340200, 340400

1.2 Relevant identified uses of the substance or mixture and uses advised against

Sector of Use

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

Product category PC35 Washing and cleaning products (including solvent based products)

Application of the substance / the mixture Car care product

1.3 Details of the supplier of the safety data sheet

Manufacturer/Supplier:

SONAX GmbH

Münchener Straße 75

D-86633 Neuburg (Donau)

Tel.: ++49 (0)8431/53-0

Further information obtainable from:

Product safety

E-mail: erp@sonax.de

Phone: + +49 (0) 8431 53 217

1.4 Emergency telephone number: Emergency Phone Munich Tel.: +49 (0)89 19240

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Flam. Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

STOT SE 3 H336 May cause drowsiness or dizziness.

Aquatic Chronic 3 H412 Harmful to aquatic life with long lasting effects.

Classification according to Directive 67/548/EEC or Directive 1999/45/EC

F+; Extremely flammable

R12: Extremely flammable.

R52/53-66-67: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Repeated exposure may cause skin dryness or cracking. Vapours may cause drowsiness and dizziness.

Information concerning particular hazards for human and environment:

Warning! Pressurised container.

Contact with skin and inhalation of aerosols/ vapours of the preparation should be avoided.

2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

Hazard pictograms



GHS02 GHS07

Signal word Danger

Hazard-determining components of labelling:

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics

Hazard statements

H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

H336 May cause drowsiness or dizziness.

H412 Harmful to aquatic life with long lasting effects.

Precautionary statements

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 3

Revision: 09.10.2014

Trade name: SONAX Rubber Protectant

(Contd. of page 1)

- P251 Do not pierce or burn, even after use.
 P211 Do not spray on an open flame or other ignition source.
 P261 Avoid breathing spray.
 P271 Use only outdoors or in a well-ventilated area.
 P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
 P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

2.3 Other hazards**Results of PBT and vPvB assessment****PBT:** Not applicable.**vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

3.2 Mixtures**Description:** Formulation consisting of pressurised gas and mixture of solvents with silicones.**Dangerous components:**

EC number: 927-241-2 Reg.nr.: 01-2119471843-32-XXXX	Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics Xn R65 R10-52/53-66-67 Flam. Liq. 3, H226; Asp. Tox. 1, H304; STOT SE 3, H336; Aquatic Chronic 3, H412	75-100%
CAS: 124-38-9 EINECS: 204-696-9	carbon dioxide Press. Gas R, H281	< 5%
CAS: 123-86-4 EINECS: 204-658-1 Reg.nr.: 01-2119485493-29-xxxx	n-butyl acetate R10-66-67 Flam. Liq. 3, H226; STOT SE 3, H336	< 5%

Regulation (EC) No 648/2004 on detergents / Labelling for contents

aliphatic hydrocarbons	≥ 30%
------------------------	-------

Additional information:

Any entry in the EC-column that begins with the number "9" is a Provisional List Number provided by ECHA pending publication of the official EC Inventory Number for the substance. See Section 15 for additional CAS number information for the substance.

For the wording of the listed risk phrases refer to section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures**General information:**

Take affected persons out of danger area and lay down.

Remove soiled clothing

After inhalation:

Supply fresh air.

In the event of irritation of the respiratory tract, dizziness, nausea or unconsciousness, call medical assistance immediately.

After skin contact:

Generally the product does not irritate the skin.

Wash the areas of skin affected with water and a mild detergent.

After eye contact:

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

After swallowing: Do not induce vomiting; call for medical help immediately.

4.2 Most important symptoms and effects, both acute and delayed

Headache

Disziness

Nausea

Drowsiness

Reddening, drying and crack formation of the skin

(Contd. on page 3)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 3

Revision: 09.10.2014

Trade name: SONAX Rubber Protectant

(Contd. of page 2)

4.3 Indication of any immediate medical attention and special treatment needed

Treatment in accordance with the doctor's assessment of the patient's condition. Symptomatic treatment.

SECTION 5: Firefighting measures**5.1 Extinguishing media****Suitable extinguishing agents:**

Foam

Carbon dioxide

Fire-extinguishing powder

Water haze

For safety reasons unsuitable extinguishing agents: Water with full jet**5.2 Special hazards arising from the substance or mixture**

Can form explosive gas-air mixtures.

In case of fire, the following can be released:

Carbon monoxide (CO)

Sulphur dioxide (SO₂)**5.3 Advice for firefighters****Protective equipment:**

Do not inhale explosion gases or combustion gases.

Wear self-contained respiratory protective device.

Wear fully protective suit.

Additional information

Cool endangered receptacles with water spray.

Collect contaminated fire fighting water separately. It must not enter the sewage system.

SECTION 6: Accidental release measures**6.1 Personal precautions, protective equipment and emergency procedures**

Wear protective equipment. Keep unprotected persons away.

Keep away from ignition sources.

Ensure adequate ventilation

6.2 Environmental precautions:

Do not allow to enter sewers/ surface or ground water.

Do not allow to penetrate the ground/soil.

Inform respective authorities in case of seepage into water course or sewage system.

6.3 Methods and material for containment and cleaning up:

Ensure adequate ventilation.

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Dispose contaminated material as waste according to item 13.

6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage**7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.**Information about fire - and explosion protection:**

Keep ignition sources away - Do not smoke.

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use.

Do not spray onto a naked flame or any incandescent material.

Protect against electrostatic charges.

Highly volatile, flammable constituents are released during processing.

7.2 Conditions for safe storage, including any incompatibilities**Storage:****Requirements to be met by storerooms and receptacles:**

Provide solvent resistant, sealed floor.

Observe official regulations on storing packagings with pressurised containers.

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 3

Revision: 09.10.2014

Trade name: SONAX Rubber Protectant

(Contd. of page 3)

Information about storage in one common storage facility: Store away from foodstuffs.**Further information about storage conditions:**

Protect from heat and direct sunlight.

Store receptacle in a well ventilated area.

Store in a cool place. Heat will increase pressure and may lead to the receptacle bursting.

Recommended storage temperature: 20 °C.

7.3 Specific end use(s) No further relevant information available.**SECTION 8: Exposure controls/personal protection****8.1 Control parameters****Ingredients with limit values that require monitoring at the workplace:****124-38-9 carbon dioxide**

WEL (Great Britain)	Short-term value: 27400 mg/m ³ , 15000 ppm
	Long-term value: 9150 mg/m ³ , 5000 ppm

IOELV (EU)	Long-term value: 9000 mg/m ³ , 5000 ppm
------------	--

123-86-4 n-butyl acetate

WEL (Great Britain)	Short-term value: 966 mg/m ³ , 200 ppm
	Long-term value: 724 mg/m ³ , 150 ppm

DNELs**Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics**

Oral	DNEL	300 mg/kg bw/day (consumer) (ChronicExposure, SystemicEffects)
Dermal	DNEL	300 mg/kg bw/day (consumer) (ChronicExposure, SystemicEffects)
		300 mg/kg bw/day (worker) (ChronicExposure, SystemicEffects)
Inhalative	DNEL	900 mg/m ³ (consumer) (ChronicExposure, SystemicEffects)
		1500 mg/m ³ (worker) (ChronicExposure, SystemicEffects)

Additional information: The lists valid during the making were used as basis.**8.2 Exposure controls****Suitable technical control devices**

Ensure good ventilation. This can be achieved by localised extraction or general ventilation. If this is not sufficient to keep the concentration below the occupational exposure limit, suitable breathing protection is to be worn.

Personal protective equipment:**General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.

Wash hands before breaks and at the end of work.

Keep away from foodstuffs, beverages and feed.

Respiratory protection:

If the occupational exposure limit is exceeded:

The following breathing protection is recommended:

Respiratory filter for organic gases and vapours (Type A)

Identification colour: Brown

[DIN EN 14387]

Protection of hands:

Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Material of gloves

Nitrile rubber, NBR

Recommended thickness of the material: ≥ 0.4 mm

[EN 374]

Penetration time of glove material Value for the permeation: Level 5 (>240min - <480min)**Eye protection:**

Safety glasses

[EN 166]

GB

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 3

Revision: 09.10.2014

Trade name: SONAX Rubber Protectant

(Contd. of page 4)

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

General Information

Appearance:

Form:	Aerosol
Colour:	Yellow tint
Odour:	Characteristic
Odour threshold:	Not determined.

Important information on protection of health and environment, and on safety.

data of the content without propellant

pH-value: Not applicable.

Change in condition

Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	120 - 165 °C

Flash point: 26 °C (DIN 51755)

Flammability (solid, gaseous): Not applicable.

Ignition temperature:

Decomposition temperature: Not determined.

Self-igniting: Not determined.

Danger of explosion: Not determined.

Explosion limits:

Lower:	Explosion limits components: Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics: 0,6Vol%
Upper:	Explosion limits components: Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics: 7,0Vol%

Vapour pressure: Not determined.

Density at 20 °C: 0.77 g/cm³

Relative density Not determined.

Vapour density Not determined.

Evaporation rate Not determined.

Solubility in / Miscibility with water:

Not miscible or difficult to mix.

Partition coefficient (n-octanol/water): Not determined.

Viscosity:

Flow time 10 - 12s (DIN EN ISO 2431 / 4mm)

Dynamic: Not determined.

Kinematic: Not determined.

9.2 Other information No further relevant information available.

SECTION 10: Stability and reactivity

10.1 Reactivity No dangerous reactions known.

10.2 Chemical stability Stable under normal conditions.

10.3 Possibility of hazardous reactions No dangerous reactions known.

10.4 Conditions to avoid

An increase in pressure may lead to bursting.

Keep ignition sources away - Do not smoke.

(Contd. on page 6)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 3

Revision: 09.10.2014

Trade name: SONAX Rubber Protectant

(Contd. of page 5)

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use.

See Section 7 for information on safe handling.

10.5 Incompatible materials: strong oxidizing agents

10.6 Hazardous decomposition products: No dangerous decomposition products known.

SECTION 11: Toxicological information

11.1 Information on toxicological effects There are no toxicological findings on this mixture.

Acute toxicity

LD/LC50 values relevant for classification:

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics

Oral	LD50	>5000 mg/kg (rat) (OECD 401)
Dermal	LD50	>5000 mg/kg (rabbit) (OECD 402)
Inhalative	LC50/4h	>4951 mg/l (rat) (OECD 403)

123-86-4 n-butyl acetate

Oral	LD50	13100 mg/kg (rat)
Dermal	LD50	>17600 mg/kg (rabbit)
Inhalative	LC50/4h	>21 mg/l (rat)

Primary irritant effect:

Skin corrosion/irritation

On the basis of the available data, the classification criteria are not complied with (Conventional Method). Long-term exposure causes slight irritation of the skin.

Serious eye damage/irritation

On the basis of the available data, the classification criteria are not complied with (Conventional Method). May cause slight, short-term eye complaints.

Respiratory or skin sensitisation

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

Repeated dose toxicity

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

None of the ingredients are known to have effects which are carcinogenic, mutagenic or harmful to reproduction.

SECTION 12: Ecological information

12.1 Toxicity

Product is considered to be harmful to aquatic organisms. May have long-term harmful effects in aquatic environments.

Aquatic toxicity:

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics

EL50 / 48h	>22 - <46 mg/l (Daphnia magna)
EL50 / 72h	>1000 mg/l (Pseudokirchneriella subcapitata)
LL50 / 96h	>10 - <30 mg/l (Oncorhynchus mykiss)
NOELR 72 h	< 1 mg/l (Pseudokirchneriella subcapitata)

123-86-4 n-butyl acetate

EC50 / 18h	959 mg/l (Pseudomonas putida)
EC50 / 24h	72.8 mg/l (Daphnia magna) (DIN 38412)
EC50 / 72h	675 mg/l (Scenedesmus subspicatus)
LC 50 / 96 h	62 mg/l (Leuciscus idus melanotus) (DIN 38412)

12.2 Persistence and degradability

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics

Biodegradation	>70 % (-) (28d)
----------------	-----------------

(Contd. on page 7)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 3

Revision: 09.10.2014

Trade name: SONAX Rubber Protectant

(Contd. of page 6)

123-86-4 n-butyl acetate

Biodegradation 98 % (-) (28d (OECD 301 D))

12.3 Bioaccumulative potential No further relevant information available.

12.4 Mobility in soil

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Highly volatile, will partition rapidly to air.

Additional ecological information:

General notes:

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

12.5 Results of PBT and vPvB assessment

PBT: Not applicable.

vPvB: Not applicable.

12.6 Other adverse effects No further relevant information available.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Dangerous waste in accordance with the Directive on the List of Waste Materials

Recommendation Waste must be disposed of while observing the local, official regulations.

European waste catalogue

Disposal / product + Disposal / contaminated packaging

15 01 10* packaging containing residues of or contaminated by dangerous substances

SECTION 14: Transport information

14.1 UN-Number

ADR, IMDG, IATA UN1950

14.2 UN proper shipping name

IMDG AEROSOLS

IATA AEROSOLS, flammable

14.3 Transport hazard class(es)

ADR



Class 2 5F Gases.

Label 2.1

IMDG, IATA



Class 2.1

Label 2.1

14.4 Packing group

ADR, IMDG, IATA Void

14.5 Environmental hazards:

Marine pollutant: No

14.6 Special precautions for user see Sections 6-8

Warning: Gases.

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 3

Revision: 09.10.2014

Trade name: SONAX Rubber Protectant

(Contd. of page 7)

Transport/Additional information:**ADR**

Limited quantities (LQ)	1L
Transport category	2
Tunnel restriction code	D

UN "Model Regulation":	UN1950, AEROSOLS, 2.1
-------------------------------	-----------------------

SECTION 15: Regulatory information**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

The following substance(s) in this product is (are) identified by CAS number either in countries not subject to the REACH regulation or in regulations not yet updated with the new naming convention for hydrocarbon solvents.

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics: CAS 64742-48-9

European Directives:

SEVESO category (96/82/EC): 8

National regulations:**Information about limitation of use:**

Employment restrictions concerning juveniles must be observed.

Employment restrictions concerning pregnant and lactating women must be observed.

15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

Relevant phrases

H226 Flammable liquid and vapour.

H281 Contains refrigerated gas; may cause cryogenic burns or injury.

H304 May be fatal if swallowed and enters airways.

H336 May cause drowsiness or dizziness.

H412 Harmful to aquatic life with long lasting effects.

R10 Flammable.

R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65 Harmful: may cause lung damage if swallowed.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.

Abbreviations and acronyms:

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation

NOEL = No Observed Effect Level

NOEC = No Observed Effect Concentration

LC = Lethal Concentration

EC50 = half maximal effective concentration

log POW = Octanol / water partition coefficient

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

DNEL: Derived No-Effect Level (REACH)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

IOELV = indicative occupational exposure limit values

Flam. Aerosol 1: Flammable aerosols, Hazard Category 1

Press. Gas R: Gases under pressure: Refrigerated liquefied gas

Flam. Liq. 3: Flammable liquids, Hazard Category 3

STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3

(Contd. on page 9)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 3

Revision: 09.10.2014

Trade name: SONAX Rubber Protectant

Asp. Tox. 1: Aspiration hazard, Hazard Category 1
Aquatic Chronic 3: Hazardous to the aquatic environment - Chronic Hazard, Category 3
*** Data compared to the previous version altered.**

(Contd. of page 8)

GB