

SAFETY DATA SHEET

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier	
Trade name or designation of the mixture	KONTAKT 40
Registration number	-
UFI:	063X-M80G-E00G-12XA
Synonyms	None.
Product code	BDS000687AE
Issue date	16-March-2022
Version number	1.0
Revision date	16-March-2022
1.2. Relevant identified uses of t	he substance or mixture and uses advised against
Identified uses	Lubricants
Uses advised against	None known.
1.3. Details of the supplier of the	e safety data sheet
Company name	CRC Industries Europe bv
Address	Touwslagerstraat 1
	9240 Zele
	Belgium
Telephone	+32(0)52/45.60.11
	hse@crcind.com
	www.crcind.com
Company name	CRC Industries UK Ltd.
Address	Wylds Road
	Castlefield Industrial Estate
	TA6 4DD Bridgwater Somerset
	United Kingdom
Telephone	+44 1278 727200
Fax	+44 1278 425644
E-mail	hse.uk@crcind.com
Website	www.crcind.com
1.4. Emergency telephone	Tel.:(+44)(0)1278 72 7200 (office hours: 9-17h CET)

number

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

Physical hazards Aerosols

Category 2

H223 - Flammable aerosol. H229 - Pressurized container: May burst if heated.

2.2. Label elements

Label according to Regulation (EC) No. 1272/2008 as amended

Hazard pictograms



Hazard statements	
H223	Flammable aerosol.
H229	Pressurized container: May burst if heated.
Precautionary statements	
Prevention	
P102	Keep out of reach of children.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
Response	Not assigned.
Storage	
P410 + P412	Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
Disposal	Not assigned.
Supplemental label information	EUH066 - Repeated exposure may cause skin dryness or cracking.
2.3. Other hazards	This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII. The product does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.
SECTION 3: Composition/	information on ingredients

SECTION 3: Composition/information on ingred

Mixture

General information

Chemical name	%	CAS-No. / EC No.	REACH Registration No.	Index No.	Notes
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	50 - 75	EC926-141-6 926-141-6	01-2119456620-43	-	
Classification:	Asp. Tox.	1;H304			
Carbon dioxide	1 - 5	124-38-9 204-696-9	-	-	#
Classification:	Press. Ga	s;H280			
Sulphonic acids, petroleum, sodium salts	1 - 5	68608-26-4 271-781-5	01-2119527859-22	-	
Classification:	Eye Irrit. 2	;H319			

List of abbreviations and symbols that may be used above

#: This substance has been assigned Union workplace exposure limit(s).

M: M-factor

PBT: persistent, bioaccumulative and toxic substance.

vPvB: very persistent and very bioaccumulative substance.

All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

Composition comments

The full text for all H-statements is displayed in section 16.

SECTION 4: First aid measures

Suitable extinguishing

media

General information Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. 4.1. Description of first aid measures Inhalation If symptoms develop move victim to fresh air. Get medical attention if symptoms persist. Skin contact Wash off with soap and water. Get medical attention if irritation develops and persists. Eye contact Rinse with water. Get medical attention if irritation develops and persists. In the unlikely event of swallowing contact a physician or poison control centre. Ingestion Exposure may cause temporary irritation, redness, or discomfort. 4.2. Most important symptoms and effects, both acute and delayed 4.3. Indication of any Treat symptomatically. immediate medical attention and special treatment needed **SECTION 5: Firefighting measures** General fire hazards Flammable aerosol. 5.1. Extinguishing media

Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).

Unsuitable extinguishing Do not use water jet as an extinguisher, as this will spread the fire. media Contents under pressure. Pressurised container may explode when exposed to heat or flame. 5.2. Special hazards arising During fire, gases hazardous to health may be formed. from the substance or mixture 5.3. Advice for firefighters **Special protective** Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA. equipment for firefighters Move containers from fire area if you can do so without risk. Containers should be cooled with **Special fire fighting** water to prevent vapour pressure build up. For massive fire in cargo area, use unmanned hose procedures holder or monitor nozzles, if possible. If not, withdraw and let fire burn out. Use standard firefighting procedures and consider the hazards of other involved materials. In the Specific methods event of fire and/or explosion do not breathe fumes.

SECTION 6: Accidental release measures

6.1. Personal precautions, protect For non-emergency personnel	ctive equipment and emergency procedures Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing.
For emergency responders	Keep unnecessary personnel away. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
6.2. Environmental precautions	Avoid discharge into drains, water courses or onto the ground.
6.3. Methods and material for containment and cleaning up	Stop leak if you can do so without risk. Move the cylinder to a safe and open area if the leak is irreparable. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil etc) away from spilled material. The product is immiscible with water and will spread on the water surface. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.
	Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.
6.4. Reference to other sections	For personal protection, see section 8 of the SDS. For waste disposal, see section 13 of the SDS.

SECTION 7: Handling and storage

7.1. Precautions for safe handling	Pressurised container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. All equipment used when handling the product must be grounded. Do not re-use empty containers. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Observe good industrial hygiene practices.
7.2. Conditions for safe storage, including any incompatibilities	Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store away from incompatible materials (see Section 10 of the SDS). Storage class (TRGS 510): 2B (Aerosol dispensers and lighters)
7.3. Specific end use(s)	Not available.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

UK. EH40 Workplace Exp Components	Type	Value	
Carbon dioxide (CAS 124-38-9)	STEL	27400 mg/m3	
		15000 ppm	
	TWA	9150 mg/m3	
		5000 ppm	
ological limit values	No biological exposure limits noted	for the ingredient(s).	
• • • • •		c	

Recommended monitoring procedures

Follow standard monitoring procedures.

Derived no effect levels (DNELs)

Derived no effect levels (DNEL:	s)			
<u>Workers</u>				
Components	Components		Assessment factor	Notes
Petrolatum (CAS 8009-03-8)				
Long-term, Systemic, De Long-term, Systemic, In		5.8 mg/kg 2.7 mg/m3		
Predicted no effect concentrations (PNECs)	Not available.			
8.2. Exposure controls				
Appropriate engineering controls	applicable, us maintain airbo	e process enclosure orne levels below rec	e used. Ventilation rates should s, local exhaust ventilation, or c ommended exposure limits. If e els to an acceptable level.	ther engineering controls to
Individual protection measures	s, such as perso	nal protective equi	pment	
General information		Use personal protective equipment as required. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.		
Eye/face protection	Wear safety glasses with side shields (or goggles). Use eye protection conforming to EN 166.			
Skin protection				
- Hand protection	time of the glo	ove should be longer ugh time, gloves sho		ard EN 374). The breakthrough ct use. If work lasts longer than h. Nitrile gloves are
- Other	Not available.			
Respiratory protection		ufficient ventilation, v ur cartridge. (Filter ty	vear suitable respiratory equipm pe A)	ent. Chemical respirator with
Thermal hazards	Wear approp	riate thermal protectiv	ve clothing, when necessary.	
Hygiene measures	after handling	the material and be	observe good personal hygien fore eating, drinking, and/or smo to remove contaminants.	
Environmental exposure controls	with the requi	rements of environm nodifications to the p	process equipment should be ental protection legislation. Fun rocess equipment may be nece	

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	
Physical state	Liquid.
Form	Aerosol.
Colour	Amber.
Odour	Characteristic odor.
Odour threshold	Not available.
рН	Not applicable.
Melting point/freezing point	-56.6 °C (-69.9 °F) estimated
Initial boiling point and boiling range	Not available.
Flash point	78.0 °C (172.4 °F) Closed cup
Evaporation rate	Not applicable.
Flammability (solid, gas)	Not available.
Upper/lower flammability or exp	losive limits
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Vapour pressure	57300 hPa estimated
Vapour density	Not available.
Relative density	0.82 g/cm3 at 20°C

Solubility(ies)	
Solubility (water)	Insoluble in water
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	> 200 °C (> 392 °F)
Decomposition temperature	Not available.
Viscosity	Not available.
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.
9.2. Other information	

Aerosol spray enclosed space

Deflagration density	> 400 s/m³
Aerosol spray ignition	< 15 cm
distance	

SECTION 10: Stability and reactivity

10.1. Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
10.4. Conditions to avoid	Avoid high temperatures.
10.5. Incompatible materials	Strong oxidising agents.
10.6. Hazardous decomposition products	Carbon oxides.

SECTION 11: Toxicological information

General information Occupational exposure to the substance or mixture may cause adverse effects.

Information on likely routes of	exposure
Inhalation	Prolonged inhalation may be harmful.
Eye contact	Based on available data, the classification criteria are not met.
Skin contact	Based on available data, the classification criteria are not met.
Ingestion	May cause discomfort if swallowed. However, ingestion is not likely to be a primary route of occupational exposure.
Symptoms	Exposure may cause temporary irritation, redness, or discomfort.
44.4. Information on toxicalor	incluster and the second se

11.1. Information on toxicological effects

Acute toxicity

Based on available data, the classification criteria are not met.

Components	Species	Test Results		
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics				
Acute				
Dermal				
LD50	Rabbit	> 5000 mg/kg		
Inhalation				
LC50	Rat	> 5000 mg/m3, 8 h		
Oral				
LD50	Rat	> 5000 mg/kg		
Skin corrosion/irritation	Based on available data, the classification criteria are not met.			
Serious eye damage/eye irritation	Based on available data, the classification criteria are	e not met.		
Respiratory sensitisation	Based on available data, the classification criteria are	e not met.		
Skin sensitisation	Based on available data, the classification criteria are	e not met.		
Germ cell mutagenicity	Based on available data, the classification criteria are	e not met.		
Carcinogenicity	Based on available data, the classification criteria are	e not met.		
Reproductive toxicity	Based on available data, the classification criteria are	e not met.		
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are	e not met.		

Specific target organ toxicity - repeated exposure	Based on	Based on available data, the classification criteria are not met.		
Aspiration hazard	Not likely,	Not likely, due to the form of the product.		
Mixture versus substance information	Not availa	Not available.		
SECTION 12: Ecological	informatio	n		
12.1. Toxicity		The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.		
Components		Species	Test Results	
Hydrocarbons, C11-C14, n-alkar	nes, isoalkane	s, cyclics, < 2% aromatics		
Aquatic				
Acute				
Crustacea	EC50	Daphnia	1000 mg/l, 48 h	
Fish	LC50	Oncorhynchus mykiss	1000 mg/l, 96 h	
12.2. Persistence and degradability	No data is	No data is available on the degradability of any ingredients in the mixture.		
12.3. Bioaccumulative potentia	al			
Partition coefficient n-octanol/water (log Kow)	Not availa	Not available.		
Bioconcentration factor (BCF)	Not availa	Not available.		
12.4. Mobility in soil	No data a	No data available.		
12.5. Results of PBT and vPvB assessment		This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.		
12.6. Other adverse effects		No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.		

SECTION 13: Disposal considerations

13.1. Waste treatment methods	
Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.
EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Dispose of contents/container in accordance with local/regional/national/international regulations.
Special precautions	Dispose in accordance with all applicable regulations.

SECTION 14: Transport information

ADR

ADI	\	
	14.1. UN number	UN1950
	14.2. UN proper shipping	AEROSOLS, flammable
	name	
	14.3. Transport hazard class	(es)
	Class	2.1
	Subsidiary risk	-
	Label(s)	2.1
	Hazard No. (ADR)	Not available.
	Tunnel restriction code	D
	14.4. Packing group	Not available.
	14.5. Environmental hazards	No
	14.6. Special precautions	Read safety instructions, SDS and emergency procedures before handling.
	for user	
RID		
	14.1. UN number	UN1950
	14.2. UN proper shipping	AEROSOLS, flammable
	name	

14.3. Transport hazard class(es) Class 2.1 Subsidiary risk 2.1 Label(s) 14.4. Packing group Not available. 14.5. Environmental hazards No Read safety instructions, SDS and emergency procedures before handling. 14.6. Special precautions for user ADN UN1950 14.1. UN number 14.2. UN proper shipping AEROSOLS, flammable name 14.3. Transport hazard class(es) Class 2.1 Subsidiary risk 2.1 Label(s) Not available. 14.4. Packing group 14.5. Environmental hazards No 14.6. Special precautions Read safety instructions, SDS and emergency procedures before handling. for user ΙΑΤΑ UN1950 14.1. UN number Aerosols, flammable 14.2. UN proper shipping name 14.3. Transport hazard class(es) Class 2.1 Subsidiary risk 14.4. Packing group Not available. 14.5. Environmental hazards No 10L **ERG Code** 14.6. Special precautions Read safety instructions, SDS and emergency procedures before handling. for user Other information Allowed with restrictions. Passenger and cargo aircraft Allowed with restrictions. Cargo aircraft only IMDG 14.1. UN number UN1950 Aerosols, flammable 14.2. UN proper shipping name 14.3. Transport hazard class(es) Class 2.1 Subsidiary risk 14.4. Packing group Not available. 14.5. Environmental hazards Marine pollutant No F-D, S-U EmS 14.6. Special precautions Read safety instructions, SDS and emergency procedures before handling. for user Not established. 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code ADN; ADR; IATA; IMDG; RID



SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Retained direct EU regulations

- Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended Not listed.
- Regulation (EU) 2019/1021 On persistent organic pollutants (recast), as amended Not listed.
- Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended Not listed.
- Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended Not listed.
- Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended Not listed.
- Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended Not listed.
- Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry, as amended Carbon dioxide (CAS 124-38-9)
- Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended Not listed.

Other EU regulations

Directive 2012/18/EU on major accident hazards involving dangerous substances, as amended

Not listed.

Other regulations

The product is classified and labelled in accordance with Regulation (EC) 1272/2008 (CLP Regulation) as amended. This Safety Data Sheet complies with the requirements of Regulation (EC) No 1907/2006, as amended.

Follow national regulation for work with chemical agents in accordance with Directive 98/24/EC, as amended.

15.2. Chemical safety No Chemical Safety Assessment has been carried out.

assessment

SECTION 16: Other information

List of abbreviations

ADN: European Agreement Concerning the International Carriage of Dangerous Goods by Inland Waterways. ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road. ADR: European Agreement Concerning the International Carriage of Dangerous Goods by Road. ATE: Acute Toxicity Estimate according to REGULATION (EC) No 1272/2008 (CLP). CAS: Chemical Abstract Service. Ceiling: Short Term Exposure Limit Ceiling value. CEN: European Committee for Standardization. CLP: Classification, Labeling and Packaging REGULATION (EC) No 1272/2008 on classification, labeling and packaging of substances and mixtures. GWP: Global Warming Potential. IATA: International Air Transport Association. IBC Code: International Code for the Construction and Equipment of Ships Carrying Dangerous Chemicals in Bulk. IMDG: International Maritime Dangerous Goods. MAK: Threshold limit values Germany (Maximale Arbeitsplatzkonzentration - DFG). MARPOL: International Convention for the Prevention of Pollution from Ships. PBT: Persistent, bioaccumulative and toxic. REACH: Registration, Evaluation and Authorization of Chemicals (REGULATION (EC) No 1907/2006 concerning Registration, Evaluation Authorization and Restriction of Chemicals). RID: Regulations concerning the international carriage of dangerous goods by rail (Règlement International concernant le transport de marchandises dangereuses par chemin de fer). RID: Regulations concerning the International Carriage of Dangerous Goods by Rail. STEL: Short term exposure limit. TLV: Threshold Limit Value. TWA: Time Weighted Average.

References

Information on evaluation method leading to the classification of mixture

Full text of any H-statements not written out in full under Sections 2 to 15

Revision information Training information Disclaimer VOC: Volatile organic compounds. vPvB: Very persistent and very bioaccumulative. STEL: Short-term Exposure Limit.

Not available.

The classification for health and environmental hazards is derived by a combination of calculation methods and test data, if available.

H280 Contains gas under pressure; may explode if heated. H304 May be fatal if swallowed and enters airways. H319 Causes serious eye irritation. None.

Follow training instructions when handling this material.

CRC Industries Europe byba cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.