

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

Booster

Print date: 27.05.2015

Product code: 148

Page 1 of 6

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Booster

1.2. Relevant identified uses of the substance or mixture and uses advised against**Uses advised against**

Reserved for industrial and professional use.

1.3. Details of the supplier of the safety data sheet

Company name:	ITW LLC & Co. KG	
Street:	Mühlackerstrasse 147	
Place:	D-75417 Mühlacker	
Telephone:	++49(0)7041-96340	Telefax: ++49(0)7041-963429
e-mail:	info@itwcp.de	
Internet:	www.itwcp.de	
Responsible Department:	Produktsicherheit	

1.4. Emergency telephone number: ++49(0)7041-96340
Mo. - Do. 8.00 - 16.30 Fr. 8.00 - 14.00

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to Directive 67/548/EEC or 1999/45/EC**

This mixture is not classified as hazardous according to Directive 1999/45/EC.

Classification according to Regulation (EC) No. 1272/2008 [CLP]Hazard Statements:
Pressurised container: May burst if heated.**2.2. Label elements**

Signal word: Warning

Hazard statements

H229 Pressurised container: May burst if heated.

Precautionary statements

P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P251	Do not pierce or burn, even after use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

Special labelling of certain mixtures

6,0 % by mass of the contents are flammable.

SECTION 3: Composition/information on ingredients**3.2. Mixtures**

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Booster

Print date: 27.05.2015

Product code: 148

Page 2 of 6

Hazardous components

EC No	Chemical name	Quantity
CAS No	Classification according to Directive 67/548/EEC	
Index No	Classification according to Regulation (EC) No. 1272/2008 [CLP]	
REACH No		
	1,1,1,2-Tetrafluoroethane	50-100 %
811-97-2		
	Liquefied gas; H280	
204-065-8	dimethyl ether	<10 %
115-10-6	F+ - Extremely flammable R12	
603-019-00-8	Flam. Gas 1; H220	

Full text of R-, H- and EUH-phrases: see section 16.

SECTION 4: First aid measures**4.1. Description of first aid measures****General information**

No special measures are necessary.

After inhalation

Provide fresh air.

After contact with skin

After contact with skin, wash immediately with: Water. Change contaminated clothing.

After contact with eyes

Rinse immediately carefully and thoroughly with eye-bath or water.

After ingestion

If swallowed, immediately drink: Water. If swallowed, do not induce vomiting: seek medical advice immediately and show this container or label.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**Co-ordinate fire-fighting measures to the fire surroundings. Extinguishing powder. Carbon dioxide (CO₂). Foam.**Unsuitable extinguishing media**

Water. Water with tenside additive.

5.2. Special hazards arising from the substance or mixture

Heating causes rise in pressure with risk of bursting. In case of fire and/or explosion do not breathe fumes.

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus. Co-ordinate fire-fighting measures to the fire surroundings.

Additional information

In case of fire: Wear self-contained breathing apparatus.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Booster

Print date: 27.05.2015

Product code: 148

Page 3 of 6

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Provide adequate ventilation. Wear personal protection equipment. Remove all sources of ignition.

6.2. Environmental precautions

Do not allow to enter into surface water or drains.

6.3. Methods and material for containment and cleaning up

Ventilate affected area. Absorb with liquid-binding material (e.g. sand, diatomaceous earth, acid- or universal binding agents).

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

Provide adequate ventilation as well as local exhaust at critical locations. Avoid contact with skin and eyes.

Advice on protection against fire and explosion

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep container tightly closed. Observe in addition any national regulations!

Further information on storage conditions

none

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits (EH40)

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
811-97-2	1,1,1,2-Tetrafluoroethane (HFC 134a)	1000	4240		TWA (8 h)	WEL
		-	-		STEL (15 min)	WEL
115-10-6	Dimethyl ether	400	766		TWA (8 h)	WEL
		500	958		STEL (15 min)	WEL

8.2. Exposure controls



Protective and hygiene measures

Change contaminated clothing. Wash hands before breaks and after work. When using do not eat or drink.

Eye/face protection

Tightly sealed safety glasses.

Hand protection

DIN EN 374 Tested protective gloves are to be worn: Butyl rubber. For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Booster

Print date: 27.05.2015

Product code: 148

Page 4 of 6

Skin protection

Protective clothing:

Respiratory protection

In case of inadequate ventilation wear respiratory protection.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state: Aerosol
Colour: colourless
Odour: characteristic

Test method**Changes in the physical state**

Flash point: No flash point according to standard method.

Lower explosion limits: 0 vol. %
Upper explosion limits: 0 vol. %

SECTION 10: Stability and reactivity**SECTION 11: Toxicological information****11.1. Information on toxicological effects****Additional information on tests**

The classification was carried out according to the calculation method of the Preparations Directive (1999/45/EC).

SECTION 12: Ecological information**12.3. Bioaccumulative potential****Partition coefficient n-octanol/water**

CAS No	Chemical name	Log Pow
115-10-6	dimethyl ether	0,1

Further information

Do not allow to enter into surface water or drains. The classification was carried out according to the calculation method of the Preparations Directive (1999/45/EC).

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Advice on disposal**

Dispose of waste according to applicable legislation.

Waste disposal number of waste from residues/unused products

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing dangerous substances
Classified as hazardous waste.

Waste disposal number of contaminated packaging

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Booster

Print date: 27.05.2015

Product code: 148

Page 5 of 6

Contaminated packaging

Dispose of waste according to applicable legislation.

SECTION 14: Transport information**Land transport (ADR/RID)**

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.2



Classification code: 5A
Special Provisions: 190 327 625
Limited quantity: 1 L
Transport category: 3
Tunnel restriction code: E

Other applicable information (land transport)

E0

Inland waterways transport (ADN)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.2



Classification code: 5A
Special Provisions: 190 327 344 625
Limited quantity: 1 L

Other applicable information (inland waterways transport)

E0

Marine transport (IMDG)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
14.4. Packing group: -
Hazard label: 2, see SP63

Special Provisions: 63, 190, 277, 327, 344, 959
Limited quantity: See SP277
EmS: F-D, S-U

Other applicable information (marine transport)

E0

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Booster

Print date: 27.05.2015

Product code: 148

Page 6 of 6

Air transport (ICAO)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2.2
Hazard label: 2.2



Special Provisions: A98 A145 A167
Limited quantity Passenger: 30 kg G
IATA-packing instructions - Passenger: 204
IATA-max. quantity - Passenger: 75 kg
IATA-packing instructions - Cargo: 204
IATA-max. quantity - Cargo: 150 kg

Other applicable information (air transport)

E0
: Y204

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: no

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****National regulatory information**

Water contaminating class (D): 1 - slightly water contaminating

SECTION 16: Other information**Relevant R-phrases (Number and full text)**

12 Extremely flammable.

Relevant H- and EUH-phrases (Number and full text)

H220 Extremely flammable gas.
H229 Pressurised container: May burst if heated.
H280 Contains gas under pressure; may explode if heated.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)