



Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 8

Pattex Hot Sticks transparent

SDS No. : 712183
V001.2

Revision: 13.04.2023

printing date: 19.01.2024

Replaces version from: 27.05.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Pattex Hot Sticks transparent

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Hotmelt adhesive

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

SDSinfo.Adhesive@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.2. Label elements

Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.3. Other hazards

None if used properly.

Following substances are present in a concentration \geq the concentration limit for depiction in Section 3 and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in a concentration \geq the concentration limit for depiction in Section 3 that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Contains no dangerous substances exceeding the limits of the EU-Regulation

SECTION 4: First aid measures

4.1. Description of first aid measures

General information:

In case of adverse health effects seek medical advice.

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:

Rinse immediately with plenty of running water, seek medical advice if necessary.

Ingestion:

Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO₂) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Wear protective equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Dispose of contaminated material as waste according to Section 13.
Remove mechanically.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Avoid skin and eye contact.

Hygiene measures:

Do not eat, drink or smoke while working.
Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Store in sealed original container.
Store in a cool, dry place.
Protect from direct sun-light and temperature above 50°C in any case.
Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

7.3. Specific end use(s)

Hotmelt adhesive

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**

Valid for
Great Britain

None

Occupational Exposure Limits

Valid for
Ireland

None

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:
Not needed.

Hand protection:
Wear heat resistance gloves while working with the hot melt (EN 407).

Eye protection:
Not needed.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Delivery form	cartridges
Colour	transparent
Odor	odourless
Physical state	solid
Melting point	200 °C (392 °F)no method / method unknown
Solidification temperature	Not applicable, Product is a solid.
Initial boiling point	Not applicable, Polymeric solid, thermally degrades above 250 °C.
Flammability	The product is not flammable.
Explosive limits	Not applicable, Product is a solid.
Flash point	No flash point up to 200 °C
Auto-ignition temperature	Not applicable, Product is a solid.
Decomposition temperature	Not applicable, Substance/mixture is not self-reactive, no organic peroxide and does not decompose under foreseen conditions of use
pH	Not applicable, Product is non-soluble (in water).
Viscosity (kinematic)	Not applicable, Product is a solid.
Viscosity, dynamic (Brookfield; 160 °C (320 °F))	25.000 - 33.000 mPa.s no method / method unknown
Solubility (qualitative) (23 °C (73.4 °F); Solvent: Water)	Insoluble
Partition coefficient: n-octanol/water	Not applicable
Vapour pressure (20 °C (68 °F))	Mixture < 0,1 hPa
Density (20 °C (68 °F))	0,92 - 0,98 g/cm3
Relative vapour density:	Not applicable, Product is a solid.
Particle characteristics	Not applicable Product is not powder.

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

None known.

SECTION 11: Toxicological information**General toxicological information:**

To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly.

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**Acute oral toxicity:**

No data available.

Acute dermal toxicity:

No data available.

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

No data available.

Serious eye damage/irritation:

No data available.

Respiratory or skin sensitization:

No data available.

Germ cell mutagenicity:

No data available.

Carcinogenicity

No data available.

Reproductive toxicity:

No data available.

STOT-single exposure:

No data available.

STOT-repeated exposure:

No data available.

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information**General ecological information:**

If used properly the product is not toxic to water organisms after hardening.
Do not empty into drains, soil or bodies of water.

12.1. Toxicity**Toxicity (Fish):**

No data available.

Toxicity (aquatic invertebrates):

No data available.

Chronic toxicity (aquatic invertebrates):

No data available.

Toxicity (Algae):

No data available.

Toxicity (microorganisms):

No data available.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code

080410

SECTION 14: Transport information

14.1. UN number or ID number

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Maritime transport in bulk according to IMO instruments

not applicable

SECTION 15: Regulatory information

No information available:

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009):	Not applicable
Prior Informed Consent (PIC) (Regulation (EU) No 649/2012):	Not applicable
Persistent organic pollutants (Regulation (EU) 2019/1021):	Not applicable

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (SDSInfo.Adhesive@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.