

ting date 12.09.2015	Version: 3	Revision: 11.06.207
SECTION 1: Identifi	cation of the substance/mixture and of	f the company/undertaking
1.1 Product identifier		
Trade name: SONAX Co	ckpit Spray Lemon-fresh	
Article number: 343041, 1.2 Relevant identified u Sector of Use SU21 Consumer uses: F SU22 Professional uses. Product category PC35		inment, services, craftsmen)
	er of the safety data sheet	
Further information obta Product safety E-mail: erp@sonax.de		
Phone: + +49 (0) 8431 53		
1.4 Emergency telephon	ne number: Emergency Phone Munich Tel.: +49 (C))89 19240
SECTION 2: Hazard		
Flam. Aerosol 1 H222-H2	to Regulation (EC) No 1272/2008 229 Extremely flammable aerosol. Pressurised cor to Directive 67/548/EEC or Directive 1999/45/E	·
F+; Extremely flammable		
R12: Extremely flamma		
R12: Extremely flamma R66: Repeated exposu Information concerning Warning! Pressurised con	re may cause skin dryness or cracking. particular hazards for human and environment tainer.	
R12: Extremely flamma R66: Repeated exposu Information concerning Warning! Pressurised con Contact with skin and inha 2.2 Label elements Labelling according to F	re may cause skin dryness or cracking. particular hazards for human and environmen t	
R12: Extremely flamma R66: Repeated exposu Information concerning Warning! Pressurised con Contact with skin and inha 2.2 Label elements Labelling according to F The product is classified a	re may cause skin dryness or cracking. particular hazards for human and environment tainer. alation of aerosols/ vapours of the preparation shou Regulation (EC) No 1272/2008	
R12: Extremely flamma R66: Repeated exposu Information concerning Warning! Pressurised com Contact with skin and inha 2.2 Label elements Labelling according to F The product is classified a Hazard pictograms GHS02 Signal word Danger Hazard statements H222-H229 Extremely flai	re may cause skin dryness or cracking. particular hazards for human and environment tainer. alation of aerosols/ vapours of the preparation shou Regulation (EC) No 1272/2008 and labelled according to the CLP regulation. mmable aerosol. Pressurised container: May burst	uld be avoided.
R12:Extremely flammaR66:Repeated exposuInformation concerningWarning! Pressurised conditionContact with skin and inhe2.2 Label elementsLabelling according to FThe product is classified aHazard pictogramsGHS02Signal word DangerHazard statementsH222-H229 Extremely flaitPrecautionary statementP102Keep out of reP210Keep away fr	re may cause skin dryness or cracking. particular hazards for human and environment itainer. alation of aerosols/ vapours of the preparation shou Regulation (EC) No 1272/2008 and labelled according to the CLP regulation. Manual Labelled according to the CLP regulation. Second Second S	uld be avoided. if heated.
R12:Extremely flammaR66:Repeated exposuInformation concerningWarning! Pressurised conditionContact with skin and inhat2.2 Label elementsLabelling according to FThe product is classified aHazard pictogramsGHS02Signal word DangerHazard statementsH222-H229 Extremely flamP102Keep out of reP102Keep out of reP210Keep away frP251Do not pierceP260Do not breattP211Do not sprayP271Use only outo	re may cause skin dryness or cracking. particular hazards for human and environment itainer. alation of aerosols/ vapours of the preparation shou Regulation (EC) No 1272/2008 and labelled according to the CLP regulation. Manual abelled according to the CLP regulation. Second Statements of the container: May burst ts each of children. som heat, hot surfaces, sparks, open flames and ot a or burn, even after use. the spray. on an open flame or other ignition source. doors or in a well-ventilated area.	uld be avoided. if heated. ther ignition sources. No smoking.
R12:Extremely flammaR66:Repeated exposuInformation concerningWarning! Pressurised comContact with skin and inhat2.2 Label elementsLabelling according to FThe product is classified aHazard pictogramsGHS02Signal word DangerHazard statementsH222-H229 Extremely flamP102Keep out of reP102Keep out of reP210Keep away frP251Do not pierceP260Do not breattP211Do not sprayP271Use only outoP410+P412 Protect from	re may cause skin dryness or cracking. particular hazards for human and environment itainer. alation of aerosols/ vapours of the preparation shou Regulation (EC) No 1272/2008 and labelled according to the CLP regulation. Manual abelled according to the CLP regulation. Second Second Se	uld be avoided. if heated. ther ignition sources. No smoking. g 50 °C/122 °F.
R12:Extremely flammaR66:Repeated exposuInformation concerningWarning! Pressurised conditionContact with skin and inhat2.2 Label elementsLabelling according to FThe product is classified aHazard pictogramsGHS02Signal word DangerHazard statementsH222-H229 Extremely flamP102Keep out of reP102Keep out of reP210Keep away frP251Do not pierceP260Do not breattP211Do not sprayP271Use only outoP410+P412 Protect fromP501Dispose of coAdditional information:	re may cause skin dryness or cracking. particular hazards for human and environment itainer. alation of aerosols/ vapours of the preparation shou Regulation (EC) No 1272/2008 and labelled according to the CLP regulation. Manual abelled according to the CLP regulation. The spirate state st	uld be avoided. if heated. ther ignition sources. No smoking. g 50 °C/122 °F.

Printing date 12.09.2015

SONAX®

Version: 3

Revision: 11.06.2014

Trade name: SONAX Cockpit Spray Lemon-fresh

(Contd. of page 1)

2.3 Other hazards Results of PBT and vPvB assessment PBT: Not applicable.

vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Description: Formulation consisting of pressurised gas and solvents with additives

CAS: 106-97-8	butane	15-25%
EINECS: 203-448-7	▶ F+ R12	
	🚸 Flam. Gas 1, H220; Press. Gas C, H280	
CAS: 74-98-6	propane	15-25%
EINECS: 200-827-9	▶ F+ R12	
	🚸 Flam. Gas 1, H220; Press. Gas C, H280	
EC number: 934-956-3	Hydrocarbons, C15-C20, n-alkanes, isoalkanes, cyclics, < 0.03%	15-25%
Reg.nr.: 01-2119827000-58-XXXX	aromatics	
	🗙 Xn R65	
	🚸 Asp. Tox. 1, H304	
EC number: 934-954-2	Hydrocarbons, C13-C16, n-alkanes, isoalkanes, cyclics, < 0.03%	10-15%
Reg.nr.: 01-2119826592-36-XXXX		
	🗙 Xn R65	
	🚸 Asp. Tox. 1, H304	
EC number: 920-107-4	Hydrocarbons, C12-C15, n-alkanes, isoalkanes, cyclics, < 2%	10-15%
Reg.nr.: 01-2119453414-43-xxxx	aromatics	
	Xn R65	
	R66	
	🗞 Asp. Tox. 1, H304	
CAS: 75-28-5	isobutane	5-10%
EINECS: 200-857-2	F+ R12	
	🚸 Flam. Gas 1, H220; Press. Gas C, H280	
CAS: 138-86-3	dipentene	<1.0%
EINECS: 205-341-0	🗙 Xn R65; 🔀 Xi R38; 🗙 Xi R43; 援 N R50/53 R10	
	🚸 Flam. Liq. 3, H226; 🚸 Asp. Tox. 1, H304; 🚸 Aquatic Acute	
	1, H400; Aquatic Chronic 1, H410; 🚸 Skin Irrit. 2, H315; Skin	
	Sens. 1, H317	
Regulation (EC) No 648/2004 on	detergents / Labelling for contents	
aliphatic hydrocarbons		≥ 30%
perfumes, Limonene, Citral, Linaloo	ol. Hexvl Cinnamal. Citronellol	

Additional information:

Any entry in the EC-column that begins with the number "9" is a Provisional List Number provided by ECHA pending publication of the official EC Inventory Number for the substance. See Section 15 for additional CAS number information for the substance.

For the wording of the listed risk phrases refer to section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures
General information:
Take affected persons out of danger area and lay down.
Remove soiled clothing
After inhalation:
Supply fresh air.
In the event of irritation of the respiratory tract, dizziness, nausea or unconsciousness, call medical assistance immediately .

Printing date 12.09.2015

ΟΝΔΧ

Version: 3

Revision: 11.06.2014

Trade name: SONAX Cockpit Spray Lemon-fresh

(Contd. of page 2) After skin contact: Generally the product does not irritate the skin. Wash the areas of skin affected with water and a mild detergent. After eye contact: Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor. After swallowing: Do not induce vomiting; call for medical help immediately. 4.2 Most important symptoms and effects, both acute and delayed Headache Disziness Nausea Drowsiness Reddening, drying and crack formation of the skin 4.3 Indication of any immediate medical attention and special treatment needed Treatment in accordance with the doctor's assessment of the patient's condition. Symptomatic treatment. SECTION 5: Firefighting measures 5.1 Extinguishing media Suitable extinguishing agents: Foam Carbon dioxide Fire-extinguishing powder Water haze For safety reasons unsuitable extinguishing agents: Water with full jet 5.2 Special hazards arising from the substance or mixture In case of fire, the following can be released: Carbon monoxide and carbon dioxide 5.3 Advice for firefighters Protective equipment: Do not inhale explosion gases or combustion gases. Wear self-contained respiratory protective device. Wear fully protective suit. Additional information Cool endangered receptacles with water spray. Collect contaminated fire fighting water separately. It must not enter the sewage system. SECTION 6: Accidental release measures 6.1 Personal precautions, protective equipment and emergency procedures Keep away from ignition sources.

Ensure adequate ventilation Wear protective equipment. Keep unprotected persons away. **6.2 Environmental precautions:** Do not allow to penetrate the ground/soil. Do not allow to enter sewers/ surface or ground water. **6.3 Methods and material for containment and cleaning up:** Ensure adequate ventilation. Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust). Dispose contaminated material as waste according to item 13. **6.4 Reference to other sections** See Section 7 for information on safe handling. See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

7.1 Precautions for safe handling Ensure good ventilation/exhaustion at the workplace. Information about fire - and explosion protection: Keep ignition sources away - Do not smoke.

(Contd. on page 4)

GB



Printing date 12.09.2015

Version: 3

Revision: 11.06.2014

Trade name: SONAX Cockpit Spray Lemon-fresh

(Contd. of page 3) Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use.

Do not spray onto a naked flame or any incandescent material.

Highly volatile, flammable constituents are released during processing.

7.2 Conditions for safe storage, including any incompatibilities

Storage:

Requirements to be met by storerooms and receptacles:

Provide solvent resistant, sealed floor.

Observe official regulations on storing packagings with pressurised containers.

Information about storage in one common storage facility: Store away from foodstuffs.

Further information about storage conditions:

Store receptacle in a well ventilated area.

Store in a cool place. Heat will increase pressure and may lead to the receptacle bursting.

Protect from heat and direct sunlight.

Recommended storage temperature: 20 °C.

7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Ingredients with limit values that require monitoring at the workplace: 106-97-8 butane WEL (Great Britain) Short-term value: 1810 mg/m³, 750 ppm Long-term value: 1450 mg/m³, 600 ppm Carc (if more than 0.1% of buta-1.3-diene) Additional information: The lists valid during the making were used as basis. 8.2 Exposure controls Suitable technical control devices Ensure good ventilation. This can be achieved by localised extraction or general ventilation. If this is not sufficient to keep the concentration below the occupational exposure limit, suitable breathing protection is to be worn. Personal protective equipment: General protective and hygienic measures: The usual precautionary measures are to be adhered to when handling chemicals. Wash hands before breaks and at the end of work. Keep away from foodstuffs, beverages and feed. Respiratory protection: If the occupational exposure limit is exceeded: The following breathing protection is recommended: Respiratory filter for organic gases and vapours (Type A) Identification colour: Brown [DIN EN 14387] Protection of hands: Protective gloves The glove material has to be impermeable and resistant to the product/ the substance/ the preparation. Material of gloves Nitrile rubber, NBR Recommended thickness of the material: ≥ 0.4 mm IEN 3741 **Penetration time of glove material** Value for the permeation: Level 6 (\geq 480min) Eye protection: Not required in normal cases GB

(Contd. on page 5)

SONAX

Printing date 12.09.2015

Safety data sheet according to 1907/2006/EC, Article 31

Version: 3

Revision: 11.06.2014

(Contd. of page 4)

Trade name: SONAX Cockpit Spray Lemon-fresh

SECTION 9: Physical and chemical properties		
9.1 Information on basic physical and chemical p	properties	
General Information		
Appearance:		
Form:	Aerosol	
Colour: Odour:	Colourless	
Odour: Odour threshold:	Characteristic Not determined.	
Important information on protection of health an		
environment, and on safety.	data of the content without propellant	
pH-value:	Not applicable.	
Change in condition		
Melting point/Melting range:	Undetermined.	
Boiling point/Boiling range:	242 - 275 °C	
Flash point:	93 °C (DIN 51755)	
Flammability (solid, gaseous):	Not applicable.	
Ignition temperature:		
Decomposition temperature:	Not determined.	
Self-igniting:	Not determined.	
Danger of explosion:	Not determined. In use, may form flammable/explosive vapour-air	
	mixture.	
Explosion limits:		
Lower:	Not determined.	
Upper:	Not determined.	
Vapour pressure:	Not determined.	
Density at 20 °C:	0.80 - 0.82 g/cm ³	
Relative density	Not determined.	
Vapour density	Not determined.	
Evaporation rate	Not applicable.	
Solubility in / Miscibility with		
water:	Not miscible or difficult to mix.	
Partition coefficient (n-octanol/water):	Not determined.	
Viscosity:		
Flow time at 20 °C	10-15 s (DIN EN ISO 2431/4mm)	

Not determined. Not determined. No further relevant information available.

SECTION 10: Stability and reactivity

10.1 Reactivity No dangerous reactions known.

- 10.2 Chemical stability Stable under normal conditions.
- 10.3 Possibility of hazardous reactions Develops readily flammable gases/fumes.
- 10.4 Conditions to avoid

Dynamic: Kinematic:

9.2 Other information

An increase in pressure may lead to bursting.

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use.

Keep ignition sources away - Do not smoke.

See Section 7 for information on safe handling.

10.5 Incompatible materials: strong oxidizing agents

(Contd. on page 6)

GB

cording to 1907/2000/EC, An

Version: 3

Revision: 11.06.2014

Trade name: SONAX Cockpit Spray Lemon-fresh

10.6 Hazardous decomposition products: No dangerous decomposition products known.

SECTION 11: Toxicological information

11.1 Information on toxicological effects There are no toxicological findings on this mixture. **Acute toxicity**

LD/LC50 values relevant for classification:Aliphatic and cyclic-aliphatic hydrocarbon mixture:oral:LD50 (rat): >5000mg/kg [OECD 401]dermal:LD50 (rabbit) >3160mg/kg [OECD 402]inhalative:LC50/4h (rat) >4951 mg/m³ [OECD 403]

106-97-8 butane

Inhalative LC50/4h 658 mg/l (rat)

Primary irritant effect: Skin corrosion/irritation

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

Serious eye damage/irritation

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

Respiratory or skin sensitisation

On the basis of the available data, the classification criteria are not complied with (Conventional Method). Contains dipentene. May produce an allergic reaction.

Repeated dose toxicity

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

CMR effects (carcinogenity, mutagenicity and toxicity for reproduction)

None of the ingredients are known to have effects which are carcinogenic, mutagenic or harmful to reproduction.

SECTION 12: Ecological information

12.1 Toxicity There are no ecotoxicological data available on this mixture. Aquatic toxicity: Aliphatic and cyclic-aliphatic hydrocarbon mixture: Acute: Daphnia - LL50 / 48h: >1000mg/l Fish - LL50 / 96h: >1000mg/l Alga - ErL50 / 72h: >1000mg/l Longterm: Daphnia magna - NOELR/21d: >1000mg/l Oncorhynchus mykiss - NOELR/28d: >1000mg/l 12.2 Persistence and degradability Aliphatic and cyclic-aliphatic hydrocarbon mixture: Biodegradation >70% (28d) 12.3 Bioaccumulative potential No further relevant information available. 12.4 Mobility in soil No further relevant information available. Additional ecological information: General notes: The product may not be released into the environment without control. 12.5 Results of PBT and vPvB assessment PBT: Not applicable. vPvB: Not applicable. 12.6 Other adverse effects No further relevant information available.

SECTION 13: Disposal considerations

13.1 Waste treatment methods Dangerous waste in accordance with the Directive on the List of Waste Materials **Recommendation** Waste must be disposed of while observing the local, official regulations.

(Contd. on page 7)



Printing date 12.09.2015

(Contd. of page 5)

GB

SONAX®

Printing date 12.09.2015

Safety data sheet according to 1907/2006/EC, Article 31

Version: 3

Revision: 11.06.2014

Trade name: SONAX Cockpit Spray Lemon-fresh

(Contd. of page 6) Must not be disposed together with household garbage. Do not allow product to reach sewage system. **European waste catalogue**

Disposal / product + Disposal / contaminated packaging

15 01 10* packaging containing residues of or contaminated by dangerous substances

UN1950 1950 AEROSOLS AEROSOLS AEROSOLS, flammable
1950 AEROSOLS AEROSOLS
AEROSOLS
AEROSOLS, flammable
5)
2 5F Gases.
2.1
2.1
2.1
Void
No
ser Warning: Gases.
ion:
1L
2
D

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture The following substance(s) in this product is (are) identified by CAS number either in countries not subject to the REACH regulation or in regulations not yet updated with the new naming convention for hydrocarbon solvents.

Hydrocarbons, C15-C20, n-alkanes, isoalkanes, cyclics, < 0.03% aromatics: CAS: 64742-46-7 Hydrocarbons, C13-C16, n-alkanes, isoalkanes, cyclics, < 0.03% aromatics: CAS 64742-46-7 Hydrocarbons, C12-C15, n-alkanes, isoalkanes, cyclics, < 2% aromatics: CAS 64742-47-8

(Contd. on page 8)

Printing date 12.09.2015

Version: 3

Revision: 11.06.2014

(Contd. of page 7)

Trade name: SONAX Cockpit Spray Lemon-fresh

National regulations:

Information about limitation of use:

Employment restrictions concerning juveniles must be observed.

Employment restrictions concerning pregnant and lactating women must be observed.

15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

Relevant phrases

- H220 Extremely flammable gas.
- H226 Flammable liquid and vapour.
- H280 Contains gas under pressure; may explode if heated.
- H304 May be fatal if swallowed and enters airways.
- H315 Causes skin irritation.
- May cause an allergic skin reaction. H317
- H400 Very toxic to aquatic life.
- Very toxic to aquatic life with long lasting effects. H410
- R10 Flammable.
- R12 Extremely flammable.
- R38 Irritating to skin.
- R43 May cause sensitisation by skin contact.
- R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R65 Harmful: may cause lung damage if swallowed.
- Repeated exposure may cause skin dryness or cracking. R66

Abbreviations and acronyms:

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation NOEL = No Observed Effect Level

NOEC = No Observed Effect Concentration

LC = letal Conentration

EC50 = half maximal effective conentraion

log POW = Octanol / water partition coefficient GHS: Globally Harmonized System of Classification and Labelling of Chemicals

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods IATA: International Air Transport Association GHS: Globally Harmonised System of Classification and Labelling of Chemicals EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

- CAS: Chemical Abstracts Service (division of the American Chemical Society) LC50: Lethal concentration, 50 percent
- LD50: Lethal dose, 50 percent

IOELV = indicative occupational exposure limit values

Flam. Gas 1: Flammable gases, Hazard Category 1

Flam. Aerosol 1: Flammable aerosols, Hazard Category 1 Press. Gas C: Gases under pressure: Compressed gas Flam. Liq. 3: Flammable liquids, Hazard Category 3

Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2

Skin Sens. 1: Sensitisation - Skin, Hazard Category 1 Asp. Tox. 1: Aspiration hazard, Hazard Category 1 Aquatic Acute 1: Hazardous to the aquatic environment - AcuteHazard, Category 1

Aquatic Chronic 1: Hazardous to the aquatic environment - Chronic Hazard, Category 1

* Data compared to the previous version altered.

GB

