
PCB terminal block - FFKDSA1/V-2,54- 2 - 1789618

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



The illustration shows the 10-position version

PCB terminal block, Nominal current: 6 A, Nom. voltage: 160 V, Pitch: 2.54 mm, Number of positions: 2, Connection method: Spring-cage conn., Mounting: Soldering, Conductor/PCB connection direction: 90 °, Color: green

Key commercial data

package_quantity	50
GTIN	4017918260675

Technical data

Dimensions

Length	12.6 mm
Pitch	2.54 mm
Dimension a	2.54 mm
Pin dimensions	0,5 x 0,8 mm
Hole diameter	1.1 mm

General

Range of articles	FFKDS(A)/V
Insulating material group	I
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	63 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	320 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	6 A
Nominal cross section	0.5 mm²
Maximum load current	6 A
Insulating material	PA
Solder pin surface	Sn
Inflammability class according to UL 94	V2
Stripping length	11 mm
Number of positions	2

PCB terminal block - FFKDSA1/V-2,54- 2 - 1789618

Technical data

Connection data

Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	20
Minimum AWG according to UL/CUL	26
Maximum AWG according to UL/CUL	20

classifications

eCl@ss

eCl@ss 4.0	27141109
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27261101
eCl@ss 7.0	27440401
eCl@ss 8.0	27440401

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002643

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	39121432
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

approvals

CSA / UL Recognized / cUL Recognized / cULus Recognized /

Approval details

CSA

Usegroups	**B**
Nominal voltage UN	150 V
Nominal current IN	6 A
mm²/AWG/kcmil	20

PCB terminal block - FFKDSA1/V-2,54- 2 - 1789618

approvals

UL Recognized

Usegroups	B
Nominal voltage UN	150 V
Nominal current IN	6 A
mm²/AWG/kcmil	26-20

cUL Recognized

Usegroups	B
Nominal voltage UN	150 V
Nominal current IN	6 A
mm²/AWG/kcmil	26-20

cULus Recognized

Drawings

© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com