

# Orthomat ® Diamond Anti-Fatigue



- Manufactured from 100% close cell PVC
- Diamond pattern provides additional underfoot grip
- Designed to offer comfortable underfoot cushioning
- Reduces pressure pain caused by prolonged standing to the feet, legs and back.
- Encourages healthier blood circulation
- Ideal for assembly areas and packing stations

Product Height: 9mm

Mat Size (m.) width x length	Weight Kg.	Packaging Size CM	Packaging Type	Packaging Quantity	Pallet Quantity	Colour	Part Code
0.6 x 0.9	2	17.5 x 17.5 x 75	Boxed	1	42	Black	DAF010001
0.9 x 1.5	5	17.5 x 17.5 x 105	Boxed	1	30	Black	DAF010002
0.9 x 18.3	55	54 x 54 x 100	Boxed	1	4	Black	DAF010003
0.9 x per linear metre	3	3 x 3 x 90	Wrapped	1	N/A	Black	DAF010003C
1.2 x 18.3	70	60 x 60 x 130	Boxed	1	4	Black	DAF010005
1.2 x per linear metre	4	3 x 3 x 120	Wrapped	1	N/A	Black	DAF010005C

## Product Performance

### Slip Resistance Test

DIN 51130: 1992 Testing of floor covering – Determination of slip resistance – Work rooms and areas of work with an increased risk of slipping – Walking method – Ramp test.

Test conducted by a SATRA approved subcontractor under agreement. The test was carried out under UKAS accreditation.

Trial No.	Operator 1 inclined platform shod°	Operator 2 inclined platform shod°
1	22.7	21.5
2	22.8	22.1
3	23.0	22.3
Average	= 22.4°	
Category	= R11	

**Notes:** The Orthomat Diamond Anti Fatigue sample submitted is regarded as suitable for floors in work rooms and work areas where there is an increased risk of slipping due to grease, oil, water, foods, left-overs, dust, flour, plant clippings, etc. It is also suitable for general and private areas when assessed according to DIN 51130.

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that matting products may be subject to a degree of shrinkage when installed into some applications.