

**SECTION 1: Identification of the substance/mixture and of the company/undertaking**

**1.1 Product identifier**

Trade name: ***Marder Duftmarken Entferner***

Article number: Z 101

**1.2 Relevant identified uses of the substance or mixture and uses advised against**

No further relevant information available.

**Sector of Use**

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

SU3 Industrial uses: Uses of substances as such or in preparations at industrial sites

**Product category** PC35 Washing and cleaning products (including solvent based products)

**Application of the substance / the mixture** Cleaning material/ Detergent

**Uses advised against** All other applications which are not explicitly listed.

**1.3 Details of the supplier of the safety data sheet**

**Manufacturer/Supplier:**

Kemo Electronic GmbH

Leher Landstr. 20

27607 Geestland

Deutschland

Tel.: +49 / (0)4743 / 9338-0

Fax: +49 / (0)4743 / 9338-22

eMail: kemo-electronic@t-online.de

www.kemo-electronic.de

**Further information obtainable from:**

Abteilung Produktsicherheit.

Ansprechpartner: Frau Meike Kernchen, Tel.: +49 / (0)4743 9338-0, kemo-electronic@t-online.de

**1.4 Emergency telephone number:**

Beratungsstelle für Vergiftungserscheinungen: D - Berlin, Tel.: +49 / 30 / 19240

**SECTION 2: Hazards identification**

**2.1 Classification of the substance or mixture**

**Classification according to Regulation (EC) No 1272/2008**



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.

**2.2 Label elements**

**Labelling according to Regulation (EC) No 1272/2008**

The product is classified and labelled according to the CLP regulation.

**Hazard pictograms**



GHS07

**Signal word** Warning

**Hazard statements**

H319 Causes serious eye irritation.

(Contd. on page 2)

Trade name: *Marder Duftmarken Entferner*

(Contd. of page 1)

**Precautionary statements**

- P101 If medical advice is needed, have product container or label at hand.
- P102 Keep out of reach of children.
- P103 Read label before use.
- P264 Wash thoroughly after handling.
- P280 Wear eye protection / face protection.
- P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P337+P313 If eye irritation persists: Get medical advice/attention.

**2.3 Other hazards**

The product does not contain any organic halogen compounds (AOX), nitrates, heavy metal compounds or formaldehydes.

**Results of PBT and vPvB assessment**

- PBT:** Not applicable.
- vPvB:** Not applicable.

**SECTION 3: Composition/information on ingredients**

**3.2 Chemical characterisation: Mixtures**

**Description:** Mixture of substances listed below with nonhazardous additions.

**Dangerous components:**

CAS: 67-63-0 EINECS: 200-661-7 Reg.nr.: 01-2119457558-25-xxxx	propan-2-ol Flam. Liq. 2, H225 Eye Irrit. 2, H319; STOT SE 3, H336	10-25%
CAS: 68891-38-3 NLP: 500-234-8 Reg.nr.: 01-2119488639-16	Alcohols, C12-14, ethoxylated, sulfates sodium salt Eye Dam. 1, H318 Skin Irrit. 2, H315 Aquatic Chronic 3, H412	≤ 2.5%
CAS: 112-34-5 EINECS: 203-961-6 Reg.nr.: 01-2119475104-44-xxxx	2-(2-butoxyethoxy)ethanol Eye Irrit. 2, H319	≤ 2.5%
CAS: 1336-21-6 EINECS: 215-647-6	ammonia Skin Corr. 1B, H314 Aquatic Acute 1, H400	≤ 2.5%

**Regulation (EC) No 648/2004 on detergents / Labelling for contents**

anionic surfactants, perfumes, METHYLISOTHIAZOLINONE, BENZISOTHIAZOLINONE	<5%
colouring agent	

**Additional information:** For the wording of the listed hazard phrases refer to section 16.

**SECTION 4: First aid measures**

**4.1 Description of first aid measures**

- General information:** Immediately remove any clothing soiled by the product.
- After inhalation:** Supply fresh air; consult doctor in case of complaints.
- After skin contact:**  
Immediately wash with water and soap and rinse thoroughly.  
If skin irritation continues, consult a doctor.

(Contd. on page 3)

Trade name: *Marder Duftmarken Entferner*

(Contd. of page 2)

- **After eye contact:**  
Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:**  
Do not induce vomiting; call for medical help immediately.  
A person vomiting while laying on their back should be turned onto their side.
- **4.2 Most important symptoms and effects, both acute and delayed**  
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

## SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
  - **Suitable extinguishing agents:**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture**  
No further relevant information available.
- **5.3 Advice for firefighters** Not available.
  - **Protective equipment:**  
Wear self-contained respiratory protective device.  
Do not inhale explosion gases or combustion gases.

## \* SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Wear protective equipment. Keep unprotected persons away.  
Product forms slippery surface when combined with water.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

## \* SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Keep receptacles tightly sealed.
  - **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
  - **Storage:**
    - **Requirements to be met by storerooms and receptacles:**  
Store only in the original receptacle.
    - **Further information about storage conditions:** Keep container tightly sealed.
      - **Recommended storage temperature:** 20 °C

(Contd. on page 4)

Trade name: *Marder Duftmarken Entferner*

(Contd. of page 3)

. **7.3 Specific end use(s)** No further relevant information available.

## SECTION 8: Exposure controls/personal protection

. **Additional information about design of technical facilities:** No further data; see item 7.

### . 8.1 Control parameters

. **Ingredients with limit values that require monitoring at the workplace:**

**CAS: 67-63-0 propan-2-ol (10-25%)**

WEL Short-term value: 1250 mg/m<sup>3</sup>, 500 ppm  
Long-term value: 999 mg/m<sup>3</sup>, 400 ppm

**CAS: 112-34-5 2-(2-butoxyethoxy)ethanol (≤1.0%)**

WEL Short-term value: 101.2 mg/m<sup>3</sup>, 15 ppm  
Long-term value: 67.5 mg/m<sup>3</sup>, 10 ppm

. **Additional information:** The lists valid during the making were used as basis.

### . 8.2 Exposure controls

. **Personal protective equipment:**

. **General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Avoid contact with the eyes and skin.

Do not eat or drink while working.

. **Respiratory protection:**

In case of insufficient ventilation and longer exposure, we recommend a respirator with filter type A.

. **Protection of hands:**

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

. **Material of gloves**

Nitrile rubber.

The gloves should comply with EN 374 and ideally cover the protection class A, J, K, L.

. **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

Nitrile rubber.

The gloves should comply with EN 374 and ideally comply with protection class A, J, K, L.

. **Eye protection:**



Tightly sealed goggles

. **Body protection:** Protective work clothing

GB

(Contd. on page 5)

Trade name: *Marder Duftmarken Entferner*

(Contd. of page 4)

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

#### General Information

##### Appearance:

Form: Fluid

Colour: Red

Odour: Characteristic

Odour threshold: Not determined.

pH-value at 20 °C: 9.5

#### Change in condition

Melting point/freezing point: Undetermined.

Initial boiling point and boiling range: 82 °C

Flash point: >45 °C

Flammability (solid, gas): Not applicable.

Ignition temperature: 425 °C

Decomposition temperature: Not determined.

Auto-ignition temperature: Product is not selfigniting.

Explosive properties: Product does not present an explosion hazard.

#### Explosion limits:

Lower: 2 Vol %

Upper: 12 Vol %

Vapour pressure at 20 °C: 43 hPa

Density at 20 °C: 0.985 g/cm<sup>3</sup>

Relative density: Not determined.

Vapour density: Not determined.

Evaporation rate: Not determined.

#### Solubility in / Miscibility with

water: Fully miscible.

Partition coefficient: n-octanol/water: Not determined.

#### Viscosity:

Dynamic: Not determined.

Kinematic: Not determined.

#### Solvent content:

VOC (EC) 10

### 9.2 Other information

Further flammability test ISO 9038 / according to UN manual (32.5.2): not independently continue burning

## SECTION 10: Stability and reactivity

10.1 Reactivity No further relevant information available.

(Contd. on page 6)

Trade name: *Marder Duftmarken Entferner*

(Contd. of page 5)

- **10.2 Chemical stability**
  - **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

\* **SECTION 11: Toxicological information**

- **11.1 Information on toxicological effects**
  - **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**

CAS: 67-63-0 propan-2-ol

Oral	LD50	5,045 mg/kg (rat)
Dermal	LD50	12,800 mg/kg (rabbit)
Inhalative	LC50/4 h	30 mg/l (rat)

- **Primary irritant effect:**
  - **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
  - **Serious eye damage/irritation**  
Causes serious eye irritation.
- **Respiratory or skin sensitisation**  
Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
  - **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
  - **Carcinogenicity** Based on available data, the classification criteria are not met.
  - **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

\* **SECTION 12: Ecological information**

· **12.1 Toxicity**

· **Aquatic toxicity:**

CAS: 67-63-0 propan-2-ol

EC50 9,640 mg/kg (daphnia) (OECD 202)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
  - **Additional ecological information:**
    - **General notes:**

(Contd. on page 7)

Trade name: **Marder Duftmarken Entferner**

(Contd. of page 6)

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water

Do not allow product to reach ground water, water course or sewage system.

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

· **12.5 Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

· **12.6 Other adverse effects** No further relevant information available.

**SECTION 13: Disposal considerations**

· **13.1 Waste treatment methods**

· **Recommendation**

Small amounts may be diluted with plenty of water and washed away. Dispose of bigger amounts in accordance with Local Authority requirements.

· **European waste catalogue**

20 00 00	MUNICIPAL WASTES (HOUSEHOLD WASTE AND SIMILAR COMMERCIAL, INDUSTRIAL AND INSTITUTIONAL WASTES) INCLUDING SEPARATELY COLLECTED FRACTIONS
20 01 00	separately collected fractions (except 15 01)
20 01 30	detergents other than those mentioned in 20 01 29

· **Uncleaned packaging:**

· **Recommendation:**

Empty contaminated packagings thoroughly. They may be recycled after thorough and proper cleaning.

· **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

**SECTION 14: Transport information**

· **14.1 UN-Number**

· **ADR, ADN, IMDG, IATA** Void

· **14.2 UN proper shipping name**

· **ADR, ADN, IMDG, IATA** Void

· **14.3 Transport hazard class(es)**

· **ADR, ADN, IMDG, IATA**

· **Class** Void

· **14.4 Packing group**

· **ADR, IMDG, IATA** Void

· **14.5 Environmental hazards:**

· **Marine pollutant:** No

(Contd. on page 8)

Trade name: *Marder Duftmarken Entferner*

(Contd. of page 7)

. 14.6 Special precautions for user	Not applicable.
. Stowage Category	A
. 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
. Transport/Additional information:	Further flammability test ISO 9038 / according to UN manual (32.5.2): not independently continue burning
. ADR	
. Remarks:	---
. IATA	
. Remarks:	---
. UN "Model Regulation":	Void

\* **SECTION 15: Regulatory information**

- . 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
  - . Directive 2012/18/EU
    - . Named dangerous substances - ANNEX I None of the ingredients is listed.
    - . REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3
- . 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

\* **SECTION 16: Other information**

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- . **Relevant phrases**
  - H225 Highly flammable liquid and vapour.
  - H314 Causes severe skin burns and eye damage.
  - H315 Causes skin irritation.
  - H318 Causes serious eye damage.
  - H319 Causes serious eye irritation.
  - H336 May cause drowsiness or dizziness.
  - H400 Very toxic to aquatic life.
  - H412 Harmful to aquatic life with long lasting effects.
- . **Department issuing SDS:** Product safety department.
- . **Contact:** Mr. Daniel Gerber
- . **Abbreviations and acronyms:**
  - RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)
  - ICAO: International Civil Aviation Organisation
  - ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
  - IMDG: International Maritime Code for Dangerous Goods
  - IATA: International Air Transport Association
  - GHS: Globally Harmonised System of Classification and Labelling of Chemicals

(Contd. on page 9)



Trade name: **Marder Duftmarken Entferner**

(Contd. of page 8)

EINECS: European Inventory of Existing Commercial Chemical Substances  
ELINCS: European List of Notified Chemical Substances  
CAS: Chemical Abstracts Service (division of the American Chemical Society)  
VOC: Volatile Organic Compounds (USA, EU)  
LC50: Lethal concentration, 50 percent  
LD50: Lethal dose, 50 percent  
PBT: Persistent, Bioaccumulative and Toxic  
vPvB: very Persistent and very Bioaccumulative  
Flam. Liq. 2: Flammable liquids – Category 2  
Skin Corr. 1B: Skin corrosion/irritation – Category 1B  
Skin Irrit. 2: Skin corrosion/irritation – Category 2  
Eye Dam. 1: Serious eye damage/eye irritation – Category 1  
Eye Irrit. 2: Serious eye damage/eye irritation – Category 2  
STOT SE 3: Specific target organ toxicity (single exposure) – Category 3  
Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1  
Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3  
\* **Data compared to the previous version altered.**

GB