

INSTRUCTION ACCUTIRE MS 49 Tire & Tread depth gauge

Measuring Tire pressure

1. Press the "ON" button to activate. If last measurement was tread depth press ON button to change to Tire pressure mode.
2. To change measuring units press and hold ON button for 2 seconds until an Icon blinks, press the "ON" button sequentially until the required icon blinks then release button to capture. Units are set when icon stops blinking.
3. Align the nozzle of the Tire gauge with the valve stem on your Tire.
4. Apply sufficient force to engage the nozzle with stem, while maintaining a proper pressure seal. As you engage the Tire gauge to the valve stem a sudden surge of air will create a crisp Sound.
5. Carefully listen for any leaks, and press firmly on the valve stem to obtain a good seal
6. Hold the Tire gauge on the valve stem until a reading appears on the display and locks. The gauge will shut off automatically.
NOTE. Gauge also can be activated for tire pressure measurement only, by directly pressing gauge nozzle on the Tire pressure valve. After gauge is activated follow points 4-6 above.

Tread depth specification:

- a) Depth <2/32 inch or 1,6 mm, the colour bar is red
- b) 1,6 mm or 2/32 inch < Depth <4/32 inch or 3,2 mm, the colour bar is yellow
- c) Depth >4/32 inch or 3.2 mm the colour bar is green

Tread Depth Measurement

1. Press the ON button to activate
2. If the last measurement was Tire pressure press the ON button to change to tread depth mode.
3. To change units press and hold the ON button for 2 seconds until an Icon blinks. Press the ON button again sequentially until the required icon blinks then release button to capture. Units are set when Icon stops blinking.
4. Hold the gauge against the tread to be measured, and push the slider into the grooved section of the Tire while resting the base section of the gauge housing on the top of the Tire tread until it meets resistance, and then the tread depth reading is displayed.
5. Remove the gauge from the Tire; the gauge LCD display reading will decrease If the user pushes the slider indicator up towards the top.
6. If no additional reading is made, the unit will automatically turn off after a 10 second time out period.

Replacing the battery:

To replace the battery open the battery cover on back of unit and remove the old battery, insert two new CR 2032 batteries, ensuring correct polarity. Replace the battery cover. Use only fresh batteries. Do not mix old and new batteries.

Advice

Always follow the Tire manufacturers' pressure ratings which are based on "cool" Tire temperatures. Use a soft damp cloth to clean your gauge. Do not use any liquids or cleaners. Use a Tire gauge every four weeks and top up with a Tire inflator to reduce fuel consumption, increase Tire life and reduce CO2 emissions.

It is advisable to check the zero set of the gauge from time to time to check the zero set of the gauge.

1. Briefly press the gauge onto the valve stem (If is not necessary for a good seal to be made as only a Small amount of air must enter the gauge to zero Set the unit).
2. When the display shows "0.0" promptly remove the gauge from the valve stem. The gauge has now been recalibrated and is ready for use.

Troubleshooting

If the display is blank: Make sure that the pressure seal between the Tire gauge and the valve stem is free from leaks Check to make sure that there are no leaks in the system. Re-zero the unit by taking a reading and allowing the unit to automatically shut off. Then check the air pressure In the Tire

If the display reads "Lo": The battery is depleted and must be replaced.

Specifications:

Tire pressure range: 5-99psi / 0,35-6,80 bar / 135-680kPa / 0,4-7,00 kg/cm³

Tire pressure resolution: 0,5 psi / 0,05 bar / 5kPa / 0,05 kg/cm³

Accuracy: +1/-1% plus 1 LSD

Tread depth range: 0-15 mm / 0-19/32 inch

Tread depth resolution: 0,1 mm / 1/32 inch

Accuracy: +/-0,2mm / 1/32 inch

Warranty and Service (US only)

Measurement Ltd., Inc warrants this gauge against defects in material of workmanship for a period of live (5) years (US only) from the date of purchase and agrees to replace it free of charge. This warranty does not cover damage resulting from misuse or abuse of the product. Should your gauge require service, you may send it back to Measurement Ltd., Inc for repair or replacement.

Information on Waste Disposal for Consumers of Electrical & Electronic Equipment.

This mark on a product and/or accompanying documents indicates that when it is to be disposed of, it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked waste products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. For proper treatment, recovery and recycling, please take all WEEE marked waste to your Local Authority Civic waste site, where it will be accepted free of Charge If all consumers dispose of Waste Electrical & Electronic Equipment correctly, they will be helping to save valuable resources and preventing any potential negative effects upon human health and the environment, of any hazardous materials that the waste may contain

Please Recycle Your Spent Batteries

Batteries should not be disposed of In unsorted municipal waste, but separately collected to facilitate the correct treatment and recycling of the substances they contain. The recycling of batteries ensures the recovery of these valuable materials and prevents any potentially harmful effects upon both the environment and human health. Please contribute to battery recycling by segregating all spent batteries and actively participating In their collection and recycling. Various battery collection schemes will be in operation In different areas of the country. However, battery collection bins will be available at retail stores that sell batteries as well as at schools, libraries and other public buildings.

Measurement Ltd., Inc. www.measurement-ltd.com Our authorized service center address: 2001 Route 46, Suite 310 Parsippany, NJ 07054 Attn: Customer Service Printed In China Patent Pending