

INTRINSICALLY SAFE



- Approved by global agencies for intrinsically safe lights

IDENTIFIABLE



- Internationally approved orange safety color

WATERPROOF



- Protects interior components from water damage
- IP67

IMPACT RESISTANT



- Survives a 2 meter drop

ECONOMICAL



- Reduced battery consumption for cost savings
- 17 hour run time

MS2ALED

European Region

Approved by global safety agencies, the MS2ALED is ideal for work in harsh conditions. The light is waterproof, dustproof and survives a 2 meter drop test.

A built-in carabiner belt clip allows quick access and the compact size fits easily in any toolbox. Internationally approved, the safety orange color provides instant recognition. The White LED lamp supplies steady, bright illumination.



APPROVED BY:

- UL913 Class I, II and III
- CAN/CSA C22.2 No. 157-92
- IEC 60529 – IP67
- ATEX
- IECEX
- CE 0539 IM2/II1G EEx iaI/IIC T4
- DEMKO 07 ATEX 0618226

Before Using Your Flashlight:


Please read all instructions and cautionary markings on the package and light

European Region

Product Detail:

- Designation:** Energizer 2AA ATEX
- Model:** MS2ALED
- Color:** Safety Orange and Black
- Power Source:** Two "AA"
- ANSI/NEDA:** 15 Series
- Lamp:** Three White Nichia GS LEDs
- Lamp Output Rating:** 30 Lumens
- Runtime:** 17 Hours
- Durability:** Survives 2 meter drop
- Typical Weight:** 66 grams (without batteries)
- Dimensions (mm):** 151.6 x 35.1 x 40.6

Performance:



Important Notice

This datasheet contains information specific to products manufactured at the time of its publication

Contents herein do not constitute a warranty
©Energizer / All Rights Reserved