



# MATERIAL SAFETY DATA SHEET

## 1. Product and Company Identification

**Material name** HP Color LaserJet CB542A Yellow Print Cartridge

**Use of the preparation** This product is a yellow toner preparation that is used in HP Color LaserJet CP1500, CM1300, and CP1200 series printers.

**Version #** 03

**Revision date** 09-12-2008

**Manufacturer information** Hewlett-Packard Company  
11311 Chinden Boulevard  
Boise, ID 83714 USA  
(Direct) 1-503-494-7199  
(Toll-free within the US) 1-800-457-4209

**Hewlett-Packard health effects line**

**(Toll-free within the US)** 1-800-457-4209

**(Direct)** 1-503-494-7199

**General information telephone number**

**HP Customer Care Line** 1-800-474-6836

**(Toll-free)** 1-800-474-6836

**(Direct)** 1-208-323-2551

**Date prepared** Sep 12, 2008

## 2. Hazards Identification

**Acute health effects**

**Skin contact** Unlikely to cause skin irritation.

**Eye contact** May cause transient slight irritation

**Inhalation** Minimal respiratory tract irritation may occur with exposure to large amounts of toner dust. Use of this product as intended does not result in inhalation of excessive amounts of dust.

**Ingestion** Low acute toxicity. Ingestion is a minor route of entry for intended use of this product.

**Potential health effects**

**Routes of exposure** Potential routes of exposure under normal use conditions are skin and eye contact; and inhalation

Ingestion is not expected to be a primary route of exposure for this product under normal use conditions.

**Chronic health effects** Prolonged inhalation of excessive amounts of any dust may cause lung damage. Use of this product as intended does not result in inhalation of excessive amounts of dust.

**Carcinogenicity** None of the ingredients have been classified as carcinogens according to EU, IARC, MAK, NTP, OSHA or ACGIH.

**Other information** This product is not classified as hazardous according to OSHA CFR 1910.1200 or EU Directive 1999/45/EC, as amended.

## 3. Composition / Information on Ingredients

Component/substance	CAS number	% by weight
Styrene acrylate copolymer	Trade Secret	< 85
Wax	Trade Secret	< 10
Pigment	Trade Secret	< 5
Amorphous silica	7631-86-9	< 2



# MATERIAL SAFETY DATA SHEET

---

## 4. First Aid Measures

### First aid procedures

<b>Eye contact</b>	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists, consult a physician.
<b>Skin contact</b>	Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.
<b>Inhalation</b>	Move person to fresh air immediately. If irritation persists, consult a physician.
<b>Ingestion</b>	Rinse mouth out with water. Drink one to two glasses of water. If symptoms occur, consult a physician.

---

## 5. Fire Fighting Measures

<b>Flash point and method</b>	Not applicable
<b>Hazardous combustion products</b>	Carbon monoxide and carbon dioxide.
<b>Flammable properties</b>	Like most organic material in powder form, toner can form explosive dust-air mixtures when finely dispersed in air.
<b>Extinguishing media</b>	
<b>Suitable extinguishing media</b>	CO <sub>2</sub> , water, or dry chemical
<b>Unsuitable extinguishing media</b>	None known.
<b>Unusual fire and explosion hazard</b>	Like most organic material in powder form, toner can form explosive dust-air mixtures when finely dispersed in air.
<b>Protection of firefighters</b>	
<b>Protective equipment and precautions for firefighters</b>	If fire occurs in the printer, treat as an electrical fire.
<b>Special firefighting procedures</b>	None established.

---

## 6. Accidental Release Measures

<b>Personal precautions</b>	Minimize dust generation and accumulation.
<b>Environmental precautions</b>	Do not flush into surface water or sanitary sewer system. See also section 13 Disposal considerations.
<b>Other information</b>	Slowly vacuum or sweep the material into a bag or other sealed container. Clean remainder with a damp cloth or vacuum cleaner. If a vacuum is used, the motor must be rated as dust explosion-proof. Fine powder can form explosive dust-air mixtures. Dispose of in compliance with federal, state, and local regulations.

---

## 7. Handling and Storage

<b>Handling</b>	Keep out of the reach of children. Avoid inhalation of dust and contact with skin and eyes. Use with adequate ventilation. Keep away from excessive heat, sparks, and open flames.
<b>Storage</b>	Keep out of the reach of children. Keep tightly closed and dry. Store away from strong oxidizers. Store at room temperature.

---

## 8. Exposure Controls / Personal Protection

<b>Exposure guidelines</b>	USA OSHA (TWA/PEL): 15 mg/m <sup>3</sup> (Total Dust), 5 mg/m <sup>3</sup> (Respirable Fraction) ACGIH (TWA/TLV): 10 mg/m <sup>3</sup> (Inhalable Particulate), 3 mg/m <sup>3</sup> (Respirable Particulate) Amorphous silica: USA OSHA (TWA/PEL): 20 mppcf 80 (mg/m <sup>3</sup> )/%SiO <sub>2</sub> , ACGIH (TWA/TLV): 10 mg/m <sup>3</sup>
<b>Personal protective equipment</b>	
<b>General</b>	No personal respiratory protective equipment required under normal conditions of use.



# MATERIAL SAFETY DATA SHEET

## 9. Physical & Chemical Properties

Appearance	Fine powder
Color	Yellow
Odor	Slight plastic odor
Odor threshold	Not available.
Physical state	Not available.
Form	solid
pH	Not applicable
Melting point	Not available.
Freezing point	Not available.
Boiling point	Not applicable
Flash point	Not applicable
Evaporation rate	Not applicable
Flammability	Not available.
Flammability limits in air, upper, % by volume	Not available.
Flammability limits in air, lower, % by volume	Not flammable
Vapor pressure	Not applicable
Vapor density	Not applicable
Specific gravity	1 - 1.2 (H <sub>2</sub> O = 1)
Relative density	Not available.
Solubility in water	Negligible in water. Partially soluble in toluene and xylene.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not applicable
Decomposition temperature	Not available.
Softening point	212 - 302 °F (100 - 150 °C)
Viscosity	Not applicable

## 10. Chemical Stability & Reactivity Information

Chemical stability	Stable under normal storage conditions.
Conditions to avoid	Imaging Drum: Exposure to light
Incompatible materials	Strong oxidizers
Hazardous decomposition products	Carbon monoxide and carbon dioxide.
Possibility of hazardous reactions	Will not occur.

## 11. Toxicological Information

Oral toxicity	LD <sub>50</sub> /oral/rat >2000 mg/kg; (OECD 401); Not harmful.. Not classified for acute oral toxicity according to EU Directive 67/548/EEC and 1999/45/EC.
Inhalation toxicity	No information available.  Not classified for acute inhalation toxicity according to EU Directive 67/548/EEC and 1999/45/EC.
Eye irritation	Not classified as irritant, according to OSHA Hazard Communication Standard (HCS) and EU Directive 67/548/EEC and as amended.



# MATERIAL SAFETY DATA SHEET

<b>Sensitization</b>	Not classified as a sensitizer according to EU Directive 67/548/EEC and as amended, and OSHA HCS (US).
<b>Chronic toxicity</b>	No information available.
<b>Carcinogenicity</b>	Not a known or suspected carcinogen according to any IARC Monograph, NTP, OSHA Regulations (USA), EU Directive, or Proposition 65 (California).

## IARC Monographs on Occupational Exposures to Chemical Agents: Evidence of carcinogenicity in humans

Amorphous silica (7631-86-9)

Inadequate data.

## Mutagenicity

Negative, does not indicate mutagenic potential (Ames Test: Salmonella typhimurium)

## Reproductive toxicity

Not classified as toxic according to EU Directive 67/548/EEC and as amended, California Prop. 65, and DFG (Germany).

## Symptoms and target organs

### NIOSH Pocket Guide - Target organs

Amorphous silica (7631-86-9)

Eyes

Amorphous silica (7631-86-9)

Eyes, resp sys

Amorphous silica (7631-86-9)

Respiratory system

---

## 12. Ecological Information

**Ecotoxicity** 96.00 Hours, LL50 > 1000 mg/l, rainbow trout

**Persistence and degradability** Not available.

---

## 13. Disposal Considerations

### Disposal instructions

Do not shred toner cartridge, unless dust-explosion prevention measures are taken. Finely dispersed particles may form explosive mixtures in air. Dispose of in compliance with federal, state, and local regulations.

HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

---

## 14. Transport Information

### IATA

Not regulated as dangerous goods.

---

## 15. Regulatory Information

**US federal regulations** US EPA TSCA Inventory: All chemical substances in this product comply with all rules or orders under TSCA.

### CERCLA (Superfund) reportable quantity

None

### Superfund Amendments and Reauthorization Act of 1986 (SARA)

#### Hazard categories

Immediate Hazard - No  
Delayed Hazard - No  
Fire Hazard - No  
Pressure Hazard - No  
Reactivity Hazard - No

#### Section 302 extremely hazardous substance

No

#### Section 311 hazardous chemical

No

### International regulations

All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.



# MATERIAL SAFETY DATA SHEET

## State regulations

US - Pennsylvania RTK - Hazardous Substances: Listed substance

Amorphous silica (7631-86-9)

Listed.

## 16. Other Information

### HMIS® ratings

Health: 1  
Flammability: 1  
Physical hazard: 0

### NFPA ratings

Health: 1  
Flammability: 1  
Instability: 0

### Issue date

Sep 12 2008 11:06AM

### Revision

3

### Replaces sheet dated

Jun 18 2008 10:00PM

### Disclaimer

This Safety Data Sheet document is provided without charge to customers of Hewlett-Packard Company. Data is the most current known to Hewlett-Packard Company at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

### MSDS sections updated

1. Product and Company Identification: Use of the preparation

### Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds