



SAFETY DATA SHEET

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Identification of the preparation CN054Series

Use of the Substance/Preparation Inkjet printing

Version # 01

Revision date 06-Jan-2012

CAS # Mixture

Company identification Hewlett-Packard GmbH
Herrenberger Str. 140
71034 Böblingen, Deutschland
Telephone 07031 140

Hewlett-Packard health effects line
(Toll-free within the US) 1-800-457-4209
(Direct) 1-503-494-7199
HP Customer Care Line
(Toll-free within the US) 1-800-474-6836
(Direct) 1-208-323-2551
Email: hpcustomer.inquiries@hp.com
Poison Information Centre telephone number +49 089 1 92 40

2. HAZARDS IDENTIFICATION

Emergency Overview Contact with skin and eyes may result in irritation.

Acute health effects

Skin contact Any potential hazards are presumed to be due to exposure to the components.
Avoid contact with skin Contact with skin may result in irritation.
2-pyrrolidone
Contact with skin may result in irritation.
Aliphatic diol
Contact with skin may result in irritation.
Tetraethylene glycol
Contact with skin may result in irritation.

Eye contact *2-pyrrolidone*
Contact with eyes may result in irritation.
Aliphatic diol
Contact with eyes may result in irritation.
Tetraethylene glycol
Contact with eyes may cause irritation.

Inhalation Inhalation may result in respiratory irritation.
2-pyrrolidone
Inhalation may result in respiratory irritation.
Aliphatic diol
Inhalation may result in respiratory irritation.
Tetraethylene glycol
Inhalation may result in respiratory irritation.

Ingestion *2-pyrrolidone*
Ingestion may result in nausea, vomiting and diarrhea.

Potential health effects

Routes of exposure Potential routes of overexposure to this product are skin and eye contact

Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions.

Complete toxicity data are not available for this specific formulation

Chronic health effects None known.

Carcinogenicity

None of the components present in this formulation at concentrations equal to or greater than 0.1% are listed by EU, MAK, IARC, NTP or OSHA.

Classification

Not classified.

Physical hazards

Not classified as a physical hazard.

Health hazards

Not classified as a health hazard.

Environmental hazards

Not classified as an environmental hazard.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Components	CAS #	Percent	EC-No.	Classification
2-pyrrolidone	616-45-5	5 - 7.5	210-483-1	Xi;R36/38
Aliphatic diol	Proprietary	2.5 - 5	Proprietary	
Tetraethylene glycol	112-60-7	2.5 - 5	203-989-9	Xi;R36/37/38
Water	7732-18-5	> 65	231-791-2	

Composition comments

This ink supply contains an aqueous ink formulation.

This product has been evaluated using criteria specified in the EU Directives 67/548/EEC and 1999/45/EC, as amended.

For the full text of the R phrases mentioned in this Section, see Section 16.

4. FIRST AID MEASURES**Inhalation**

Move to fresh air. If symptoms persist, get medical attention.

Skin contact

Wash affected areas thoroughly with mild soap and water. If irritation persists get medical attention.

Eye contact

Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.

Ingestion

If ingestion of a large amount does occur, seek medical attention.

5. FIRE-FIGHTING MEASURES**Flash point**

> 100 °C (> 212 °F) Pensky-Martens Closed Cup US EPA Method 1020

Suitable extinguishing media

For small (incipient) fires, use media such as foam, sand, dry chemical, or carbon dioxide. For large fires use very large (flooding) quantities of water and/or foam, applied as a mist or spray.

Extinguishing media which must not be used for safety reasons

None known.

Unusual fire & explosion hazards

None known.

Specific methods

None established.

Hazardous combustion products

Refer to section 10.

6. ACCIDENTAL RELEASE MEASURES**Personal precautions**

Wear appropriate personal protective equipment.

Environmental precautions

Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

Other information

Soak up with inert absorbent material. Slowly vacuum or sweep the material into a bag or other sealed container. Dispose of in compliance with federal, state, and local regulations. See also section 13 Disposal considerations.

7. HANDLING AND STORAGE**Handling**

Avoid contact with skin, eyes and clothing.

Storage

Keep away from excessive heat or cold. Keep out of the reach of children.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Exposure limit values****Germany****Components**

Tetraethylene glycol (112-60-7)

Type

TWA

Value

1000.0000
mg/m³

Additional exposure data

Exposure limits have not been established for this product.

Exposure controls

Use in a well ventilated area.

Occupational exposure controls

General

Use personal protective equipment to minimize exposure to skin and eye.

Hygiene measures

Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Not available.
Physical state	Liquid
Form	Not available.
Color	Cyan
Odor	Not available.
Odour threshold	Not available.
pH	8.8
Boiling point	Not available.
Flash point	> 100 °C (> 212 °F) Pensky-Martens Closed Cup US EPA Method 1020
Flammability limits in air, upper, % by volume	Not available.
Flammability limits in air, lower, % by volume	Not available.
Vapor pressure	Not available.
Relative density	Not available.
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available
Viscosity	Not available.
Vapor density	Not available.
Evaporation rate	Not available.
Melting point	Not available.
Freezing point	Not available.
Auto-ignition temperature	Not available.
VOC	< 291 g/l

10. STABILITY AND REACTIVITY

Hazardous decomposition products	Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons.
Stability	Stable under recommended storage conditions.
Materials to avoid	Incompatible with strong bases and oxidizing agents.
Hazardous polymerization	Will not occur.

11. TOXICOLOGICAL INFORMATION

Serious eye damage/eye irritation	Not available.
Further information	This ink formulation has not been tested for toxicological effects. Refer to Section 2 for potential health effects and Section 4 for first aide measures.

12. ECOLOGICAL INFORMATION

Ecotoxicity	No information available. This product is highly soluble in water.
Aquatic toxicity	No data available for this product.

13. DISPOSAL CONSIDERATIONS

Disposal instructions	Do not allow this material to drain into sewers/water supplies. Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations. HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit http://www.hp.com/recycle .
------------------------------	---

14. TRANSPORT INFORMATION

Further information	Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.
----------------------------	--

ADR

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

RID

Not regulated as dangerous goods.

15. REGULATORY INFORMATION**Labeling**

Contains 2-pyrrolidone, Aliphatic diol, Tetraethylene glycol, Water

EC Label This product does not require a label according to EU Directive 1999/45/EC.

Regulatory information

All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

Water hazard class

VwVws WGK1

16. OTHER INFORMATION

Wording of the R-phrases in sections 2 and 3 R36/37/38 Irritating to eyes, respiratory system and skin.
R36/38 Irritating to eyes and skin.

Other information This MSDS was prepared in compliance with EU Directive 91/155/EEC as amended by 2001/58/EC.

Disclaimer This Safety Data Sheet document is provided without charge to customers of Hewlett-Packard Company. Data is the most current known to Hewlett-Packard Company at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

Issue date 06-Jan-2012

Manufacturer information Hewlett-Packard Company
3000 Hanover Street
Palo Alto, California 94304-1112 US
(Direct) 1-503-494-7199
(Toll-free within the US) 1-800-457-4209

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-term exposure limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds