

# Basic terminal block - PI-EX-TB/T - 2835927

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ex-basic terminal block, with knife disconnection and integrated temperature measurement of the input terminal blocks for cold point compensation



## Key commercial data

package_quantity	10
GTIN	4017918911805

## Technical data

### Dimensions

Width	12.4 mm
Height	145 mm
Depth	86.5 mm

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

### General

Nominal voltage $U_N$	250 V
Nominal current $I_N$	4 A
Housing insulation material	PBT
Inflammability class according to UL 94	V0
Color	gray
Conformance	CE-compliant
ATEX	# II (1) G [Ex ia] IIC
ATEX	# II (1) D [Ex iaD]
ATEX	# II 3 G Ex nA II T4 X

### Connection data

Connection method	Screw connection
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section solid min.	0.2 mm <sup>2</sup>

# Basic terminal block - PI-EX-TB/T - 2835927

## Technical data

### Connection data

Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Screw thread	M3
Stripping length	12 mm
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Screw thread	M3
Stripping length	12 mm
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

## classifications

### eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27371603
eCl@ss 5.1	27371603
eCl@ss 6.0	27371603
eCl@ss 7.0	27371603
eCl@ss 8.0	27371603

### ETIM

ETIM 2.0	EC000764
ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC001456

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## approvals

# Basic terminal block - PI-EX-TB/T - 2835927

## approvals

### Approval details

ATEX	
Nominal voltage UN	
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	4

GOST	
------	--

### accessories

#### Insulating sleeve

MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH GY - 0201728



#### Screwdriver tools

## Basic terminal block - PI-EX-TB/T - 2835927

### accessories

SZG 0,6X3,5 VDE - 1205121



---

### Terminal marking

ZBFM 6/WH:UNBEDRUCKT - 0803618



---

### Labeled terminal marker

ZBFM 6/WH,LGS:1-100 - 0800284



---

ZBFM 6/WH,LGS:FORTL.ZAHLEN - 0803621



---

### Bridge

FBST 500-PLC RD - 2966786



## Basic terminal block - PI-EX-TB/T - 2835927

### accessories

FBST 500-PLC BU - 2966692



---

FBST 500-PLC GY - 2966838



### accessories

ZBFM 6:SO/CMS - 0803650



---


PI-ATP - 2835969



### Drawings

# Basic terminal block - PI-EX-TB/T - 2835927

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>