


# Safety data sheet

## according to 1907/2006/EC, Article 31

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** CARAMBA Profi High-Performance Graphite Oil (Aerosol)
- **Article number:** 6003071
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**  
No further relevant information available.
- **Application of the substance / the mixture** Penetrating oil
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
CARAMBA CHEMIE GMBH & Co.KG  
Wanheimerstr. 334/336  
47055 DUISBURG  
www.caramba.de
- Tel.: +49(0)203/7786 01
- **Further information obtainable from:**  
Abteilung Produktsicherheit  
Sicherheitsdatenblaetter@caramba.de
- **1.4 Emergency telephone number:** Giftnotruf Berlin +49(0)30 30686 790 Beratung in Deutsch und Englisch

### SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**  
Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.  
Asp. Tox. 1 H304 May be fatal if swallowed and enters airways.
- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**  
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**
- 
- GHS02
- **Signal word** Danger
- **Hazard-determining components of labelling:**  
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics  
Distillates (petroleum), hydrotreated light naphthenic
- **Hazard statements**  
H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.
- **Precautionary statements**  
P101 If medical advice is needed, have product container or label at hand.  
P102 Keep out of reach of children.  
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
P211 Do not spray on an open flame or other ignition source.  
P251 Do not pierce or burn, even after use.  
P261 Avoid breathing spray.  
P271 Use only outdoors or in a well-ventilated area.  
P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.  
P501 Dispose of contents/container in accordance with local/regional/national/international regulations.
- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 11.04.2022

Version number 3 (replaces version 2)

Revision: 11.04.2022

**Trade name: CARAMBA Profi High-Performance Graphite Oil (Aerosol)**

(Contd. of page 1)

· **vPvB:** Not applicable.

### SECTION 3: Composition/information on ingredients

#### · 3.2 Mixtures

· **Description:** Mixture of substances listed below with nonhazardous additions.

#### · **Dangerous components:**

|   |   |         |
|---|---|---------|
| EINECS: 265-149-8<br>Reg.nr.: 01-2119456620-43                    | Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics<br>Asp. Tox. 1, H304, EUH066 | 50-100% |
| CAS: 64742-53-6<br>EINECS: 265-156-6<br>Reg.nr.: 01-2119480375-34 | Distillates (petroleum), hydrotreated light naphthenic<br>Asp. Tox. 1, H304                       | 10-25%  |
| CAS: 106-97-8<br>EINECS: 203-448-7<br>Reg.nr.: 01-2119474691-32   | butane<br>Flam. Gas 1A, H220; Press. Gas (Comp.), H280  | 10-25%  |
| CAS: 74-98-6<br>EINECS: 200-827-9<br>Reg.nr.: 01-2119486944-21    | Propane<br>Flam. Gas 1A, H220; Press. Gas (Liq.), H280  | 2.5-5%  |
| CAS: 124-38-9<br>EINECS: 204-696-9                                | Carbondioxide<br>Press. Gas (Comp.), H280   | 1-2.5%  |

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

### SECTION 4: First aid measures

#### · 4.1 Description of first aid measures

- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:** If symptoms persist consult doctor.

#### · 4.2 Most important symptoms and effects, both acute and delayed

No further relevant information available.

#### · 4.3 Indication of any immediate medical attention and special treatment needed

No further relevant information available.

### SECTION 5: Firefighting measures

#### · 5.1 Extinguishing media

##### · **Suitable extinguishing agents:**

CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

##### · **For safety reasons unsuitable extinguishing agents:** Water with full jet

#### · 5.2 Special hazards arising from the substance or mixture

No further relevant information available.

#### · 5.3 Advice for firefighters

· **Protective equipment:** No special measures required.

### SECTION 6: Accidental release measures

#### · 6.1 Personal precautions, protective equipment and emergency procedures

Wear protective equipment. Keep unprotected persons away.

#### · 6.2 Environmental precautions:

Inform respective authorities in case of seepage into water course or sewage system.

Do not allow to enter sewers/ surface or ground water.

#### · 6.3 Methods and material for containment and cleaning up:

Ensure adequate ventilation.

(Contd. on page 3)

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 11.04.2022

Version number 3 (replaces version 2)

Revision: 11.04.2022

**Trade name: CARAMBA Profi High-Performance Graphite Oil (Aerosol)**

(Contd. of page 2)

- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**  
Ensure good ventilation/exhaustion at the workplace.  
Open and handle receptacle with care.
- **Information about fire - and explosion protection:**  
Keep ignition sources away - Do not smoke.  
Protect against electrostatic charges.  
Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.  
Do not spray onto a naked flame or any incandescent material.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**  
Store in a cool location.  
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**  
Store in cool, dry conditions in well sealed receptacles.  
Protect from heat and direct sunlight.
- **7.3 Specific end use(s)** No further relevant information available.

### SECTION 8: Exposure controls/personal protection

- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**

|  |   |
|--|---|
| <b>106-97-8 butane (10-25%)</b>        |   |
| WEL                                    | Short-term value: 1810 mg/m <sup>3</sup> , 750 ppm<br>Long-term value: 1450 mg/m <sup>3</sup> , 600 ppm<br>Carc (if more than 0.1% of buta-1.3-diene) |
| <b>124-38-9 Carbondioxide (1-2.5%)</b> |   |
| WEL                                    | Short-term value: 27400 mg/m <sup>3</sup> , 15000 ppm<br>Long-term value: 9150 mg/m <sup>3</sup> , 5000 ppm   |

- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Appropriate engineering controls** No further data; see item 7.
- **Individual protection measures, such as personal protective equipment**
- **General protective and hygienic measures:**  
Wash hands before breaks and at the end of work.  
Do not inhale gases / fumes / aerosols.
- **Respiratory protection:** Not required.
- **Hand protection** Solvent resistant gloves
- **Material of gloves** Nitrile rubber, NBR
- **Penetration time of glove material** Value for the permeation: Level ≥ 480 min
- **Eye/face protection** Safety glasses

GB  
(Contd. on page 4)

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 11.04.2022

Version number 3 (replaces version 2)

Revision: 11.04.2022

**Trade name: CARAMBA Profi High-Performance Graphite Oil (Aerosol)**

(Contd. of page 3)

### SECTION 9: Physical and chemical properties

#### · 9.1 Information on basic physical and chemical properties

##### · General Information

|  |                                   |
|--|-----------------------------------|
| · Colour:  | Dark grey                         |
| · Odour:   | Characteristic                    |
| · Odour threshold:   | Not determined.                   |
| · Melting point/freezing point:                            | Undetermined.                     |
| · Boiling point or initial boiling point and boiling range | Not applicable, as aerosol.       |
| · Flammability   | Not applicable.                   |
| · Lower and upper explosion limit                          |                                   |
| · Lower:   | Not determined.                   |
| · Upper:   | Not determined.                   |
| · Flash point:   | -71 °C                            |
| · Auto-ignition temperature:                               | Product is not selfigniting.      |
| · Decomposition temperature:                               | Not determined.                   |
| · pH   | Not determined.                   |
| · Viscosity:   |                                   |
| · Kinematic viscosity                                      | Not determined.                   |
| · Dynamic:   | Not determined.                   |
| · Solubility   |                                   |
| · water:   | Not miscible or difficult to mix. |
| · Partition coefficient n-octanol/water (log value)        | Not determined.                   |
| · Vapour pressure:   | Not determined.                   |
| · Density and/or relative density                          |                                   |
| · Density at 20 °C:  | 0.83 g/cm <sup>3</sup>            |
| · Relative density   | Not determined.                   |
| · Vapour density   | Not determined.                   |

#### · 9.2 Other information

|   |   |
|---|---|
| · Appearance:   |   |
| · Form:   | Aerosol   |
| · Important information on protection of health and environment, and on safety. |   |
| · Explosive properties:   | Product is not explosive. However, formation of explosive air/vapour mixtures are possible. |
| · Change in condition   |   |
| · Evaporation rate  | Not applicable.   |
| · Information with regard to physical hazard classes                            |   |
| · Explosives  | Void  |
| · Flammable gases   | Void  |
| · Aerosols  | Extremely flammable aerosol. Pressurised container: May burst if heated.                    |
| · Oxidising gases   | Void  |
| · Gases under pressure  | Void  |
| · Flammable liquids   | Void  |
| · Flammable solids  | Void  |
| · Self-reactive substances and mixtures   | Void  |
| · Pyrophoric liquids  | Void  |
| · Pyrophoric solids   | Void  |
| · Self-heating substances and mixtures  | Void  |
| · Substances and mixtures, which emit flammable gases in contact with water     | Void  |
| · Oxidising liquids   | Void  |
| · Oxidising solids  | Void  |

(Contd. on page 5)

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 11.04.2022

Version number 3 (replaces version 2)

Revision: 11.04.2022

**Trade name: CARAMBA Profi High-Performance Graphite Oil (Aerosol)**

(Contd. of page 4)

- **Organic peroxides** Void
- **Corrosive to metals** Void
- **Desensitised explosives** Void

### SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

### SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity** Based on available data, the classification criteria are not met.

- **LD/LC50 values relevant for classification:**

**Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics**

|        |      |                       |
|--------|------|-----------------------|
| Oral   | LD50 | >5,000 mg/kg (rat)    |
| Dermal | LD50 | >5,000 mg/kg (rabbit) |

- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard**  
May be fatal if swallowed and enters airways.

### SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Endocrine disrupting properties** For information on endocrine disrupting properties see section 11.
- **12.7 Other adverse effects**
- **Remark:** Harmful to fish
- **Additional ecological information:**
- **General notes:**  
Harmful to aquatic organisms  
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water  
Do not allow product to reach ground water, water course or sewage system.

(Contd. on page 6)

## Safety data sheet

### according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 11.04.2022

Version number 3 (replaces version 2)

Revision: 11.04.2022

**Trade name: CARAMBA Profi High-Performance Graphite Oil (Aerosol)**

Danger to drinking water if even small quantities leak into the ground.

(Contd. of page 5)

### SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**  
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

### SECTION 14: Transport information

- **14.1 UN number or ID number**
- **ADR, IMDG, IATA** UN1950
- **14.2 UN proper shipping name**
- **ADR, IMDG** AEROSOLS
- **IATA** AEROSOLS, flammable
- **14.3 Transport hazard class(es)**
- **ADR**



- **Class** 2 5F Gases.
- **Label** 2.1

- **IMDG, IATA**



- **Class** 2.1 Gases.
- **Label** 2.1
- **14.4 Packing group**
- **ADR, IMDG, IATA** Void
- **14.5 Environmental hazards:**
- **Marine pollutant:** No
- **14.6 Special precautions for user** Warning: Gases.
- **Hazard identification number (Kemler code):** -
- **EMS Number:** F-D,S-U
- **Stowage Code** SW1 Protected from sources of heat.  
SW22 For AEROSOLS with a maximum capacity of 1 litre:  
Category A. For AEROSOLS with a capacity above 1 litre:  
Category B. For WASTE AEROSOLS: Category C, Clear  
of living quarters.
- **Segregation Code** SG69 For AEROSOLS with a maximum capacity of 1 litre:  
Segregation as for class 9. Stow "separated from" class 1  
except for division 1.4.  
For AEROSOLS with a capacity above 1 litre:  
Segregation as for the appropriate subdivision of class 2.  
For WASTE AEROSOLS:  
Segregation as for the appropriate subdivision of class 2.
- **14.7 Maritime transport in bulk according to IMO  
instruments** Not applicable.

(Contd. on page 7)

GB



# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 11.04.2022

Version number 3 (replaces version 2)

Revision: 11.04.2022

**Trade name: CARAMBA Profi High-Performance Graphite Oil (Aerosol)**

(Contd. of page 6)

**· Transport/Additional information:**

- **ADR**
- **Excepted quantities (EQ):** E0
- **Limited quantities (LQ)** 1L
- **Transport category** 2
- **Tunnel restriction code** D
- **UN "Model Regulation":** UN 1950 AEROSOLS, 2.1

### SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**  
Please note TRGS 510.
- **Directive 2012/18/EU**
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

**· Relevant phrases**

- H220 Extremely flammable gas.
- H280 Contains gas under pressure; may explode if heated.
- H304 May be fatal if swallowed and enters airways.
- EUH066 Repeated exposure may cause skin dryness or cracking.

**· Abbreviations and acronyms:**

- ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
- IMDG: International Maritime Code for Dangerous Goods
- IATA: International Air Transport Association
- GHS: Globally Harmonised System of Classification and Labelling of Chemicals
- EINECS: European Inventory of Existing Commercial Chemical Substances
- ELINCS: European List of Notified Chemical Substances
- CAS: Chemical Abstracts Service (division of the American Chemical Society)
- LC50: Lethal concentration, 50 percent
- LD50: Lethal dose, 50 percent
- PBT: Persistent, Bioaccumulative and Toxic
- vPvB: very Persistent and very Bioaccumulative
- Flam. Gas 1A: Flammable gases – Category 1A
- Aerosol 1: Aerosols – Category 1
- Press. Gas (Comp.): Gases under pressure – Compressed gas
- Press. Gas (Liq.): Gases under pressure – Liquefied gas
- Asp. Tox. 1: Aspiration hazard – Category 1

- **\* Data compared to the previous version altered.**