



# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 28.09.2022

Version number 15 (replaces version 14)

Revision: 28.09.2022

**Trade name: CARAMBA Profi High performance silicone spray(Aerosol)**

(Contd. of page 1)

P271 Use only outdoors or in a well-ventilated area.

P302+P352 IF ON SKIN: Wash with plenty of water.

P332+P313 If skin irritation occurs: Get medical advice/attention.

P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Additional information:**

Contains (R)-p-mentha-1,8-diene. May produce an allergic reaction.

· **2.3 Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

### SECTION 3: Composition/information on ingredients

· **3.2 Mixtures**

· **Description:** Mixture of substances listed below with nonhazardous additions.

· **Dangerous components:**

CAS: 64742-49-0 EC number: 931-254-9 Reg.nr.: 01-2119484651-34	Hydrocarbons, C6, isoalkanes, <5% n-hexane Flam. Liq. 2, H225; Asp. Tox. 1, H304; Aquatic Chronic 2, H411; Skin Irrit. 2, H315; STOT SE 3, H336	10-25%
CAS: 106-97-8 EINECS: 203-448-7 Reg.nr.: 01-2119474691-32	butane Flam. Gas 1A, H220; Press. Gas (Comp.), H280	10-25%
CAS: 64742-49-0 EC number: 927-510-4 Reg.nr.: 01-2119475515-33	Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics Flam. Liq. 2, H225; Asp. Tox. 1, H304; Aquatic Chronic 2, H411; Skin Irrit. 2, H315; STOT SE 3, H336	10-25%
CAS: 74-98-6 EINECS: 200-827-9 Reg.nr.: 01-2119486944-21	Propane Flam. Gas 1A, H220; Press. Gas (Liq.), H280	10-25%
CAS: 75-28-5 EINECS: 200-857-2 Reg.nr.: 01-2119485395-27	Isobutane Flam. Gas 1A, H220; Press. Gas (Comp.), H280	1-2.5%
CAS: 110-54-3 EINECS: 203-777-6 Reg.nr.: 01-2119480412-44	n-hexane Flam. Liq. 2, H225; Repr. 2, H361f; STOT RE 2, H373; Asp. Tox. 1, H304; Aquatic Chronic 2, H411; Skin Irrit. 2, H315; STOT SE 3, H336 Specific concentration limit: STOT RE 2; H373: C ≥ 5 %	<1%
CAS: 110-82-7 EINECS: 203-806-2 Reg.nr.: 01-2119463273-41	Cyclohexane Flam. Liq. 2, H225; Asp. Tox. 1, H304; Aquatic Acute 1, H400; Aquatic Chronic 1, H410; Skin Irrit. 2, H315; STOT SE 3, H336	<1%

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

### SECTION 4: First aid measures

· **4.1 Description of first aid measures**

· **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.

· **After skin contact:** Immediately wash with water and soap and rinse thoroughly.

· **After eye contact:** Rinse opened eye for several minutes under running water.

· **After swallowing:** If symptoms persist consult doctor.

· **4.2 Most important symptoms and effects, both acute and delayed**

No further relevant information available.

(Contd. on page 3)

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 28.09.2022

Version number 15 (replaces version 14)

Revision: 28.09.2022

**Trade name: CARAMBA Profi High performance silicone spray(Aerosol)**

(Contd. of page 2)

- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

### SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

### SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:**  
Inform respective authorities in case of seepage into water course or sewage system.  
Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:** Ensure adequate ventilation.
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**  
Ensure good ventilation/exhaustion at the workplace.  
Open and handle receptacle with care.
- **Information about fire - and explosion protection:**  
Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.  
Do not spray onto a naked flame or any incandescent material.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**  
Store in a cool location.  
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Protect from heat and direct sunlight.
- **7.3 Specific end use(s)** No further relevant information available.

### SECTION 8: Exposure controls/personal protection

- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**

**106-97-8 butane (10-25%)**

WEL	Short-term value: 1810 mg/m <sup>3</sup> , 750 ppm Long-term value: 1450 mg/m <sup>3</sup> , 600 ppm Carc (if more than 0.1% of buta-1.3-diene)
-----	---

(Contd. on page 4)

GB

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 28.09.2022

Version number 15 (replaces version 14)

Revision: 28.09.2022

**Trade name: CARAMBA Profi High performance silicone spray(Aerosol)**

(Contd. of page 3)

<b>110-54-3 n-hexane (&lt;1%)</b>	
WEL	Long-term value: 72 mg/m <sup>3</sup> , 20 ppm
<b>110-82-7 Cyclohexane (&lt;1%)</b>	
WEL	Short-term value: 1050 mg/m <sup>3</sup> , 300 ppm Long-term value: 350 mg/m <sup>3</sup> , 100 ppm

- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Appropriate engineering controls** No further data; see item 7.
- **Individual protection measures, such as personal protective equipment**
- **General protective and hygienic measures:**  
Keep away from foodstuffs, beverages and feed.  
Immediately remove all soiled and contaminated clothing  
Wash hands before breaks and at the end of work.  
Do not inhale gases / fumes / aerosols.
- **Respiratory protection:** Not required.
- **Hand protection** Solvent resistant gloves
- **Material of gloves** Nitrile rubber, NBR
- **Penetration time of glove material** Value for the permeation: Level ≥ 480
- **Eye/face protection** Safety glasses

## SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**
- **General Information**
- **Physical state** Aerosol
- **Colour:** Clear
- **Odour:** Fruit-like
- **Odour threshold:** Not determined.
- **Melting point/freezing point:** Undetermined.
- **Boiling point or initial boiling point and boiling range** Not applicable, as aerosol.
- **Flammability** Not applicable.
- **Lower and upper explosion limit**
- **Lower:** Not determined.
- **Upper:** Not determined.
- **Flash point:** -82 °C
- **Decomposition temperature:** Not determined.
- **pH** Not determined.
- **Viscosity:**
- **Kinematic viscosity** Not determined.
- **Dynamic:** Not determined.
- **Solubility**
- **water:** Not miscible or difficult to mix.
- **Partition coefficient n-octanol/water (log value)** Not determined.
- **Vapour pressure:** Not determined.
- **Density and/or relative density**
- **Density at 20 °C:** 0.68 g/cm<sup>3</sup>
- **Relative density** Not determined.
- **Vapour density** Not determined.
- **9.2 Other information**
- **Appearance:**
- **Form:** Aerosol

(Contd. on page 5)

GB

## Safety data sheet

### according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 28.09.2022

Version number 15 (replaces version 14)

Revision: 28.09.2022

**Trade name: CARAMBA Profi High performance silicone spray(Aerosol)**

(Contd. of page 4)

- **Important information on protection of health and environment, and on safety.**
- **Auto-ignition temperature:** Product is not selfigniting.
- **Explosive properties:** Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
- **Change in condition**
- **Evaporation rate** Not applicable.
- **Information with regard to physical hazard classes**
- **Explosives** Void
- **Flammable gases** Void
- **Aerosols**  
Extremely flammable aerosol. Pressurised container: May burst if heated.
- **Oxidising gases** Void
- **Gases under pressure** Void
- **Flammable liquids** Void
- **Flammable solids** Void
- **Self-reactive substances and mixtures** Void
- **Pyrophoric liquids** Void
- **Pyrophoric solids** Void
- **Self-heating substances and mixtures** Void
- **Substances and mixtures, which emit flammable gases in contact with water** Void
- **Oxidising liquids** Void
- **Oxidising solids** Void
- **Organic peroxides** Void
- **Corrosive to metals** Void
- **Desensitised explosives** Void

### SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

### SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**

#### 110-82-7 Cyclohexane

Oral	LD50	12,705 mg/kg (rat)
------	------	--------------------

- **Skin corrosion/irritation**  
Causes skin irritation.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.

(Contd. on page 6)

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 28.09.2022

Version number 15 (replaces version 14)

Revision: 28.09.2022

**Trade name: CARAMBA Profi High performance silicone spray(Aerosol)**

(Contd. of page 5)

- **STOT-single exposure**  
May cause drowsiness or dizziness.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard**  
May be fatal if swallowed and enters airways.

### SECTION 12: Ecological information

#### · 12.1 Toxicity

##### · Aquatic toxicity:

##### **64742-49-0 Hydrocarbons, C6, isoalkanes, <5% n-hexane**

LC50/96 h	18.27 mg/l (Oncorhynchus mykiss)
EC50/48 h	31.9 mg/l (Daphnia Magna)
NOEC/28 d	4.089 mg/l (Oncorhynchus mykiss)
NOEC/21 d	7.138 mg/l (Daphnia Magna)

##### **64742-49-0 Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics**

LC50/96 h	>13.4 mg/l (Oncorhynchus mykiss)
EC50/48 h	3 mg/l (Daphnia Magna)
NOEC/28 d	1.543 mg/l (Oncorhynchus mykiss)
NOEC/21 d	1 mg/l (Daphnia Magna)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Endocrine disrupting properties** For information on endocrine disrupting properties see section 11.
- **12.7 Other adverse effects**
- **Remark:** Toxic for fish
- **Additional ecological information:**
- **General notes:**  
Also poisonous for fish and plankton in water bodies.  
Toxic for aquatic organisms  
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water  
Do not allow product to reach ground water, water course or sewage system.  
Danger to drinking water if even small quantities leak into the ground.

### SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**  
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

### SECTION 14: Transport information

- **14.1 UN number or ID number**
- **ADR, IMDG, IATA** UN1950
- **14.2 UN proper shipping name**
- **ADR** AEROSOLS, ENVIRONMENTALLY HAZARDOUS
- **IMDG** AEROSOLS, MARINE POLLUTANT

(Contd. on page 7)

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 28.09.2022

Version number 15 (replaces version 14)

Revision: 28.09.2022

**Trade name: CARAMBA Profi High performance silicone spray(Aerosol)**

(Contd. of page 6)

· **IATA** AEROSOLS, flammable  
 · **14.3 Transport hazard class(es)**

· **ADR**

· **Class** 2 5F Gases.  
 · **Label** 2.1

· **IMDG**

· **Class** 2.1 Gases.  
 · **Label** 2.1

· **IATA**

· **Class** 2.1 Gases.  
 · **Label** 2.1

· **14.4 Packing group**· **ADR, IMDG, IATA**· **14.5 Environmental hazards:**· **Marine pollutant:**· **Special marking (ADR):**· **14.6 Special precautions for user**· **Hazard identification number (Kemler code):**· **EMS Number:**· **Stowage Code**

Void

Product contains environmentally hazardous substances:

Symbol (fish and tree)

Symbol (fish and tree)

Warning: Gases.

-

F-D,S-U

SW1 Protected from sources of heat.

SW22 For AEROSOLS with a maximum capacity of 1 litre:

Category A. For AEROSOLS with a capacity above 1 litre:

Category B. For WASTE AEROSOLS: Category C, Clear of living quarters.

SG69 For AEROSOLS with a maximum capacity of 1 litre:

Segregation as for class 9. Stow "separated from" class 1 except for division 1.4.

For AEROSOLS with a capacity above 1 litre:

Segregation as for the appropriate subdivision of class 2.

For WASTE AEROSOLS:

Segregation as for the appropriate subdivision of class 2.

· **Segregation Code**· **14.7 Maritime transport in bulk according to IMO instruments**

Not applicable.

· **Transport/Additional information:**· **ADR**· **Excepted quantities (EQ):**

E0

· **Limited quantities (LQ)**

1L

· **Transport category**

2

· **Tunnel restriction code**

D

· **UN "Model Regulation":**

UN 1950 AEROSOLS, 2.1, ENVIRONMENTALLY HAZARDOUS

GB

(Contd. on page 8)

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 28.09.2022

Version number 15 (replaces version 14)

Revision: 28.09.2022

**Trade name: CARAMBA Profi High performance silicone spray(Aerosol)**

(Contd. of page 7)

### SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**  
Please note TRGS 510.
- **Directive 2012/18/EU**
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

*This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.*

- **Relevant phrases**

- H220 Extremely flammable gas.
- H225 Highly flammable liquid and vapour.
- H280 Contains gas under pressure; may explode if heated.
- H304 May be fatal if swallowed and enters airways.
- H315 Causes skin irritation.
- H336 May cause drowsiness or dizziness.
- H361f Suspected of damaging fertility.
- H373 May cause damage to organs through prolonged or repeated exposure.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.
- H411 Toxic to aquatic life with long lasting effects.

- **Abbreviations and acronyms:**

- ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
- IMDG: International Maritime Code for Dangerous Goods
- IATA: International Air Transport Association
- GHS: Globally Harmonised System of Classification and Labelling of Chemicals
- EINECS: European Inventory of Existing Commercial Chemical Substances
- ELINCS: European List of Notified Chemical Substances
- CAS: Chemical Abstracts Service (division of the American Chemical Society)
- LC50: Lethal concentration, 50 percent
- LD50: Lethal dose, 50 percent
- PBT: Persistent, Bioaccumulative and Toxic
- vPvB: very Persistent and very Bioaccumulative
- Flam. Gas 1A: Flammable gases – Category 1A
- Aerosol 1: Aerosols – Category 1
- Press. Gas (Comp.): Gases under pressure – Compressed gas
- Press. Gas (Liq.): Gases under pressure – Liquefied gas
- Flam. Liq. 2: Flammable liquids – Category 2
- Skin Irrit. 2: Skin corrosion/irritation – Category 2
- Repr. 2: Reproductive toxicity – Category 2
- STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
- STOT RE 2: Specific target organ toxicity (repeated exposure) – Category 2
- Asp. Tox. 1: Aspiration hazard – Category 1
- Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1
- Aquatic Chronic 1: Hazardous to the aquatic environment - long-term aquatic hazard – Category 1
- Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

- **\* Data compared to the previous version altered.**