

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 11.09.2015

Version: 4

Revision: 20.05.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name: SONAX Xtreme Glass Clear

Article number: 238241

1.2 Relevant identified uses of the substance or mixture and uses advised against

Sector of Use

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

Product category PC35 Washing and cleaning products (including solvent based products)

Application of the substance / the mixture Car care product

1.3 Details of the supplier of the safety data sheet

Manufacturer/Supplier:

SONAX GmbH

Münchener Straße 75

D-86633 Neuburg (Donau)

Tel.: ++49 (0)8431/53-0

Further information obtainable from:

Product safety

E-mail: erp@sonax.de

Phone: + +49 (0) 8431 53 217

1.4 Emergency telephone number: Emergency Phone Munich Tel.: +49 (0)89 19240

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

The product is not classified according to the CLP regulation.

Classification according to Directive 67/548/EEC or Directive 1999/45/EC Not applicable.

2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008 Void

Hazard pictograms Void

Signal word Void

Hazard statements Void

Precautionary statements P102 Keep out of reach of children.

2.3 Other hazards

Results of PBT and vPvB assessment

PBT: Not applicable.


vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Description: aqueous tenside solution with additives

Dangerous components:

CAS: 64-17-5 EINECS: 200-578-6 Reg.nr.: 01-2119457610-43-XXXX	ethanol  F R11 Flam. Liq. 2, H225; Eye Irrit. 2, H319	20 - <25%
CAS: 107-98-2 EINECS: 203-539-1 Reg.nr.: 01-2119457435-35-xxxx	1-Methoxy-2-propanol R10-67 Flam. Liq. 3, H226; STOT SE 3, H336	5 - <10%
Regulation (EC) No 648/2004 on detergents / Labelling for contents		
anionic surfactants		< 5%
perfumes		

Additional information: For the wording of the listed risk phrases refer to section 16.

GB

(Contd. on page 2)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 11.09.2015

Version: 4

Revision: 20.05.2015

Trade name: SONAX Xtreme Glass Clear

(Contd. of page 1)

SECTION 4: First aid measures**4.1 Description of first aid measures****General information:** No special measures required.**After inhalation:** No special measures required**After skin contact:**

Generally the product does not irritate the skin.

Wash the areas of skin affected with water and a mild detergent.

After eye contact:

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

After swallowing:

Rinse out mouth and then drink plenty of water.

If symptoms persist consult doctor.

4.2 Most important symptoms and effects, both acute and delayed

No further relevant information available.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment in accordance with the doctor's assessment of the patient's condition. Symptomatic treatment.

SECTION 5: Firefighting measures**5.1 Extinguishing media****Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.**5.2 Special hazards arising from the substance or mixture** No further relevant information available.**5.3 Advice for firefighters****Protective equipment:** The normal measures for firefighting are to be taken.**SECTION 6: Accidental release measures****6.1 Personal precautions, protective equipment and emergency procedures** Not required.**6.2 Environmental precautions:**

Do not allow to penetrate the ground/soil.

Do not allow to enter sewers/ surface or ground water.

6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Dispose contaminated material as waste according to item 13.

6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage**7.1 Precautions for safe handling** No special precautions are necessary if used correctly.**Information about fire - and explosion protection:** No special measures required.**7.2 Conditions for safe storage, including any incompatibilities****Storage:****Requirements to be met by storerooms and receptacles:** Prevent any seepage into the ground.**Information about storage in one common storage facility:** Store away from foodstuffs.**Further information about storage conditions:**

Protect from frost.

Recommended storage temperature: 20 °C.

7.3 Specific end use(s) No further relevant information available.

GB

(Contd. on page 3)

Trade name: SONAX Xtreme Glass Clear

(Contd. of page 2)

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Ingredients with limit values that require monitoring at the workplace:

64-17-5 ethanol

WEL (Great Britain) Long-term value: 1920 mg/m³, 1000 ppm

107-98-2 1-Methoxy-2-propanol

WEL (Great Britain) Short-term value: 560 mg/m³, 150 ppm
Long-term value: 375 mg/m³, 100 ppm
Sk

IOELV (EU) Short-term value: 568 mg/m³, 150 ppm
Long-term value: 375 mg/m³, 100 ppm
Skin

DNELs

64-17-5 ethanol

Oral	DNEL	87 mg/kg (consumer) (long-term exposure - systemic effects)
Dermal	DNEL	206 mg/kg bw/day (consumer) (long-term exposure - systemic effects) 343 mg/kg bw/day (worker) (long-term exposure - systemic effects)
Inhalative	DNEL	950 mg/m ³ (consumer) (acute short-term exposure - local effects) 114 mg/m ³ (consumer) (long-term exposure - systemic effects) 1900 mg/m ³ (worker) (acute short-term exposure - local effects) 950 mg/m ³ (worker) (long-term exposure - systemic effects)

107-98-2 1-Methoxy-2-propanol

Oral	DNEL	3.3 mg/kg (consumer) (long-term / systemic effects)
Dermal	DNEL	18.1 mg/kg (consumer) (long-term / systemic effects) 50.6 mg/kg (worker) (long-term / systemic effects)
Inhalative	DNEL	43.9 mg/m ³ (consumer) (long-term / systemic effects) 553.5 mg/m ³ (worker) (short-term / local effects) 369 mg/m ³ (worker) (long-term / systemic effects)

PNECs

64-17-5 ethanol

PNEC 3.6 mg/kg (sediment (fresh water))
2.9 mg/kg (sediment (sea water))
0.63 mg/kg (soil)
0.96 mg/l (water (fresh water))
0.79 mg/l (water (sea water))

107-98-2 1-Methoxy-2-propanol

PNEC 100 mg/l (STP)
2.47 mg/kg (gro)
41.6 mg/kg (sediment (fresh water))
4.17 mg/kg (sediment (sea water))
100 mg/l (water (intermittent release))
10 mg/l (water (fresh water))
1 mg/l (water (sea water))

Additional information: The lists valid during the making were used as basis.

8.2 Exposure controls

Suitable technical control devices

Ensure good ventilation. This can be achieved by localised extraction or general ventilation. If this is not sufficient to keep the concentration below the occupational exposure limit, suitable breathing protection is to be worn.

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 11.09.2015

Version: 4

Revision: 20.05.2015

Trade name: SONAX Xtreme Glass Clear

(Contd. of page 3)

Personal protective equipment:**General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.

Keep away from foodstuffs, beverages and feed.

Wash hands before breaks and at the end of work.

Respiratory protection: Not required in normal cases**Protection of hands:** Not required in normal cases**Eye protection:** Not required in normal cases

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties**General Information****Appearance:**

Form:	Fluid
Colour:	Blue
Odour:	Characteristic
Odour threshold:	Not determined.

pH-value at 20 °C: 8.5 - 9.5**Change in condition**

Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	78 - 120 °C

Flash point: 38 °C (DIN 51755)**Flammability (solid, gaseous):** Not applicable.**Ignition temperature:****Decomposition temperature:** Not determined.**Self-igniting:** Product is not selfigniting.**Danger of explosion:** Product does not present an explosion hazard.**Explosion limits:**

Lower:	Not determined.
Upper:	Not determined.

Vapour pressure: Not determined.**Density at 20 °C:** 0.97 - 0.98 g/cm³**Relative density** Not determined.**Vapour density** Not determined.**Evaporation rate** Not determined.**Solubility in / Miscibility with****water:** Fully miscible.**Partition coefficient (n-octanol/water):** Not determined.**Viscosity:****Flow time at 20 °C** 10 - 15 s (DIN EN ISO 2431/4mm)**Dynamic:** Not determined.**Kinematic:** Not determined.**9.2 Other information** Sustained combustibility test ISO 9038/UN manual of tests and criteria (32.5.2):

no self-sustained combustion

SECTION 10: Stability and reactivity

10.1 Reactivity No dangerous reactions known.**10.2 Chemical stability** Stable under normal conditions.**10.3 Possibility of hazardous reactions** No dangerous reactions known.

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 11.09.2015

Version: 4

Revision: 20.05.2015

Trade name: SONAX Xtreme Glass Clear

(Contd. of page 4)

10.4 Conditions to avoid See Section 7 for information on safe handling.**10.5 Incompatible materials:** strong oxidizing agents**10.6 Hazardous decomposition products:** No dangerous decomposition products known.**SECTION 11: Toxicological information****11.1 Information on toxicological effects** There are no toxicological findings on this mixture.**Acute toxicity****LD/LC50 values relevant for classification:****64-17-5 ethanol**

Oral	LD50	7060 mg/kg (rat)
Dermal	LD50	>2000 mg/kg (rat)
Inhalative	LC50/4h	20000 mg/l (rat)
	LD 50	5560 mg/kg (Gp)
		3450 mg/kg (mouse) 6300 mg/kg (rabbit)

107-98-2 1-Methoxy-2-propanol

Oral	LD50	4016 mg/kg (rat)
Dermal	LD50	>2000 mg/kg (rat)
Inhalative	LC0 / 6h	>7000 ppm (rat)

Primary irritant effect:**Skin corrosion/irritation**

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

Serious eye damage/irritation

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

Respiratory or skin sensitisation

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

Repeated dose toxicity

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

Does not fulfill the criteria for classification

SECTION 12: Ecological information**12.1 Toxicity** There are no ecotoxicological data available on this mixture.**Aquatic toxicity:****64-17-5 ethanol**

EC5 / 16h	6500 mg/l (Pseudomonas putida)
EC50 / 48h	9268 mg/l (Daphnia magna)
LC50 / 24h	>100 mg/l (Daphnia magna)
LC50 / 48h	8140 mg/l (Leuciscus idus)

107-98-2 1-Methoxy-2-propanol

EC50	>1000 mg/l (Pseudokirchneriella subcapitata) (7d)
EC50/3h	>1000 mg/l (Bel) (OECD 209)
LC 50 / 96 h	>6800 mg/l (Leuciscus idus) (DIN38412)
LC50 / 48h	23300 mg/l (Daphnia magna)

12.2 Persistence and degradability**107-98-2 1-Methoxy-2-propanol**

Biodegradation	90 - 100 % (-) (OECD 301E)
----------------	----------------------------

(Contd. on page 6)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 11.09.2015

Version: 4

Revision: 20.05.2015

Trade name: SONAX Xtreme Glass Clear

(Contd. of page 5)

12.3 Bioaccumulative potential**107-98-2 1-Methoxy-2-propanol**

log Kow | -0.43 log Kow (-) (25 °C)

12.4 Mobility in soil No further relevant information available.**Additional ecological information:****General notes:**

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

12.5 Results of PBT and vPvB assessment**PBT:** Not applicable.**vPvB:** Not applicable.**12.6 Other adverse effects** No further relevant information available.**SECTION 13: Disposal considerations****13.1 Waste treatment methods****Recommendation** Waste must be disposed of while observing the local, official regulations.**European waste catalogue**

1) Disposal / product

2) Disposal / contaminated packaging

20 01 30 | detergents other than those mentioned in 20 01 29

15 01 02 | plastic packaging

SECTION 14: Transport information**14.1 UN-Number**

ADR, IMDG, IATA | Void

14.2 UN proper shipping name

ADR, IMDG, IATA | Void

14.3 Transport hazard class(es)

ADR, ADN, IMDG, IATA

Class | Void

14.4 Packing group

ADR, IMDG, IATA | Void

14.5 Environmental hazards:**Marine pollutant:** | No**14.6 Special precautions for user** | Not applicable.**Transport/Additional information:** Sustained combustibility test ISO 9038/UN manual of tests and criteria (32.5.2):
no self-sustained combustion**UN "Model Regulation":** | -**SECTION 15: Regulatory information****15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture****National regulations:****Information about limitation of use:**

Employment restrictions concerning juveniles must be observed.

Employment restrictions concerning pregnant and lactating women must be observed.

15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

GB

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 11.09.2015

Version: 4

Revision: 20.05.2015

Trade name: SONAX Xtreme Glass Clear

(Contd. of page 6)

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

Relevant phrases

H225 Highly flammable liquid and vapour.

H226 Flammable liquid and vapour.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

R10 Flammable.

R11 Highly flammable.

R67 Vapours may cause drowsiness and dizziness.

Abbreviations and acronyms:

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation

NOEL = No Observed Effect Level

NOEC = No Observed Effect Concentration

LC = Lethal Concentration

EC50 = half maximal effective concentration

log POW = Octanol / water partition coefficient

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

DNEL: Derived No-Effect Level (REACH)

PNEC: Predicted No-Effect Concentration (REACH)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

IOELV = indicative occupational exposure limit values

Flam. Liq. 2: Flammable liquids, Hazard Category 2

Flam. Liq. 3: Flammable liquids, Hazard Category 3

Eye Irrit. 2: Serious eye damage/eye irritation, Hazard Category 2

STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3

*** Data compared to the previous version altered.**