



Product Specification

Customer Name:	akasa
Product	USB internal to external adapter
Designed for	
Part No.	EXUSBIE-40
Issue Date	2022/08/09
Spec No.	
Version	V1.2

Customer Approved By	Design	Inspect	Check
	Jenny Liu		

鍊立康科技股份有限公司
新北市三重區新北大道二段260號13樓之5

Akasa (Asia) Corp.

13F-5, No. 260, Sec.2, New Taipei Blvd., Sanchong District, New Taipei City, Taiwan


Tel +886 29996289 fax +886 29996228

sales@akasa.com.tw www.akasa.com.tw

1.0 EXUSBIE-40

	(Item)	(Specification/Condition)
01	Dimensions	400 mm

REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	V1.0	Primary Issue	20100202	
	V1.1	Changed wire specification	20160525	



USB AM(NICKEL PLATED)
BLACK MOLDING

- NOTE:
1. CABLE: UL2725 AL+B(AM)+28#*1P+24#*2C, OD=4.5mm, BLACK COLOR, PVC JACKET.
 2. LENGTH: 400mm(SR-SR)
 3. CONNECTOR: USB AM*1PCS(NICKEL PLATED), PH 2.54mm 5P HOUSING*1PCS
 4. MOLD: BLACK MOLDING/ASSEMBLY
 5. CONTACTS:

P1	1	2	3	4
P2	1	2	3	4 + 64
	RED	WHT	GRN	BLK+GND
		28#		
		28#		
		TP		

6. OPEN/SHORT TEST: 100% TEST.
- INSULATION: MIN. 5M.
7. RoHS: Compliant.

		UNIT: MM	NAME	DATE	Akasa (Asia) Corp
		TOLERANCES: ±0.2mm	BRAUN	2009029	
		FRACTIONAL ±	CHECKED		
		ANGULAR: MACH ±	ENG APPR.		
		TYP PLACE DECIMAL ±	MFG APPR.		EXUSBIE-40
		THREE PLACE DECIMAL ±	O/A		
		MATERIAL	COMMENTS:		
		FINISH			
	NEXT ASSY USED DN				SIZE DWG. NO.
	APPLICATION	DD NOT SCALE DRAWING			SCALE: 1:1
					WEIGHT:
					SHEET 1 OF 1
					REV. V1.1

2.0 Packaging

	(Item)	(Specification/Condition)
01	Dimensions	90 x 190 mm

