



NOTE:

1. CABLE: 30AWG, NON-UL, AL-FOIL, 9C+1, BEIGE COLOR, OD=5.0mm. PVC JACKET.
2. LENGTH: 5000mm
3. CONNECTOR: ⌀ DB9M *1, Ⓞ DB9F*1
4. MOLD: APPLE MOLD
5. SCREW: 4*40 INCH *4
6. CONTACTS:

DB9M	1	2	3	4	5	6	7	8	9	64
DB9F	1	2	3	4	5	6	7	8	9	64
7. OPEN/SHORT TEST: 100% TEST.
INSULATION: 1M.

		APPD.	REVD.
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE:		CUSTOMER.	CHKD.
		SCALE. /	UNIT. mm
			DR.
		TITLE. 304368-ICG-1	13/04/06
		BARCODE NO.	SIZE. A4
		FILE NAME:	SHEET 1 / 1 REV. A