



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 08.11.2018

Version number 13

Revision: 08.11.2018

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** Lötfett
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
- **Technical function** soldering
- **Application of the substance / the mixture** Soldering flux
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Stannol GmbH & Co. KG
Haberstrasse 24
D-42551 Velbert

+49 (0) 2051 3120 332
sdb@stannol.de
- **Further information obtainable from:** Product Safety Department
- **1.4 Emergency telephone number:** 8:00 am - 5:00 pm (CET) +49 (0) 2051 3120 332

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
Skin Irrit. 2 H315 Causes skin irritation.
Eye Dam. 1 H318 Causes serious eye damage.
Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.
- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**



GHS05 GHS09

- **Signal word** Danger
- **Hazard-determining components of labelling:**
zinc chloride
- **Hazard statements**
H315 Causes skin irritation.
H318 Causes serious eye damage.
H411 Toxic to aquatic life with long lasting effects.
- **Precautionary statements**
P102 Keep out of reach of children.
P273 Avoid release to the environment.
P280 Wear protective gloves/protective clothing/eye protection/face protection.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310 Immediately call a doctor.
P391 Collect spillage.
P501 Dispose of contents/container in accordance with local/regional/national/international regulations.
- **2.3 Other hazards**
Flux / flux gels:
Inhalation of vapors released during the soldering process should be avoided. Flux vapors irritate the nose, throat, and respiratory tract, and can lead to allergic reactions (asthma) after prolonged or repeated contact. Therefore, an active suction is recommended.
After working with the product and before eating, drinking or smoking, wash your hands with soap and water.
Keep out of the reach of children.



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 08.11.2018

Version number 13

Revision: 08.11.2018

Trade name: Löt fett

(Contd. of page 1)

- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

· 3.2 Mixtures

- **Description:** Mixture of substances listed below with nonhazardous additions.

· **Dangerous components:**

CAS: 7646-85-7	zinc chloride	2-9%
EINECS: 231-592-0	Skin Corr. 1B, H314; Aquatic Acute 1, H400; Aquatic Chronic 1, H410; Acute Tox. 4, H302; STOT SE 3, H335	
CAS: 8009-03-8	Petrolatum	60-95%
EINECS: 232-373-2		
CAS: 101316-72-7	Lubricating oils (petroleum), C24-50, solvent-extd., dewaxed, hydrogenated	10-35%
EC number: 309-877-7		

· **Additional information:**

- Nota N, R45 applies to CAS 8009-03-8
- Nota L, R45 applies to CAS 101316-72-7
- For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· 4.1 Description of first aid measures

- **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Ensure adequate ventilation
Wear protective clothing.
- **6.2 Environmental precautions:**
Do not allow product to reach sewage system or any water course.
Inform respective authorities in case of seepage into water course or sewage system.
Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Use neutralising agent.
Dispose contaminated material as waste according to item 13.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.

(Contd. on page 3)
GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 08.11.2018

Version number 13

Revision: 08.11.2018

Trade name: Löffett

(Contd. of page 2)

See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Thorough dedusting.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
- **CAS: 7646-85-7 zinc chloride**
- WEL (Great Britain) Short-term value: 2 mg/m³
Long-term value: 1 mg/m³
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing
Wash hands before breaks and at the end of work.
Avoid contact with the skin.
Avoid contact with the eyes and skin.
- **Respiratory protection:**
Not necessary if room is well-ventilated.
Use suitable respiratory protective device in case of insufficient ventilation.
- **Protection of hands:**



Protective gloves

Rubber gloves

Synthetic rubber gloves

To avoid skin problems reduce the wearing of gloves to the required minimum.

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

(Contd. on page 4)

GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 08.11.2018

Version number 13

Revision: 08.11.2018

Trade name: Lötfett

(Contd. of page 3)

- **Eye protection:** Safety glasses

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Appearance:

Form:	Solid
Colour:	According to product specification
· Odour:	Characteristic
· Odour threshold:	Not determined.

· pH-value: Not applicable.

· Change in condition

Melting point/freezing point:	Undetermined.
Initial boiling point and boiling range:	Undetermined.

· Flash point: Not applicable.

· Flammability (solid, gas): Not determined.
Not applicable.

· Decomposition temperature: Not determined.

· Auto-ignition temperature: Product is not selfigniting.

· Explosive properties: Product does not present an explosion hazard.

· Explosion limits:

Lower:	Not determined.
Upper:	Not determined.

· Vapour pressure: Not applicable.

· Density: Not determined.

· Relative density: Not determined.

· Vapour density: Not applicable.

· Evaporation rate: Not applicable.

· Solubility in / Miscibility with water:

Soluble.

· Partition coefficient: n-octanol/water: Not determined.

· Viscosity:

Dynamic:	Not applicable.
Kinematic:	Not applicable.

· Solvent content:

Water:	4.0 %
VOC (EC)	0.00 %

· 9.2 Other information: No further relevant information available.

SECTION 10: Stability and reactivity

· 10.1 Reactivity: No further relevant information available.

· 10.2 Chemical stability

· Thermal decomposition / conditions to be avoided: No decomposition if used according to specifications.

· 10.3 Possibility of hazardous reactions: No dangerous reactions known.

· 10.4 Conditions to avoid: No further relevant information available.

· 10.5 Incompatible materials: No further relevant information available.

(Contd. on page 5)
GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 08.11.2018

Version number 13

Revision: 08.11.2018

Trade name: Löffett

(Contd. of page 4)

- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **LD/LC50 values relevant for classification:**
 - **CAS: 7646-85-7 zinc chloride**
 - Oral LD50 350 mg/kg (rat)
- **Primary irritant effect:**
- **Skin corrosion/irritation**
Causes skin irritation.
- **Serious eye damage/irritation**
Causes serious eye damage.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Toxic for fish
- **Additional ecological information:**
- **General notes:**
Water hazard class 3 (German Regulation) (Self-assessment): extremely hazardous for water
Do not allow product to reach ground water, water course or sewage system, even in small quantities.
Must not reach sewage water or drainage ditch undiluted or unneutralised.
Danger to drinking water if even extremely small quantities leak into the ground.
Also poisonous for fish and plankton in water bodies.
Toxic for aquatic organisms
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

(Contd. on page 6)
GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 08.11.2018

Version number 13


Revision: 08.11.2018

Trade name: Löt fett

(Contd. of page 5)

- **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

SECTION 14: Transport information

- **14.1 UN-Number**
- **ADR, IMDG, IATA** UN3077
- **14.2 UN proper shipping name**
- **ADR** 3077 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (ZINC CHLORIDE)
- **IMDG** ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (ZINC CHLORIDE), MARINE POLLUTANT
- **IATA** ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (ZINC CHLORIDE)
- **14.3 Transport hazard class(es)**
- **ADR, IMDG, IATA**
- 
- **Class** 9 Miscellaneous dangerous substances and articles.
- **Label** 9
- **14.4 Packing group**
- **ADR, IMDG, IATA** III
- **14.5 Environmental hazards:**
- **Marine pollutant:** Product contains environmentally hazardous substances: zinc chloride
- **Special marking (ADR):** Symbol (fish and tree)
- **Special marking (IATA):** Symbol (fish and tree)
- **14.6 Special precautions for user** Warning: Miscellaneous dangerous substances and articles.
- **Danger code (Kemler):** 90
- **EMS Number:** F-A,S-F
- **Segregation groups** Acids
- **Stowage Category** A
- **Stowage Code** SW23 When transported in BK3 bulk container, see 7.6.2.12 and 7.7.3.9.
- **14.7 Transport in bulk according to Annex II of Marpol and the IBC Code** Not applicable.
- **Transport/Additional information:**
- **ADR**
- **Limited quantities (LQ)** 5 kg
- **Excepted quantities (EQ)** Code: E1
Maximum net quantity per inner packaging: 30 g
Maximum net quantity per outer packaging: 1000 g
- **Transport category** 3
- **Tunnel restriction code** E
- **IMDG**
- **Limited quantities (LQ)** 5 kg

(Contd. on page 7)
GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 08.11.2018

Version number 13

Revision: 08.11.2018

Trade name: Lötfett

(Contd. of page 6)

- **Excepted quantities (EQ)** Code: E1
Maximum net quantity per inner packaging: 30 g
Maximum net quantity per outer packaging: 1000 g
- **UN "Model Regulation":** UN 3077 ENVIRONMENTALLY HAZARDOUS
SUBSTANCE, SOLID, N.O.S. (ZINC CHLORIDE), 9, III

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **Seveso category E2** Hazardous to the Aquatic Environment
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 200 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
H302 Harmful if swallowed.
H314 Causes severe skin burns and eye damage.
H335 May cause respiratory irritation.
H400 Very toxic to aquatic life.
H410 Very toxic to aquatic life with long lasting effects.
- **Department issuing SDS:** Product Safety Department
- **Contact:** Hr. Dörr
- **Abbreviations and acronyms:**
ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
VOC: Volatile Organic Compounds (USA, EU)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
Acute Tox. 4: Acute toxicity – Category 4
Skin Corr. 1B: Skin corrosion/irritation – Category 1B
Skin Irrit. 2: Skin corrosion/irritation – Category 2
Eye Dam. 1: Serious eye damage/eye irritation – Category 1
STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1
Aquatic Chronic 1: Hazardous to the aquatic environment - long-term aquatic hazard – Category 1
Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2