



SAFETY DATA SHEET

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture QUICKLEEN PLUS IND

Synonyms None.

Product code BDS001716

Issue date 07-September-2020

Version number 01

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaners - Heavy duty

Uses advised against None known.

1.3. Details of the supplier of the safety data sheet

Company name CRC Industries Europe bvba

Address Touwslagerstraat 1
9240 Zele
Belgium

Telephone +32(0)52/45.60.11

Fax +32(0)52/45.00.34

E-mail hse@crcind.com

Website www.crcind.com

1.4. Emergency telephone number Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

Physical hazards

Aerosols	Category 1	H222 - Extremely flammable aerosol. H229 - Pressurized container: May burst if heated.
----------	------------	---

Health hazards

Specific target organ toxicity - single exposure	Category 3 narcotic effects	H336 - May cause drowsiness or dizziness.
--	-----------------------------	---

Environmental hazards

Hazardous to the aquatic environment, long-term aquatic hazard	Category 3	H412 - Harmful to aquatic life with long lasting effects.
--	------------	---

Hazard summary

Aerosol CONTENTS UNDER PRESSURE.
Pressurised container may explode when exposed to heat or flame. May cause drowsiness or dizziness. Dangerous for the environment if discharged into watercourses. Occupational exposure to the substance or mixture may cause adverse health effects.

2.2. Label elements

Label according to Regulation (EC) No. 1272/2008 as amended

Contains: 1-METHOXY-2-PROPANOL; MONOPROPYLENE GLYCOL METHYL ETHER, Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, < 2% aromatics

Hazard pictograms



Signal word Danger

Hazard statements

H222 Extremely flammable aerosol.

H229 Pressurized container: May burst if heated.
H336 May cause drowsiness or dizziness.
H412 Harmful to aquatic life with long lasting effects.

Precautionary statements

Prevention

P102 Keep out of reach of children.
P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P211 Do not spray on an open flame or other ignition source.
P251 Pressurised container: Do not pierce or burn, even after use.
P261 Avoid breathing mist/vapours.
P271 Use only outdoors or in a well-ventilated area.

Response

Not available.

Storage

P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Disposal

P501 Dispose of contents/container (in accordance with related regulations).

Supplemental label information

EUH066 - Repeated exposure may cause skin dryness or cracking.
According to Regulation (EC) No. 648/2004 on Detergents, as amended; Contains: Limonene.
aliphatic hydrocarbons > 30 %

Perfumes

2.3. Other hazards

This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General information

Chemical name	%	CAS-No. / EC No.	REACH Registration No.	Index No.	Notes
Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, < 2% aromatics	75 - 100	EC927-241-2	01-2119471843-32-0000	-	
Classification: Flam. Liq. 3;H226, Asp. Tox. 1;H304, STOT SE 3;H336, Aquatic Chronic 3;H412					
1-METHOXY-2-PROPANOL; MONOPROPYLENE GLYCOL METHYL ETHER	5 - 10	107-98-2 203-539-1	01-2119457435-35	603-064-00-3	#
Classification: Flam. Liq. 3;H226, STOT SE 3;H336					
Carbon dioxide	1 - 5	124-38-9 204-696-9	Exempt	-	#
Classification: Press. Gas;H280					

List of abbreviations and symbols that may be used above

#: This substance has been assigned Union workplace exposure limit(s).
M: M-factor
PBT: persistent, bioaccumulative and toxic substance.
vPvB: very persistent and very bioaccumulative substance.
All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

Composition comments The full text for all H-statements is displayed in section 16.

SECTION 4: First aid measures

General information

Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

4.1. Description of first aid measures

Inhalation

Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a poison centre or doctor/physician if you feel unwell.

Skin contact

Wash off with soap and water. Get medical attention if irritation develops and persists.

Eye contact

Rinse with water. Get medical attention if irritation develops and persists.

Ingestion

In the unlikely event of swallowing contact a physician or poison control centre.

4.2. Most important symptoms and effects, both acute and delayed

May cause drowsiness or dizziness. Headache. Nausea, vomiting.

4.3. Indication of any immediate medical attention and special treatment needed

Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.

SECTION 5: Firefighting measures

General fire hazards	Extremely flammable aerosol.
5.1. Extinguishing media	
Suitable extinguishing media	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
5.2. Special hazards arising from the substance or mixture	Contents under pressure. Pressurised container may explode when exposed to heat or flame. During fire, gases hazardous to health may be formed.
5.3. Advice for firefighters	
Special protective equipment for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Special fire fighting procedures	Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapour pressure build up. For massive fire in cargo area, use unmanned hose holder or monitor nozzles, if possible. If not, withdraw and let fire burn out.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials. In the event of fire and/or explosion do not breathe fumes.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures	
For non-emergency personnel	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Avoid breathing mist/vapours. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
For emergency responders	Keep unnecessary personnel away. Use personal protection recommended in Section 8 of the SDS.
6.2. Environmental precautions	Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.
6.3. Methods and material for containment and cleaning up	Stop leak if you can do so without risk. Move the cylinder to a safe and open area if the leak is irreparable. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil etc) away from spilled material. The product is immiscible with water and will spread on the water surface. Prevent product from entering drains. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.
6.4. Reference to other sections	For personal protection, see section 8 of the SDS. For waste disposal, see section 13 of the SDS.

SECTION 7: Handling and storage

7.1. Precautions for safe handling	Pressurised container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. All equipment used when handling the product must be grounded. Do not re-use empty containers. Avoid breathing mist/vapours. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices.
7.2. Conditions for safe storage, including any incompatibilities	Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store away from incompatible materials (see Section 10 of the SDS).
7.3. Specific end use(s)	Not available.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

UK. EH40 Workplace Exposure Limits (WELs)

Components	Type	Value
1-METHOXY-2-PROPANOL ; MONOPROPYLENE GLYCOL METHYL ETHER (CAS 107-98-2)	STEL	560 mg/m3

UK. EH40 Workplace Exposure Limits (WELs)

Components	Type	Value
Carbon dioxide (CAS 124-38-9)		150 ppm
	TWA	375 mg/m ³
		100 ppm
	STEL	27400 mg/m ³
	TWA	15000 ppm
		9150 mg/m ³
		5000 ppm

EU. Indicative Exposure Limit Values in Directives 91/322/EEC, 2000/39/EC, 2006/15/EC, 2009/161/EU, 2017/164/EU

Components	Type	Value
1-METHOXY-2-PROPANOL ; MONOPROPYLENE GLYCOL METHYL ETHER (CAS 107-98-2)	STEL	568 mg/m ³
		150 ppm
	TWA	375 mg/m ³
Carbon dioxide (CAS 124-38-9)		100 ppm
	TWA	9000 mg/m ³
		5000 ppm

Biological limit values No biological exposure limits noted for the ingredient(s).

Recommended monitoring procedures Follow standard monitoring procedures.

Derived no effect levels (DNELs)**General Population**

Components	Value	Assessment factor	Notes
1-METHOXY-2-PROPANOL; MONOPROPYLENE GLYCOL METHYL ETHER (CAS 107-98-2)			
Long-term, Systemic, Dermal	78 mg/kg bw/day	16.8	Repeated dose toxicity
Long-term, Systemic, Inhalation	43.9 mg/m ³		Repeated dose toxicity
Long-term, Systemic, Oral	33 mg/kg bw/day	28	Repeated dose toxicity

Workers

Components	Value	Assessment factor	Notes
1-METHOXY-2-PROPANOL; MONOPROPYLENE GLYCOL METHYL ETHER (CAS 107-98-2)			
Long-term, Systemic, Dermal	183 mg/kg bw/day	10.08	Repeated dose toxicity
Long-term, Systemic, Inhalation	369 mg/m ³		Repeated dose toxicity
Short-term, Local, Inhalation	553.5 mg/m ³		Neurotoxicity
Short-term, Systemic, Inhalation	553.5 mg/m ³		Neurotoxicity

Predicted no effect concentrations (PNECs)

Components	Value	Assessment factor	Notes
1-METHOXY-2-PROPANOL; MONOPROPYLENE GLYCOL METHYL ETHER (CAS 107-98-2)			
Freshwater	10 mg/l	100	
Intermittent releases	100 mg/l	10	
Marine water	1 mg/l	1000	
Sediment (freshwater)	52.3 mg/kg		
Sediment (marine water)	5.2 mg/kg		
Soil	4.59 mg/kg		
STP	100 mg/l	10	

Exposure guidelines**UK EH40 WEL: Skin designation**

1-METHOXY-2-PROPANOL; MONOPROPYLENE GLYCOL METHYL ETHER (CAS 107-98-2) Can be absorbed through the skin.

8.2. Exposure controls

Appropriate engineering controls Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

General information	Use personal protective equipment as required. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.
Eye/face protection	Use eye protection conforming to EN 166.
Skin protection	
- Hand protection	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through. Suitable gloves can be recommended by the glove supplier. Full contact: Glove material: nitrile. Use gloves with breakthrough time of 480 minutes. Minimum glove thickness 0.38 mm.
- Other	Not available.
Respiratory protection	Chemical respirator with organic vapour cartridge and full facepiece. (Filter type A)
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
Hygiene measures	When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.
Environmental exposure controls	Inform appropriate managerial or supervisory personnel of all environmental releases. Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. Fume scrubbers, filters or engineering modifications to the process equipment may be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state	Liquid.
Form	Aerosol
Colour	Colourless.
Odour	Characteristic odor.
Odour threshold	Not available.
pH	Not applicable.
Melting point/freezing point	-95 °C (-139 °F) estimated
Initial boiling point and boiling range	Not available.
Flash point	29.0 °C (84.2 °F) Closed cup
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	0.77 g/cm ³
Relative density temperature	20 °C (68 °F)
Solubility(ies)	
Solubility (water)	Insoluble in water
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.

9.2. Other information

Chemical family	Cleaner
------------------------	---------

VOC

750 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
10.4. Conditions to avoid	Avoid high temperatures. Avoid temperatures exceeding the decomposition temperature.
10.5. Incompatible materials	Strong acids.
10.6. Hazardous decomposition products	Carbon oxides.

SECTION 11: Toxicological information

General information Occupational exposure to the substance or mixture may cause adverse effects.

Information on likely routes of exposure

Inhalation	May cause drowsiness or dizziness. Headache. Nausea, vomiting. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Prolonged inhalation may be harmful.
Skin contact	May cause an allergic skin reaction.
Eye contact	Based on available data, the classification criteria are not met.
Ingestion	May cause discomfort if swallowed. However, ingestion is not likely to be a primary route of occupational exposure.

Symptoms May cause drowsiness or dizziness. Headache. Nausea, vomiting.

11.1. Information on toxicological effects

Acute toxicity	Based on available data, the classification criteria are not met.
Skin corrosion/irritation	Based on available data, the classification criteria are not met.
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met.
Respiratory sensitisation	Based on available data, the classification criteria are not met.
Skin sensitisation	Based on available data, the classification criteria are not met.
Germ cell mutagenicity	Based on available data, the classification criteria are not met.
Carcinogenicity	Based on available data, the classification criteria are not met.
Reproductive toxicity	Based on available data, the classification criteria are not met.
Specific target organ toxicity - single exposure	May cause drowsiness or dizziness.
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.
Aspiration hazard	Based on available data, the classification criteria are not met.
Mixture versus substance information	Not available.
Other information	May cause allergic respiratory and skin reactions.

SECTION 12: Ecological information

12.1. Toxicity	Harmful to aquatic life with long lasting effects.
12.2. Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.
12.3. Bioaccumulative potential	
Partition coefficient n-octanol/water (log Kow)	
Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, < 2% aromatics	> 4
Bioconcentration factor (BCF)	Not available.
12.4. Mobility in soil	No data available.
12.5. Results of PBT and vPvB assessment	This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.
12.6. Other adverse effects	The product contains volatile organic compounds which have a photochemical ozone creation potential.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.
EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.
Special precautions	Dispose in accordance with all applicable regulations.

SECTION 14: Transport information

ADR

14.1. UN number	UN1950
14.2. UN proper shipping name	AEROSOLS
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Hazard No. (ADR)	Not available.
Tunnel restriction code	(D)
ADR/RID - Classification code:	5F
14.4. Packing group	Not applicable
14.5. Environmental hazards	No
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

IATA

14.1. UN number	UN1950
14.2. UN proper shipping name	AEROSOLS
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
14.4. Packing group	Not applicable
14.5. Environmental hazards	No
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

IMDG

14.1. UN number	UN1950
14.2. UN proper shipping name	AEROSOLS
14.3. Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
14.4. Packing group	Not applicable
14.5. Environmental hazards	
Marine pollutant	No
EmS	F-D,S-U
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not established.



SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulations

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended

Not listed.

Regulation (EU) 2019/1021 On persistent organic pollutants (recast), as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended

Not listed.

Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry, as amended

Carbon dioxide (CAS 124-38-9)

Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA

Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended

Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended

Not listed.

Directive 2004/37/EC: on the protection of workers from the risks related to exposure to carcinogens and mutagens at work, as amended.

Not listed.

Other EU regulations

Directive 2012/18/EU on major accident hazards involving dangerous substances, as amended

1-METHOXY-2-PROPANOL; MONOPROPYLENE GLYCOL METHYL ETHER (CAS 107-98-2)

Other regulations

The product is classified and labelled in accordance with Regulation (EC) 1272/2008 (CLP Regulation) as amended. This Safety Data Sheet complies with the requirements of Regulation (EC) No 1907/2006, as amended.

National regulations

Follow national regulation for work with chemical agents in accordance with Directive 98/24/EC, as amended.

15.2. Chemical safety assessment

No Chemical Safety Assessment has been carried out.

SECTION 16: Other information

List of abbreviations

ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways.

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.

ADR: European Agreement Concerning the International Carriage of Dangerous Goods by Road.

ATE: Acute Toxicity Estimate according to REGULATION (EC) No 1272/2008 (CLP).

CAS: Chemical Abstract Service.

Ceiling: Short Term Exposure Limit Ceiling value.

CEN: European Committee for Standardization.

CLP: Classification, Labeling and Packaging REGULATION (EC) No 1272/2008 on classification, labeling and packaging of substances and mixtures.

GWP: Global Warming Potential.
IATA: International Air Transport Association.
IBC: Intermediate Bulk Container.
IMDG: International Maritime Dangerous Goods.
MAK: Threshold limit values Germany (Maximale Arbeitsplatzkonzentration - DFG).
MARPOL: International Convention for the Prevention of Pollution from Ships.
PBT: Persistent, bioaccumulative, toxic.
REACH: Registration, Evaluation and Authorization of Chemicals (REGULATION (EC) No 1907/2006 concerning Registration, Evaluation Authorization and Restriction of Chemicals).
RID: Regulations concerning the international carriage of dangerous goods by rail (Règlement International concernant le transport de marchandises dangereuses par chemin de fer).
RID: Regulations concerning the International Carriage of Dangerous Goods by Rail.
STEL: Short term exposure limit.
TLV: Threshold Limit Value.
TWA: Time Weighted Average.
VOC: Volatile organic compounds.
vPvB: Very persistent and very bioaccumulative.
STEL: Short-term Exposure Limit.

References

Information on evaluation method leading to the classification of mixture

Not available.

The classification for health and environmental hazards is derived by a combination of calculation methods and test data, if available.

Full text of any H-statements not written out in full under Sections 2 to 15

H226 Flammable liquid and vapour.
H280 Contains gas under pressure; may explode if heated.
H304 May be fatal if swallowed and enters airways.
H336 May cause drowsiness or dizziness.
H412 Harmful to aquatic life with long lasting effects.

Revision information

None.

Training information

Follow training instructions when handling this material.

Disclaimer

CRC Industries Europe bvba cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available.