


ENERGIZER CR2032

Lithium Coin



Industry Standard Dimensions

mm (inches)




Simulated Application test

Typical Performance at 21°C (70°F)

Schedule:	Typical Drains:	Load	Cutoff
	at 2.9V (mA)	(ohms)	2.0V (hours)
Continuous	0.19	15,000	1235

Continuous Discharge Characteristics

Load: 15K ohms - continuous 21°C (70°F)
Typical Drain @ 2.9V: 0.19 mA




Pulse Discharge Characteristics

Pulse Test at 21°C (70°F)

Bkgnd Drain: Continuous
21°C (70°F) 15K ohms
0.19 mA @2.9V

Pulse Drain: 2 seconds X 12 times/day
400 ohms
~6.8 mA @2.7V



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
Values are for reference purposes and not intended for specific calculations.

©Energizer Brands, LLC. - Contents herein do not constitute a warranty.