

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name: TOOLCRAFT Ethyl-Cyanoacrylate

This safety data sheet pertains to the following products:

814761: SPEZIAL REIFENKLEBER
886512: SEKUNDENKLEBER ROPID 100 20G
886514: SEKUNDENKLEBER ROPID 150 20G
886515: SEKUNDENKLEBER ROPID 200 20 G
886517: SEKUNDENKLEBER FLÜSSIG + GEL 2 X 3 G
886535: SEKUNDENKLEBER BLITZSCHNELL 20 G
886544: FLEXIBLER SEKUNDENKLEBER 20 G
886547: SEKUNDENKLEBER MIT PINSEL 5 G
886554: SEKUNDENKLEBER-GEL 20 G
887427: TOOLCRAFT SEKUNDENKLEBER 4G
890556: SEKUNDENKLEBER BLITZSCHNELL 50 G
890557: SEKUNDENKLEBER 1200, 50 G
890558: SEKUNDENKLEBER 2800, 50 G
1488278: TOOLCRAFT 2K SEKUNDENKLEBSTOFF 10G_Komponente A

UFI: NM00-Q0KU-C005-FYP6

1.2 Relevant identified uses of the substance or mixture and uses advised against

General use: Adhesive

1.3 Details of the supplier of the safety data sheet

Company name: Conrad Electronic SE
Street/POB-No.: Klaus-Conrad-Str.1
Postal Code, city: DE-92240 Hirschau
WWW: www.conrad.de
E-mail: quality-control@conrad.de
Telephone: +49 (0)9604/40 8988
Telefax: +49 (0)9604/40 8936

Department responsible for information:
Telephone: +49 (0) 9604/40-8988, E-mail: quality-control@conrad.de

1.4 Emergency telephone number

Telephone: +49(0) 89-19240

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to EC regulation 1272/2008 (CLP)

Skin Irrit. 2; H315 Causes skin irritation.
Eye Irrit. 2; H319 Causes serious eye irritation.
STOT SE 3; H335 May cause respiratory irritation.

2.2 Label elements

Labelling (CLP)



Signal word:

Warning

Hazard statements:

H315 Causes skin irritation.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.

Precautionary statements:	P102	Keep out of reach of children.
	P261	Avoid breathing mist/vapours/spray.
	P271	Use only outdoors or in a well-ventilated area.
	P280	Wear protective gloves/protective clothing/eye protection.
	P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
	P312	Call a POISON CENTER/doctor if you feel unwell.
	P405	Store locked up.
	P501	Dispose of contents/container to hazardous or special waste collection point.

Special labelling

EUH202 Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

Text for labelling: Contains Ethyl 2-cyanoacrylate.

2.3 Other hazards

Special danger of slipping by leaking/spilling product.

Endocrine disrupting properties, Results of PBT and vPvB assessment:

The product does not contain any as PBT or vPvB classified substances.

SECTION 3: Composition/information on ingredients

3.1 Substances: not applicable

3.2 Mixtures

Chemical characterisation: Mixture of the substances listed below with non-hazardous additions:

Hazardous ingredients:

Identifiers	Designation Classification	Content
REACH 01-2119527766-29-xxxx EC No. 230-391-5 CAS 7085-85-0	Ethyl 2-cyanoacrylate Skin Irrit. 2; H315. Eye Irrit. 2; H319. STOT SE 3; H335. Specific concentration limits (SCL): STOT SE 3; H335: C ≥ 10 %	70 - 90 %
EC No. 204-617-8 CAS 123-31-9	Hydroquinone Acute Tox. 4; H302. Eye Dam. 1; H318. Skin Sens. 1; H317. Muta. 2; H341. Carc. 2; H351. Aquatic Acute 1; H400. M-factors: Aquatic Acute 1: M = 10.	< 0.1 %

Full text of H- and EUH-statements: see section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

General information:	If medical advice is needed, have product container or label at hand. Cyanacrylate - Danger - skin and eyelids will stick together in seconds. Take off contaminated clothing and wash it before reuse.
In case of inhalation:	Move victim to fresh air, put at rest and loosen restrictive clothing. Seek medical attention.
Following skin contact:	Thoroughly wash skin with soap and water. In case of skin reactions, consult a physician.
After eye contact:	Immediately flush eyes with plenty of flowing water for 10 to 15 minutes holding eyelids apart. Remove contact lenses, if present and easy to do. Continue rinsing. Subsequently seek the immediate attention of an ophthalmologist. Do not attempt to pull apart bonded eyelid.
After swallowing:	Do not induce vomiting. Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person. Seek medical attention.

4.2 Most important symptoms and effects, both acute and delayed

Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation.

4.3 Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media: Water spray jet, extinguishing powder, foam, carbon dioxide.

Extinguishing media which must not be used for safety reasons:

Full water jet

5.2 Special hazards arising from the substance or mixture

Combustible. On contact with air, potentially explosive mixtures may develop.

In case of strong heating/In case of fire may be liberated: Cyanides, nitrogen oxides (NO_x), carbon monoxide and carbon dioxide.

5.3 Advice for firefighters

Special protective equipment for firefighters:

Wear self-contained positive pressure breathing apparatus and full firefighting protective clothing.

Additional information:

Hazchem-Code: -

Use fine water spray to cool endangered containers. You have to dispose of contaminated extinguishing water according to the regulations of the authorities.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Do not breathe mist/vapours/spray. Avoid contact with the substance. If possible, eliminate leakage. Provide adequate ventilation. Wear appropriate protective equipment. Keep unprotected people away. Take off contaminated clothing and wash it before reuse.

6.2 Environmental precautions

Do not allow to enter into ground-water, surface water or drains.

6.3 Methods and material for containment and cleaning up

Absorb with liquid-binding material (e.g. sand, diatomaceous earth, acid- or universal binding agents) and place in closed containers for disposal. Plug leak if safely possible.

Additional information:

Special danger of slipping by leaking/spilling product.

6.4 Reference to other sections

Refer additionally to section 8 and 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advices on safe handling:

Provide adequate ventilation, and local exhaust as needed. Do not breathe mist/vapours/spray. Do not get in eyes, on skin, or on clothing. Wear appropriate protective equipment. Do not eat, drink or smoke when using this product. Wash hands thoroughly after handling. Take off contaminated clothing and wash it before reuse. Have eye wash bottle or eye rinse ready at work place.

Precautions against fire and explosion:

Keep away from heat.

When handling larger quantities, take precautionary measures against electrostatic charging.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storerooms and containers:

Keep container dry, tightly closed and store at cool and aired place.

Keep only in original container.

Hints on joint storage:

Do not store together with strong oxidizing agents or strong acids.

Keep away from food, drink and animal feedingstuffs.

7.3 Specific end use(s)

No information available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limit values:

CAS No.	Designation	Type	Limit value
7085-85-0	Ethyl 2-cyanoacrylate	Great Britain: WEL-STEL	1.5 mg/m ³ ; 0.3 ppm
		Ireland: 15 minutes	1 ppm
		Ireland: 8 hours	0.2 ppm
123-31-9	Hydroquinone	Great Britain: WEL-TWA	0.5 mg/m ³
		Ireland: 8 hours	0.5 mg/m ³

8.2 Exposure controls

Provide good ventilation and/or an exhaust system in the work area.

Personal protection equipment

Occupational exposure controls

Respiratory protection:	Respiratory protection in case of aerosol or vapour formation. The filter class must be suitable for the maximum contaminant concentration (gas/vapour/aerosol/particulates) that may arise when handling the product.
Hand protection:	Protective gloves according to EN 374. Glove material: nitrile rubber Layer thickness: >= 0.4 mm Breakthrough time: > 480 min. Observe glove manufacturer's instructions concerning penetrability and breakthrough time.
Eye protection:	Tightly sealed goggles according to EN 166.
Body protection:	Wear suitable protective clothing.
General protection and hygiene measures:	Do not breathe mist/vapours/spray. Do not get in eyes, on skin, or on clothing. Take off contaminated clothing and wash it before reuse. Do not eat, drink or smoke when using this product. Wash hands thoroughly after handling. Have eye wash bottle or eye rinse ready at work place.

Environmental exposure controls

Refer to "6.2 Environmental precautions".

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance:	Physical state at 20 °C and 101.3 kPa: liquid Colour: colourless
Odour:	Stinging
Odour threshold:	No data available
pH:	No data available
Melting point/freezing point:	No data available
Initial boiling point and boiling range:	150 °C
Flash point/flash point range:	87 °C
Evaporation rate:	No data available
Flammability:	No data available
Explosion limits:	No data available
Vapour pressure:	No data available
Vapour density:	No data available
Density:	1.05 g/mL
Solubility:	Soluble in: acetone
Water solubility:	Insoluble
Partition coefficient: n-octanol/water:	No data available
Auto-ignition temperature:	No data available
Decomposition temperature:	No data available

Viscosity, kinematic: No data available
Explosive properties: No data available
Oxidizing characteristics: No data available

9.2 Other information

Ignition temperature: 500 °C

SECTION 10: Stability and reactivity

10.1 Reactivity

Refer to subsection "Possibility of hazardous reactions".

10.2 Chemical stability

Stable under recommended storage conditions.

10.3 Possibility of hazardous reactions

Contact with the following materials leads to a violent reaction: Water, humidity - Polymerization along with heat production.

10.4 Conditions to avoid

Protect from moisture contamination. Avoid open flames.
Protect from frost, heat and sunlight.

10.5 Incompatible materials

Strong oxidizing agents, strong acids

10.6 Hazardous decomposition products

Thermal decomposition: No decomposition when used properly.
No data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity: LD50 rat, oral: 5000 mg/kg
LD50 Rabbit, dermal: 2000 mg/kg

Toxicological effects: The statements are derived from the properties of the single components. No toxicological data is available for the product as such.

Acute toxicity (oral): Based on available data, the classification criteria are not met.
Acute toxicity (dermal): Based on available data, the classification criteria are not met.
Acute toxicity (inhalative): Lack of data.

Skin corrosion/irritation: Skin Irrit. 2; H315 = Causes skin irritation.
Serious eye damage/irritation: Eye Irrit. 2; H319 = Causes serious eye irritation.
Sensitisation to the respiratory tract: Based on available data, the classification criteria are not met.
Skin sensitisation: Based on available data, the classification criteria are not met.
Germ cell mutagenicity/Genotoxicity: Based on available data, the classification criteria are not met.
Carcinogenicity: Based on available data, the classification criteria are not met.
Reproductive toxicity: Based on available data, the classification criteria are not met.
Effects on or via lactation: Based on available data, the classification criteria are not met.
Specific target organ toxicity (single exposure): STOT SE 3; H335 = May cause respiratory irritation.
Specific target organ toxicity (repeated exposure): Based on available data, the classification criteria are not met.
Aspiration hazard: Based on available data, the classification criteria are not met.

Symptoms

In case of inhalation: Thoracic oppression, cough
In case of ingestion: Stomachache, nausea, redness.
After contact with skin: Irritation and redness may occur.
After eye contact: Upon direct contact with eyes may cause burning, tearing, redness.

SECTION 12: Ecological information**12.1 Toxicity**

Further details: No data available

12.2 Persistence and degradability

Further details: Product is biodegradable.

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: Bioaccumulation is unlikely.
No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

The product does not contain any as PBT or vPvB classified substances.

12.6 Other adverse effects

General information: Do not allow to enter into ground-water, surface water or drains.

SECTION 13: Disposal considerations**13.1 Waste treatment methods****Product**

Waste key number: 08 04 09* = Waste adhesives and sealants containing organic solvents or other dangerous substances

* = Evidence for disposal must be provided.

Recommendation: Incinerate as hazardous waste according to applicable local, state, and federal regulations.

Package

Recommendation: Dispose of waste according to applicable legislation.
Non-contaminated packages may be recycled.

SECTION 14: Transport information**14.1 UN number**

ADR/RID, IMDG: not applicable

IATA-DGR: UN 3334

14.2 UN proper shipping name

ADR/RID, IMDG: Not restricted

IATA-DGR: UN 3334, AVIATION REGULATED LIQUID, N.O.S. (Ethyl 2-cyanoacrylate)

14.3 Transport hazard class(es)

ADR/RID, IMDG: not applicable

IATA-DGR: Class 9

14.4 Packing group

ADR/RID, IMDG: not applicable

IATA-DGR: III

14.5 Environmental hazards

Marine pollutant: NO

14.6 Special precautions for user**Air transport (IATA)**

Hazard label:	Miscellaneous
Excepted Quantity Code:	E1
Passenger and Cargo Aircraft: Ltd.Qty.:	Pack.Instr. Y964 - Max. Net Qty/Pkg. 30 kg G
Passenger and Cargo Aircraft:	Pack.Instr. 964 - Max. Net Qty/Pkg. 450 L
Cargo Aircraft only:	Pack.Instr. 964 - Max. Net Qty/Pkg. 450 L
Special Provisions:	A27
Emergency Response Guide-Code (ERG):	9A

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

No data available

SECTION 15: Regulatory information**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture****National regulations - Great Britain**Hazchem-Code: -
No data available**National regulations - EC member states**Volatile organic compounds (VOC):
2 % by weight = 20 g/LFurther regulations, limitations and legal requirements:
Use restriction according to REACH annex XVII, no.: 3, 75**15.2 Chemical Safety Assessment**

For this mixture a chemical safety assessment is not required.

SECTION 16: Other information**Further information**

Wording of the H-phrases under paragraph 2 and 3:

H302 = Harmful if swallowed.
H315 = Causes skin irritation.
H317 = May cause an allergic skin reaction.
H318 = Causes serious eye damage.
H319 = Causes serious eye irritation.
H335 = May cause respiratory irritation.
H341 = Suspected of causing genetic defects.
H351 = Suspected of causing cancer.
H400 = Very toxic to aquatic life.
EUH202 = Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

Abbreviations and acronyms:

- Acute Tox.: Acute toxicity
- ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
- ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road
- Aquatic Acute: Hazardous to the aquatic environment - acute
- AS/NZS: Australian Standards/New Zealand Standards
- Carc.: Carcinogenicity
- CAS: Chemical Abstracts Service
- CFR: Code of Federal Regulations
- CLP: Classification, Labelling and Packaging
- DMEL: Derived minimal effect level
- DNEL: Derived no-effect level
- EC: European Community
- EN: European Standard
- EQ: Excepted quantities
- Eye Dam.: Eye damage
- Eye Irrit.: Eye irritation
- IATA: International Air Transport Association
- IATA-DGR: International Air Transport Association – Dangerous Goods Regulations
- IBC Code: International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk
- IMDG Code: International Maritime Dangerous Goods Code
- LD50: Lethal dose 50%
- MARPOL: Maritime Pollution: The International Convention for the Prevention of Pollution from Ships
- M-factor: Multiplication factor
- Muta.: Mutagenicity
- OSHA: Occupational Safety and Health Administration
- PBT: Persistent, bioaccumulative and toxic
- PNEC: Predicted no-effect concentration
- REACH: Registration, Evaluation, Authorisation and Restriction of Chemicals
- RID: Regulations Concerning the International Carriage of Dangerous Goods by Rail
- Skin Irrit.: Skin irritation
- Skin Sens.: Skin sensitisation
- STOT SE: Specific target organ toxicity - single exposure
- TRGS: Technical Rules for Hazardous Substances
- UN: United Nations
- vPvB: Very persistent and very bioaccumulative

Reason of change: Changes in section 1: Product identifier (UFI)

General revision

Date of first version: 24/8/2020

Department issuing data sheet

Contact person: see section 1: Department responsible for information

The information in this data sheet has been established to our best knowledge and was up-to-date at time of revision. It does not represent a guarantee for the properties of the product described in terms of the legal warranty regulations.