QTC3 Series
1.5x3.2 SMD Tuning Fork

Features

- Low frequency in small size SMD
- Seam sealed ceramic package offers excellent environmental & heat resistance
- Extended temperature -40 to +85°C for industrial applications


Applications

- Commercial and Industrial applications
- Wireless communications
- PDA and Smartphone
- Time of day applications






General Specifications			
Nominal Frequency	32.768kHz		
Frenquency Tolerance at 25°C	±20ppm		
Temperature Coefficient	-0.034 ± 0.008 ppm/ Δ °C ²		
Temperature Range (Operating)	-40 to +85°C		
Storage Temperature	-55 to +125°C		
Load Capacitance C _L	7pF, 9pF, 12.5pF		
Shunt Capacitance C ₀	1.7pF typ.		
Motional Capacitance C ₁	3.0fF typ.		
Equivalent Series Resistance (ESR)	65KΩ max.		
Drive Level	1μW max.		
Aging per Year	±3ppm max.		
Insulation Resistance (M Ω)	500 at 100Vdc ±15Vdc		
Quality Factor	70000 typ.		
Capacitance Ratio	450 typ.		



Part Numbering Guide							
Qantek Code	Package	Nominal Frequency (in kHz)	Load Capacitance	Operating Temperature Range	Frequency Tolerance	Packaging	
Q = Qantek	TC3 = 1.5x3.2 SMD Tuning Fork	32.768	07 = 7pF 09 = 9pF 12 = 12.5pF	B = -40 to +85°C	1 = ±10ppm 2 = ±20ppm 3 = ±30ppm	R = 3000pcs Tape&Reel	
Example: QTC332.76812B2R bold letters = recommended standard specification							







QTC3 Series 1.5x3.2 SMD Tuning Fork

Marking Code Guide

Contains manufacturer code / lot code



Frequency vs. Temperature Characteristics



To calculate the frequency stability the parabolic curvature constant (K) is needed. For calculating the stability at 45°C?

- 1- Change in temperature (ΔT) is (45-25) = +20°C
- 2- Change in frequency is $(-0.034 \text{ x} (\Delta^{\circ}\text{C})^2) = (-0.035 \text{ x} (20)^2 = -13.6 \text{ppm}$

