

## Red Line Lasermodule

LFL635-5-6(9x20)60

Order Number: 70108477

Main Parameters (*)	min	typ	max	Unit
Wavelength		635		nm
Optical Diode Power	2	3.5	5	mW
Operating Voltage	3		6	V DC
Operating Current	20	40	60	mA
Operating Temperature	-20		40	°C
Storage Temperature	-40		80	°C

### Optical Parameters

Beam Shape	Line
Laser Class	1
Divergence	1mrad
Fan Angle	60°
Line Thickness	<1.2mm@1m
Operating Distance	2m
Optics	acrylic lens
Laser technology	Diode
Focus	fixed (1000mm)

### Technical Parameters

Lifetime	>3000h
RoHS	yes

### Electrical Parameters

Potential of Housing	VDD(+)
Power Supply	LFNT-3

### Mechanical Parameters


Size	Ø9x20mm
Material	Brass
Cable length	100mm
Wire type	26AWG, 0,14mm <sup>2</sup>
Output Aperture	6mm
Weight	6g

(\*) Over the complete operating temperature

### Features

- Operating Voltage 3-6V DC
- Laser Class 1
- Compact size
- Uniform line thickness
- Low cost


### Picture




### Cable Colors

Ground		black	GND
Positive		red	3 - 6V DC

### Drawing



### Safety Label



### Revision

REV 6

Laserfuchs is a registered trademark of the Picotronic GmbH

<b>Picotronic GmbH</b>	Geschäftsführende Gesellschafter:	FON +49(0)261-983 497-50 FAX +49(0)261-983 497-55 www.laserfuchs.de info@laserfuchs.de	Sparkasse Koblenz BLZ 570 501 20, KTO 211 003 BIC / IBAN : MALADE51KOB DE41 5705 0120 0000 2110 03	Postbank Stuttgart BLZ 600 100 70, KTO 770 787 04 BIC / IBAN : PBNKDEFF DE41 6001 0070 0077 0787 04	Steuernummer: 22/651/0291/4 Ust-Idnr. DE814473445 Amtsgericht Koblenz HRB 20026 WEEE-Reg.-Nr. DE85231360
------------------------	--------------------------------------	---	---	--	---