

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Degeaser		
Print date: 18.05.2015	Product code: 106	Page 1 of 8

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Degeaser

1.2. Relevant identified uses of the substance or mixture and uses advised against

Uses advised against

Reserved for industrial and professional use.

1.3. Details of the supplier of the safety data sheet

Company name:	ITW LLC & Co. KG	
Street:	Mühlackerstrasse 147	
Place:	D-75417 Mühlacker	
Telephone:	++49(0)7041-96340	Telefax: ++49(0)7041-963429
e-mail:	info@itwcp.de	
Internet:	www.itwcp.de	
Responsible Department:	Produktsicherheit	

1.4. Emergency telephone number:

++49(0)7041-96340
Mo. - Do. 8.00 - 16.30 Fr. 8.00 - 14.00

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Directive 67/548/EEC or 1999/45/EC

Indications of danger: F+ - Extremely flammable, Xi - Irritant
R phrases:
Extremely flammable.
Irritating to eyes and skin.
Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
Vapours may cause drowsiness and dizziness.

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Hazard categories:
Flammable gas: Flam. Gas 1
Serious eye damage/eye irritation: Eye Irrit. 2
Specific target organ toxicity - single exposure: STOT SE 3
Hazardous to the aquatic environment: Aquatic Chronic 3
Hazard Statements:
Extremely flammable aerosol.
Pressurised container: May burst if heated.
Causes serious eye irritation.
May cause drowsiness or dizziness.
Harmful to aquatic life with long lasting effects.

2.2. Label elements

Hazardous components which must be listed on the label

Propan-2-ol, 1-Methoxy-2-propanol, Monopropylenglycolmethylether, Hydrocarbons

Signal word: Danger

Pictograms: GHS02-GHS07



Safety Data Sheet

according to Regulation (EC) No 1907/2006

Degeaser

Print date: 18.05.2015

Product code: 106

Page 2 of 8

Hazard statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H412	Harmful to aquatic life with long lasting effects.

Precautionary statements

P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P273	Avoid release to the environment.
P251	Do not pierce or burn, even after use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P271	Use only outdoors or in a well-ventilated area.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Hazardous components

EC No	Chemical name	Quantity
CAS No	Classification according to Directive 67/548/EEC	
Index No	Classification according to Regulation (EC) No. 1272/2008 [CLP]	
REACH No		
200-661-7	propan-2-ol; isopropyl alcohol; isopropanol	25-50%
67-63-0	F - Highly flammable, Xi - Irritant R11-36-67	
603-117-00-0	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3; H225 H319 H336	
203-539-1	1-Methoxy-2-propanol	25-50 %
107-98-2	F - Highly flammable, Xn - Harmful, Xi - Irritant R11-22-36/37/38	
	Flam. Liq. 3, STOT SE 3; H226 H336	
01-2119457435-35		
	Solvent naphta light	2,5-10%
64742-95-6	Xn - Harmful, Xi - Irritant, N - Dangerous for the environment R10-37-51-53-65	
	Flam. Liq. 3, STOT SE 3, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H226 H335 H336 H304 H411	
204-696-9	Carbondioxide	2,5-10%
124-38-9		
	Compressed gas; H280	

Full text of R-, H- and EUH-phrases: see section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

After inhalation

Provide fresh air. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

After contact with skin

After contact with skin, wash immediately with: Water. Change contaminated clothing.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Degeaser

Print date: 18.05.2015

Product code: 106

Page 3 of 8

After contact with eyes

If product gets into the eye, keep eyelid open and rinse immediately with large quantities of water, for at least 5 minutes. Subsequently consult an ophthalmologist.

After ingestion

If swallowed, immediately drink: Water.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**

Carbon dioxide (CO₂). Foam. Extinguishing powder.

Unsuitable extinguishing media

Water with tenside additive. Water.

5.2. Special hazards arising from the substance or mixture

Combustible. Vapours may form explosive mixtures with air. Heating causes rise in pressure with risk of bursting.

5.3. Advice for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Suppress gases/vapours/mists with water spray jet. Contaminated fire-fighting water must be collected separately. Do not allow to enter into surface water or drains.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Remove all sources of ignition. Provide adequate ventilation. Wear a self-contained breathing apparatus and chemical protective clothing.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Explosion hazard.

6.3. Methods and material for containment and cleaning up

Ventilate affected area.

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Advice on protection against fire and explosion

Keep away from sources of ignition. - No smoking.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**

Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from sources of ignition. - No smoking.

Advice on storage compatibility

Do not store together with: Material, rich in oxygen, oxidizing.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Degeaser

Print date: 18.05.2015

Product code: 106

Page 4 of 8

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits (EH40)

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
107-98-2	1-Methoxypropan-2-ol	100	375		TWA (8 h)	WEL
		150	560		STEL (15 min)	WEL
124-38-9	Carbon dioxide	5000	9150		TWA (8 h)	WEL
		15000	27400		STEL (15 min)	WEL
67-63-0	Propan-2-ol	400	999		TWA (8 h)	WEL
		500	1250		STEL (15 min)	WEL

8.2. Exposure controls



Appropriate engineering controls

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Protective and hygiene measures

Remove contaminated, saturated clothing immediately. Protect skin by using skin protective cream. After work, wash hands and face. When using do not eat or drink.

Eye/face protection

Tightly sealed safety glasses.

Hand protection

DIN EN 374 Tested protective gloves are to be worn: Butyl rubber. For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

Skin protection

Protective clothing:

Respiratory protection

In case of inadequate ventilation wear respiratory protection.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Aerosol
Colour:	colourless
Odour:	characteristic

Test method

Changes in the physical state

Initial boiling point and boiling range:	82,4 °C
Flash point:	<0 °C
Lower explosion limits:	1,8 vol. %
Upper explosion limits:	13,1 vol. %

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Degeaser

Print date: 18.05.2015

Product code: 106

Page 5 of 8

Ignition temperature:	270 °C
Vapour pressure: (at 20 °C)	13,3 hPa
Vapour pressure: (at 50 °C)	60 hPa
Density (at 0,82 °C):	0,82 g/cm ³
Solvent content:	34,40 %

SECTION 10: Stability and reactivity**10.1. Reactivity**

No data available

10.2. Chemical stability

No data available

10.3. Possibility of hazardous reactions

No data available

10.4. Conditions to avoid

Keep away from heat. Ignition hazard.

10.5. Incompatible materials

No data available

10.6. Hazardous decomposition products

No data available

SECTION 11: Toxicological information**11.1. Information on toxicological effects****Irritation and corrosivity**

Irritating to eyes. Following inhalation: Lung irritation. Coughing. shortage of breath. After skin contact: Irritant.

Additional information on tests

The classification was carried out according to the calculation method of the Preparations Directive (1999/45/EC).

SECTION 12: Ecological information**12.1. Toxicity**

Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Further information

Do not allow to enter into surface water or drains. The classification was carried out according to the calculation method of the Preparations Directive (1999/45/EC).

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Advice on disposal**

Do not allow to enter into surface water or drains. Dispose of waste according to applicable legislation.

Waste disposal number of waste from residues/unused products160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing dangerous substances
Classified as hazardous waste.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Degeaser

Print date: 18.05.2015

Product code: 106

Page 6 of 8

Waste disposal number of contaminated packaging

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information**Land transport (ADR/RID)**

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 625
Limited quantity: 1 L
Transport category: 2
Tunnel restriction code: D

Other applicable information (land transport)

E0

Inland waterways transport (ADN)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 344 625
Limited quantity: 1 L

Other applicable information (inland waterways transport)

E0

Marine transport (IMDG)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
14.4. Packing group: -
Hazard label: 2, see SP63

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Degeaser

Print date: 18.05.2015

Product code: 106

Page 7 of 8

Special Provisions: 63, 190, 277, 327, 344, 959
Limited quantity: See SP277
EmS: F-D, S-U

Other applicable information (marine transport)

E0

Air transport (ICAO)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS, flammable
14.3. Transport hazard class(es): 2.1
Hazard label: 2.1



Special Provisions: A145 A167
Limited quantity Passenger: 30 kg G
IATA-packing instructions - Passenger: 203
IATA-max. quantity - Passenger: 75 kg
IATA-packing instructions - Cargo: 203
IATA-max. quantity - Cargo: 150 kg

Other applicable information (air transport)

E0

: Y203

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: no

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

2004/42/EC (VOC): 34,4 %

National regulatory information

Water contaminating class (D): 2 - water contaminating

SECTION 16: Other information**Relevant R-phrases (Number and full text)**

10 Flammable.
11 Highly flammable.
22 Harmful if swallowed.
36 Irritating to eyes.
36/37/38 Irritating to eyes, respiratory system and skin.
37 Irritating to respiratory system.
51 Toxic to aquatic organisms.
53 May cause long-term adverse effects in the aquatic environment.
65 Harmful: may cause lung damage if swallowed.
67 Vapours may cause drowsiness and dizziness.

Relevant H- and EUH-phrases (Number and full text)

H222 Extremely flammable aerosol.
H225 Highly flammable liquid and vapour.
H226 Flammable liquid and vapour.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Degeaser

Print date: 18.05.2015

Product code: 106

Page 8 of 8

H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)