

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Urethane

Print date: 20.05.2015

Product code: 121

Page 2 of 8

Hazard statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

Precautionary statements

P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P271	Use only outdoors or in a well-ventilated area.
P251	Do not pierce or burn, even after use.
P211	Do not spray on an open flame or other ignition source.
P210	Keep away from heat. No Smoking.

Special labelling of certain mixtures

EUH208	Contains Butanon-2-oxim = methylethylketonoxim = MEKO (CAS 96-29-7). Long-term exposure to MEKO may damage the mucous membrane of the nose. Long-term high dose inhalation of MEKO may cause irreversible damage to health.. May produce an allergic reaction.
--------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Hazardous components

EC No	Chemical name	Quantity
CAS No	Classification according to Directive 67/548/EEC	
Index No	Classification according to Regulation (EC) No. 1272/2008 [CLP]	
REACH No		
265-151-9	Naphtha (petroleum), hydrotreated light; Low boiling point hydrogen treated naphtha	10-30%
64742-49-0	F - Highly flammable, Xn - Harmful, Xi - Irritant, N - Dangerous for the environment R11-38-51-53-65	
	Flam. Liq. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H225 H336 H304 H411	
01-2119484651-34		
265-185-4	Naphtha (petroleum), hydrodesulfurized heavy	10-30%
64742-82-1	Xn - Harmful, N - Dangerous for the environment R10-51-65-66-67	
	Flam. Liq. 3, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H226 H336 H304 H411	
	Solvent naphtha light	10-20%
64742-95-6	Xn - Harmful, Xi - Irritant, N - Dangerous for the environment R10-37-51-53-65	
	Flam. Liq. 3, STOT SE 3, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H226 H335 H336 H304 H411	
201-159-0	butanone; ethyl methyl ketone	<1%
78-93-3	F - Highly flammable, Xi - Irritant R11-36-66-67	
606-002-00-3	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3; H225 H319 H336 EUH066	

Full text of R-, H- and EUH-phrases: see section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

After inhalation

Provide fresh air. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Urethane

Print date: 20.05.2015

Product code: 121

Page 3 of 8

After contact with skin

After contact with skin, wash immediately with: Water. Change contaminated clothing.

After contact with eyes

If product gets into the eye, keep eyelid open and rinse immediately with large quantities of water, for at least 5 minutes. Subsequently consult an ophthalmologist.

After ingestion

If swallowed, immediately drink: Water.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**Carbon dioxide (CO₂). Foam. Extinguishing powder.**Unsuitable extinguishing media**

Water with tenside additive. Water.

5.2. Special hazards arising from the substance or mixture

Combustible. Vapours may form explosive mixtures with air. Heating causes rise in pressure with risk of bursting.

5.3. Advice for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Use water spray jet to protect personnel and to cool endangered containers. Suppress gases/vapours/mists with water spray jet. Contaminated fire-fighting water must be collected separately. Do not allow to enter into surface water or drains.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Remove all sources of ignition. Provide adequate ventilation. Wear a self-contained breathing apparatus and chemical protective clothing.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Explosion hazard.

6.3. Methods and material for containment and cleaning up

Ventilate affected area.

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Advice on protection against fire and explosion

Keep away from sources of ignition. - No smoking.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from sources of ignition.
- No smoking.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Urethane

Print date: 20.05.2015

Product code: 121

Page 4 of 8

Advice on storage compatibility

Do not store together with: Material, rich in oxygen, oxidizing.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits (EH40)

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
78-93-3	Butan-2-one (methyl ethyl ketone)	200	600		TWA (8 h)	WEL
		300	899		STEL (15 min)	WEL
106-97-8	Butane	600	1450		TWA (8 h)	WEL
		750	1810		STEL (15 min)	WEL

Biological Monitoring Guidance Values (EH40)

CAS No	Substance	Parameter	Value	Test material	Sampling time
78-93-3	Butan-2-one	butan-2-one	70 µmol/L	urine	Post shift

8.2. Exposure controls



Appropriate engineering controls

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Protective and hygiene measures

Remove contaminated, saturated clothing immediately. Protect skin by using skin protective cream. After work, wash hands and face. When using do not eat or drink.

Eye/face protection

Tightly sealed safety glasses.

Hand protection

DIN EN 374 Tested protective gloves are to be worn: Butyl rubber. For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

Skin protection

Protective clothing:

Respiratory protection

In case of inadequate ventilation wear respiratory protection.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Aerosol
Colour:	colourless
Odour:	characteristic

Test method

Changes in the physical state

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Urethane

Print date: 20.05.2015

Product code: 121

Page 5 of 8

Initial boiling point and boiling range:	-0,5 °C
Flash point:	<0 °C
Lower explosion limits:	1,2 vol. %
Upper explosion limits:	9,4 vol. %
Ignition temperature:	300 °C
Vapour pressure: (at 20 °C)	2100 hPa
Vapour pressure: (at 50 °C)	4900 hPa
Density (at 20 °C):	0,79 g/cm ³

SECTION 10: Stability and reactivity**10.1. Reactivity**

No data available

10.2. Chemical stability

No data available

10.3. Possibility of hazardous reactions

No data available

10.4. Conditions to avoid

Keep away from heat. Ignition hazard.

10.5. Incompatible materials

No data available

10.6. Hazardous decomposition products

No data available

Further information

No data available

SECTION 11: Toxicological information**11.1. Information on toxicological effects****Irritation and corrosivity**

Irritating to eyes. Following inhalation: Lung irritation. Coughing. shortage of breath. After skin contact: Irritant.

Additional information on tests

The classification was carried out according to the calculation method of the Preparations Directive (1999/45/EC).

SECTION 12: Ecological information**12.1. Toxicity**

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Further information

Do not allow to enter into surface water or drains. The classification was carried out according to the calculation method of the Preparations Directive (1999/45/EC).

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Advice on disposal**

Do not allow to enter into surface water or drains. Dispose of waste according to applicable legislation.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Urethane

Print date: 20.05.2015

Product code: 121

Page 6 of 8

Waste disposal number of waste from residues/unused products

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing dangerous substances
Classified as hazardous waste.

Waste disposal number of contaminated packaging

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information**Land transport (ADR/RID)**

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 625
Limited quantity: 1 L
Transport category: 2
Tunnel restriction code: D

Other applicable information (land transport)

E0

Inland waterways transport (ADN)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 344 625
Limited quantity: 1 L

Other applicable information (inland waterways transport)

E0

Marine transport (IMDG)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
14.4. Packing group: -

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Urethane

Print date: 20.05.2015

Product code: 121

Page 7 of 8

Hazard label: 2, see SP63

Special Provisions: 63, 190, 277, 327, 344, 959

Limited quantity: See SP277

EmS: F-D, S-U

Other applicable information (marine transport)

E0

Air transport (ICAO)**14.1. UN number:** UN1950**14.2. UN proper shipping name:** AEROSOLS, flammable**14.3. Transport hazard class(es):** 2.1

Hazard label: 2.1



Special Provisions: A145 A167

Limited quantity Passenger: 30 kg G

IATA-packing instructions - Passenger: 203

IATA-max. quantity - Passenger: 75 kg

IATA-packing instructions - Cargo: 203

IATA-max. quantity - Cargo: 150 kg

Other applicable information (air transport)

E0

: Y203

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: no

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

2004/42/EC (VOC): 45,71 % (319,97 g/l)

National regulatory information

Water contaminating class (D): 2 - water contaminating

SECTION 16: Other information**Relevant R-phrases (Number and full text)**

- 10 Flammable.
- 11 Highly flammable.
- 36 Irritating to eyes.
- 37 Irritating to respiratory system.
- 38 Irritating to skin.
- 51 Toxic to aquatic organisms.
- 53 May cause long-term adverse effects in the aquatic environment.
- 65 Harmful: may cause lung damage if swallowed.
- 66 Repeated exposure may cause skin dryness or cracking.
- 67 Vapours may cause drowsiness and dizziness.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Urethane

Print date: 20.05.2015

Product code: 121

Page 8 of 8

Relevant H- and EUH-phrases (Number and full text)

H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H304	May be fatal if swallowed and enters airways.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.
EUH066	Repeated exposure may cause skin dryness or cracking.
EUH208	Contains Butanon-2-oxim = methylethylketonoxim = MEKO (CAS 96-29-7). Long-term exposure to MEKO may damage the mucous membrane of the nose. Long-term high dose inhalation of MEKO may cause irreversible damage to health.. May produce an allergic reaction.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)