

**Repair Stick Aqua****SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier**

Name of product Repair Stick Aqua
Code-Nr. 105310

1.2. Relevant identified uses of the substance or mixture and uses advised against**Recommended intended purpose(s)**

2-Component Epoxy Resins

1.3. Details of the supplier of the safety data sheet**Distributor**

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster
Postbox 48045, DE-8460 Münster
Phone ++49(0)251 / 9322 - 0, Fax ++49(0)251 / 9322 - 244
E-Mail : msds@weicon.de
Internet : www.weicon.de

Advice

Produktsicherheit / Product-Safety-Department
Phone ++49(0)251 / 9322 - 0
E-mail (competent person):
msds@weicon.de

1.4. Emergency telephone number

GIZ Bonn (German, English) Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

Manufacturer

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster

1.4. Emergency telephone number**Emergency advice**

-
Phone -
GIZ Bonn (Medizinische Auskunft in Deutsch und Englisch)
Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]**

Hazard classes and Hazard categories	Hazard Statements	Classification procedure
--------------------------------------	-------------------	--------------------------

Skin Irrit. 2	H315	
Eye Irrit. 2	H319	
Skin Sens. 1	H317	
Aquatic Chronic 3	H412	

Hazard Statements

H315 Causes skin irritation.

H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H412	Harmful to aquatic life with long lasting effects.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008 [CLP/GHS]



GHS07

Signal word

Warning

Hazard Statements

H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H412	Harmful to aquatic life with long lasting effects.

Precautionary Statements

P102	Keep out of reach of children.
P264	Wash hands thoroughly after handling.
P272	Contaminated work clothing should not be allowed out of the workplace.
P273	Avoid release to the environment.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P302 + P352	IF ON SKIN: Wash with plenty of soap and water.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P332 + P313	If skin irritation occurs: Get medical advice/attention.
P333 + P313	If skin irritation or rash occurs: Get medical advice/attention.
P337 + P313	If eye irritation persists: Get medical advice/attention.
P362	Take off contaminated clothing.
P363	Wash contaminated clothing before reuse.
P501	Dispose of contents/container to hazardous or special waste collection point.

Hazardous ingredients for labeling

reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight <= 700)

Special rules for supplemental label elements for certain mixtures

Contains epoxy constituents. May produce an allergic reaction.

2.3. Other hazards

Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

**SECTION 3: Composition/ information on ingredients****3.1. Substances**

not applicable

3.2. Mixtures**Description**

2-component epoxy sticks

Hazardous ingredients

CAS No	EC No	Name	[% weight]	Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]
25068-38-6	500-033-5	reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight <= 700)	20 - 50	Eye Irrit. 2, H319 / Skin Irrit. 2, H315 / Skin Sens. 1, H317 / Aquatic Chronic 2, H411
108-95-2	203-632-7	phenol	0,5 < 1	Muta. 2, H341 / Acute Tox. 3, H331 / Acute Tox. 3, H311 / Acute Tox. 3, H301 / STOT RE 2, H373 / Skin Corr. 1B, H314
13463-67-7	236-675-5	titanium-dioxide	5 - 10	

REACH

CAS No	Name	REACH registration number
25068-38-6	reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight <= 700)	01-2119456619-26-xxxx

! SECTION 4: First aid measures**4.1. Description of first aid measures****General information**

Remove contaminated soaked clothing immediately.

In case of inhalation

Ensure of fresh air.

In the event of symptoms refer for medical treatment.

In case of skin contact

Do not use solvents or thinners.

In case of contact with skin wash off with water.

Consult a doctor if skin irritation persists.

! In case of eye contact

After eye contact, rinse opened eye for 15 minutes under running water. Transfer to hospital for specialist examination.

In case of ingestion

Do not induce vomiting.

Call for a doctor immediately.

4.2. Most important symptoms and effects, both acute and delayed**Physician's information / possible symptoms**

vomiting

Allergic symptoms

skin irritation

Physician's information / possible dangers

allergic reactions

4.3. Indication of any immediate medical attention and special treatment needed

No information available.

! SECTION 5: Firefighting measures**5.1. Extinguishing media****! Suitable extinguishing media**

Alcohol-resistant foam
Dry fire-extinguishing substance
Carbon dioxide
Water spray jet

! Unsuitable extinguishing media

Full water jet

5.2. Special hazards arising from the substance or mixture

In case of fire formation of dangerous gases possible.

Nitrogen oxides (NO_x)
Carbon monoxide (CO)
Carbon dioxide (CO₂)

5.3. Advice for firefighters**Special protective equipment for fire-fighters**

Fire-fighting operations, rescue and clearing work under effect of combustion and smoulder gases just may be done with breathing apparatus.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures****For non-emergency personnel**

Ensure adequate ventilation.
Remove persons to safety.
Use personal protective clothing.

6.2. Environmental precautions

Inform pollution control authorities if product gets into the sewerage systems or open waters.
Do not discharge into the drains/surface waters/groundwater.

6.3. Methods and material for containment and cleaning up

Send in suitable containers for recovery or disposal.
Take up with absorbent material.

6.4. Reference to other sections

Safe handling: see section 7
Disposal: see section 13
Personal protection equipment: see section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

Care for thoroughly room ventilation, if necessary use in well ventilated area with local exhaust ventilation at workplace.

General protective measures

Avoid contact with eyes and skin

Hygiene measures

At work do not eat, drink, smoke or take drugs.
Wash hands before breaks and after work.

**Repair Stick Aqua****Advice on protection against fire and explosion**

Pay attention to general rules of internal fire prevention.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**

Keep in closed original container.

Advice on storage compatibility

Do not store together with acids.

Do not store together with oxidizing agents.

Further information on storage conditions

Protect from direct solar radiation.

Store container at cool and aired place.

Store in a dry place.

Protect from heat/overheating.

7.3. Specific end use(s)**Recommendation(s) for intended use**

See section 1.2

! SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Ingredients with occupational exposure limits to be monitored**

CAS No	Name	Code	[mg/m3]	[ppm]	Remark
14807-96-6	Talc respirable dust	8 hours	1		EH40/2005
13463-67-7	Titanium dioxide: total inhalable dust	8 hours	10		EH40/2005
13463-67-7	Titanium dioxide: respirable dust	8 hours	4		EH40/2005

Indicative occupational exposure limit values (91/322/EEC, 2000/39/EC, 2006/15/EC or 2009/161/EU)

CAS No	Name	Code	[mg/m3]	[ppm]	Remark
108-95-2	phenol	8 hours	8	2	skin
		Short-term	16	4	

Additional advice

The statutory local and national regulations have to be observed.

8.2. Exposure controls**Respiratory protection**

In case of insufficient ventilation or long-term effect use breathing apparatus.

! Hand protection

In the cases of special applications, it is recommended to check the chemical resistance with the manufacturer of the gloves.

Glove material specification [make/type, thickness, permeation time/life, wetting resistance]: Nitrile rubber; 0,4mm; 480min;60min.

Chemical protective gloves must be chosen carefully in view of their design and depending on the dependence on the concentration and amounts of dangerous goods used in the specific working tasks.

Eye protection

tightly fitting goggles

Other protection measures

protective clothing

Appropriate engineering controls

Sufficient ventilation and exhaustion.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties****Appearance**

pasty

Colour

green/white

Odour

hardly noticeable

Odour threshold

not determined

Important health, safety and environmental information

	Value	Temperature	at	Method	Remark
pH value	not applicable				
boiling point	> 35 °C		ca. 101 kPa		
melting point	not applicable				
Flash point	> 100 °C				
Vapourisation rate	not applicable				
Flammable (solid)	not determined				
Flammability (gas)	not determined				
Ignition temperature	not determined				
Self ignition temperature	not determined				
Lower explosion limit	not determined				
Upper explosion limit	not determined				
Vapour pressure	< 500 Pa	20 °C			
Relative density	ca. 2				
Vapour density	not applicable				
Solubility in water					insoluble
Solubility/other	not determined				
Partition coefficient n-octanol/water (log P O/W)	not determined				
Decomposition temperature	not determined				
Viscosity dynamic	not applicable				
Viscosity kinematic	not applicable				

Oxidising properties

No information available.

**Repair Stick Aqua****Explosive properties**

not applicable

9.2. Other information

No information available.

SECTION 10: Stability and reactivity**10.1. Reactivity**

No information available.

10.2. Chemical stability

No information available.

10.3. Possibility of hazardous reactions

Reactions with acids and strong oxidising agents.

10.4. Conditions to avoid

No information available.

10.5. Incompatible materials**Substances to avoid**

Amines

Acid

Oxidising agent, strong

10.6. Hazardous decomposition products

Carbon monoxide and carbon dioxide.

Nitrous oxides (NO_x)

Toxic gases/vapours

Thermal decomposition

Remark No decomposition if used as directed.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****Acute toxicity/Irritation/Sensitization**

	Value/Validation	Species	Method	Remark
LD50 acute oral	650 mg/kg	rat		CAS: 108-95-2
LD50 acute dermal	0,625 mg/kg	rat		CAS: 108-95-2
LC50 acute inhalation	3 mg/l ()		Conversion value for acute toxicity	
Skin irritation	irritant			
Eye irritation	irritant			
Skin sensitization	sensitizing			

Experiences made from practice

Sensitization through skin contact possible.

Irritates eyes and skin.

**Repair Stick Aqua****Additional information**

The product is to be handled with the caution usual with chemicals.

Other hazardous properties may not be excluded.

SECTION 12: Ecological information**12.1. Toxicity****Ecotoxicological effects**

	Value	Species	Method	Validation
Fish	LC50 2 mg/l (96 h)	Oncorhynchus mykiss		CAS: 25068-38-6
Daphnia	EC50 1,8 mg/l (48 h)	Daphnia magna		CAS: 25068-38-6
Algae	EC50 220 mg/l (96 h)	Scenedesmus subspicatus		CAS: 25068-38-6

12.2. Persistence and degradability

	Elimination rate	Method of analysis	Method	Validation
Biological degradability				not degradable

12.3. Bioaccumulative potential

Because of the n-octanol/water distribution coefficient (log K_{ow}) accumulation in organisms is possible.

12.4. Mobility in soil

No information available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

12.6. Other adverse effects**General regulation**

Because of insolubility in water details are impossible to determinate.

Do not allow uncontrolled leakage of product into the environment.

Product is not allowed to be discharged into aquatic environment, drains or sewage treatment plants.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Recommendations for the product**

Remove in accordance with local official regulations.

Recommendations for packaging

Untampered packaging may be treated as household waste.

Packaging that cannot be cleaned should be disposed of like the product.

General information

Assignment to a waste code number / waste identification according to the EWC is to be carried out on a sector or process-specific basis.

**SECTION 14: Transport information**

	ADR/RID	IMDG	IATA-DGR
14.1. UN number	-	-	-
14.2. UN proper shipping name	-	-	-
14.3. Transport hazard class(es)	-	-	-
14.4. Packing group	-	-	-
14.5. Environmental hazards	-	-	-
14.6. Special precautions for user	No information available.		
14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	not applicable		
Transport/further information	No dangerous goods as defined by the transport regulations - ADR/RID, IMDG, ICAO/IATA-DGR.		

! SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****VOC standard**

VOC content 0 %

15.2. Chemical Safety Assessment

Chemical safety assessments for substances in this mixture were not carried out.

! SECTION 16: Other information**! Recommended uses and restrictions**

National and local regulations concerning chemicals shall be observed.

For industrial use only.

Further information

Each user is responsible for the implementation of the national special regulations.

The information contained herein is based on the state of our knowledge. It characterizes the product with regard to the appropriate safety precautions. It does not represent a guarantee of the properties of the product.

Please observe the following disclaimer! --- Our safety data sheets have been compiled according to effective EU-directives, WITHOUT taking into account the special national directives concerning the handling of hazardous substances.

Indication of changes: "!" = Data changed compared with the previous version. Previous version: 8.2

H301	Toxic if swallowed.
H311	Toxic in contact with skin.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H331	Toxic if inhaled.
H341	Suspected of causing genetic defects (state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard).



Safety Data Sheet according to Regulation (EC)

No. 1907/2006 (REACH)

Printed 08.01.2016

revision 31.08.2015 (GB) Version 8.3

Repair Stick Aqua

-
- H373 May cause damage to organs (or state all organs affected, if known) through prolonged or repeated exposure (state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard).
- H411 Toxic to aquatic life with long lasting effects.