

Safety Data Sheet

according to Regulation (EC) No 1907/2006

EM-070

Print date: 31.05.2015 No: 83031 Page 1 of 6

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier EM-070

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture: Cleaning agent. Special cleaner for the ultrasonic bath, based on citric acid, concentrate. Restricted to professional users.

1.3. Details of the supplier of the safety data sheet

Company name: EMAG AG

Street: Gerauer Strasse 34
Place: 64546 Mörfelden-Walldorf

Telephone: +49 6105 4067 780

e-mail: info@emmi-nail.de

Internet: www.emmi-nail.de

1.4. Emergency telephone number: 24-hours-emergency: Giftnotruf Berlin: +49 30 30686790 (german, english)

SECTION 2: Hazards identification

SECTION 2:

2.1. Classification of the substance or mixture

Classification according to Directive 67/548/EEC or 1999/45/EC

Indications of danger: Xi - Irritant R phrases:
Irritating to eyes and skin.

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Hazard categories:

Serious eye damage/eye irritation: Eye Dam. 1 Hazard Statements:
Causes serious eye damage.

2.2. Label elements

Hazardous components which must be listed on the label

C12-C14 Fatty alcohol ethoxylate Fatty alcohol, ethoxylated, phosphated

Signal word: Danger

Pictograms: GHS05

Hazard statements

H318 Causes serious eye damage.

Precautionary statements

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Hazard statements

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Hazardous components

EC No	Chemical name	Quantity
CAS No	Classification according to Directive 67/548/EEC	
Index No	Classification according to Regulation (EC) No. 1272/2008 [CLP]	
REACH No		
213-791-2	Water	70-80 %
7732-18-5		
201-069-1	Citric acid	<16,0 %
5949-29-1	Xi - Irritant R36	
	Eye Irrit. 2; H319	
	C12-C14 Fatty alcohol ethoxylate	<8,5 %
68439-50-9	Xn - Harmful, Xi - Irritant, N - Dangerous for the environment R22-41-50	
	Acute Tox. 4, Eye Dam. 1, Aquatic Acute 1 (M-Factor = 1); H302 H318 H400	
202-394-1	1,2,3-Benzotriazole	<2,0 %
95-14-7	Xn - Harmful, Xi - Irritant R20/22-36	
	Acute Tox. 4, Acute Tox. 4, Eye Irrit. 2; H302 H332 H319	
	Fatty alcohol, ethoxylated, phosphated	<1,5 %
73038-25-2	Xi - Irritant, N - Dangerous for the environment R38-41-51-53	
	Skin Irrit. 2, Eye Dam. 1, Aquatic Chronic 2; H315 H318 H411	

Full text of R-, H- and EUH-phrases: see section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Change contaminated clothing.

After inhalation

In case of inhaling spray mists, consult a doctor .

After contact with skin

After contact with skin, wash immediately with: Water and soap.

After contact with eyes

Immediately flush eyes with plenty of flowing water for 10 to 15 minutes holding eyelids apart. In case of troubles or persistent symptoms, consult an ophthalmologist.

After ingestion

Rinse mouth immediately and drink large quantities of water. Do not induce vomiting. Consult physician.

4.2. Most important symptoms and effects, both acute and delayed

No symptoms known up to now.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Water. Foam. Atomized water.

Unsuitable extinguishing media

High power water jet.

5.2. Special hazards arising from the substance or mixture

Can be released in case of fire: Nitrogen oxides (NOx). Carbon dioxide (CO2). Phosphorus oxides.

5.3. Advice for firefighters

Protective clothing.

Additional information

Material is not combustible. Extinguishing materials should be selected according to the surrounding area.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear personal protection equipment.

6.2. Environmental precautions

Do not empty into drains or the aquatic environment.

6.3. Methods and material for containment and cleaning up

Treat the assimilated material according to the section on waste disposal . Absorb with liquid-binding material (e.g. sand, diatomaceous earth, acid- or universal binding agents).

6.4. Reference to other sections

See protective measures under point 7 and 8.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

No special technical protective measures are necessary.

Advice on protection against fire and explosion

Product is not: Oxidizing. Flammable. Explosive.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Store only in original container.
Keep away from food, drink and animal feedingstuffs.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.2. Exposure controls

Appropriate engineering controls

Refer to chapter 7. No further action is necessary.

Protective and hygiene measures

Do not eat, drink, smoke or sneeze at the workplace. Take off immediately all contaminated clothing. Wash hands before breaks and at the end of work.

Eye/face protection

Wear eye/face protection.

Hand protection

Suitable material: PE (polyethylene). CR (polychloroprenes, Chloroprene rubber). NBR (Nitrile rubber). Butyl rubber. FKM (Fluoroelastomer (Viton)).
Tested protective gloves are to be worn: EN 374

Skin protection

Skin protection: not required.

Respiratory protection

Respiratory protection not required.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state: liquid

Colour: colourless, clear

Odour: characteristic

pH-Value (at 20 °C): 1,5 (conc.) 3,0 (1 %) **Test method** DGF H-III 1

Changes in the physical state

Melting point: -12 °C

Initial boiling point and boiling range: 100 °C

Flash point: ---

Explosive properties

not Explosive.

Oxidizing properties

not oxidizing. Density (at 20 °C): 1,07 g/cm³ DIN 12791

Water solubility: (at 20 °C) complete miscible

SECTION 10: Stability and reactivity

10.1. Reactivity

None, in case of proper use.

10.2. Chemical stability

The product is chemically stable under normal ambient conditions.

10.3. Possibility of hazardous reactions

None, in case of proper use.

10.4. Conditions to avoid

Thermal decomposition can lead to the escape of irritating gases and vapors.

10.5. Incompatible materials

Alkalis (alkalis), concentrated. Alkali metals.

10.6. Hazardous decomposition products

None, in case of proper use.

Further information

Do not mix with other products.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity

CAS No	Chemical name			
	Exposure routes	Method Dose	Species	Source
68439-50-9	C12-C14 Fatty alcohol ethoxylate			
	oral	ATE 500 mg/kg		
95-14-7	1,2,3-Benzotriazole			
	oral	ATE 500 mg/kg		
	inhalative vapour	ATE 11 mg/l		
	inhalative aerosol	ATE 1,5 mg/l		
73038-25-2	Fatty alcohol, ethoxylated, phosphated			
	oral	LD50 >2000 mg/kg	Ratte	

Irritation and corrosivity

Risk of serious damage to eyes.

Sensitising effects

no danger of sensitization.

SECTION 12: Ecological information

12.1. Toxicity

Technically correct releases of minimal concentrations to adapted biological sewage treatment facility , will not disturb the biodegradability of activated sludge. Product is acid. The product needs to apply neutralizing agents before draining to wastewater treatment plants.

12.2. Persistence and degradability

The surfactants contained in this preparation comply with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

12.3. Bioaccumulative potential

On the basis of existing data about disposal/decomposition and bio-accumulation potential, long term environmental damage is unlikely.

12.4. Mobility in soil

No data available

12.5. Results of PBT and vPvB assessment

not applicable

12.6. Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Advice on disposal

According to EAKV, allocation of waste identity numbers/waste descriptions must be carried out in a specific way for every industry and process.

Contaminated packaging

Contaminated packing must be completely emptied and can be re-used following appropriate cleaning.

SECTION 14: Transport information

Other applicable information

Not a hazardous material with respect to transportation regulations.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulatory information

2004/42/EC (VOC): 0 % (0 g/l)

National regulatory information

Water contaminating class (D): 2 - water contaminating

15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information

Changes

Data changed from previous versions: 2, 8, 11, 12, 15, 16

Relevant R-phrases (Number and full text)

20/22 Harmful by inhalation and if swallowed.

22 Harmful if swallowed.

36 Irritating to eyes.

38 Irritating to skin.

41 Risk of serious damage to eyes.

50 Very toxic to aquatic organisms.

51 Toxic to aquatic organisms.

53 May cause long-term adverse effects in the aquatic environment.

Relevant H- and EUH-phrases (Number and full text)

H302 Harmful if swallowed.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H332 Harmful if inhaled.

H400 Very toxic to aquatic life.

H411 Toxic to aquatic life with long lasting effects.

Further Information

Training instructions: Notice the directions for use on the label.

EG-SICHERHEITSDATENBLATT (VERORDNUNG (EG) n° 1907/2006 - REACH)
Version : Nr. 1 (20/05/2015)

The information is based on present level of our knowledge. It does not, however, give assurances of product properties and establishes no contract legal rights.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)