

Printing date 12.09.2015 Version: 3 Revision: 24.02.2014

# SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

Trade name: SONAX Tyre Care

Article number: 435300

1.2 Relevant identified uses of the substance or mixture and uses advised against

Sector of Use

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

**Product category** PC35 Washing and cleaning products (including solvent based products)

Application of the substance / the mixture Car care product

## 1.3 Details of the supplier of the safety data sheet

Manufacturer/Supplier:

SONAX GmbH

Münchener Straße 75

D-86633 Neuburg (Donau)

Tel.: ++49 (0)8431/53-0

## Further information obtainable from:

Product safety

E-mail: erp@sonax.de

Phone: + +49 (0) 8431 53 217

1.4 Emergency telephone number: Emergency Phone Munich Tel.: +49 (0)89 19240

## **SECTION 2: Hazards identification**

#### 2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Flam. Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

#### Classification according to Directive 67/548/EEC or Directive 1999/45/EC

F+; Extremely flammable

R12: Extremely flammable.

Information concerning particular hazards for human and environment: Warning! Pressurised container.

#### 2.2 Label elements

#### Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

Hazard pictograms



GHS02

#### Signal word Danger

#### Hazard statements

H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

### Precautionary statements

P102 Keep out of reach of children.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P251 Do not pierce or burn, even after use.

P211 Do not spray on an open flame or other ignition source.

P271 Use only outdoors or in a well-ventilated area.

P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

#### 2.3 Other hazards

### Results of PBT and vPvB assessment

**PBT:** Not applicable. **vPvB:** Not applicable.



Printing date 12.09.2015 Version: 3 Revision: 24.02.2014

Trade name: SONAX Tyre Care

(Contd. of page 1)

## SECTION 3: Composition/information on ingredients

#### 3.2 Mixtures

Description: Formulation consisting of pressurised gas and care components in aqueous solution

Dangerous components:		
EC number: 926-141-6 Reg.nr.: 01-2119456620-43-XXXX	Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics	5-10%
CAS: 106-97-8 EINECS: 203-448-7	butane ► + R12 ◆ Flam. Gas 1, H220; Press. Gas C, H280	5-10%
CAS: 74-98-6 EINECS: 200-827-9	propane ►+ R12 ◆ Flam. Gas 1, H220; Press. Gas C, H280	5-10%
CAS: 75-28-5 EINECS: 200-857-2	isobutane F+ R12 Flam. Gas 1, H220; Press. Gas C, H280	< 5%

Regulation (EC) No 648/2004 on detergents / Labelling for contents	
aliphatic hydrocarbons 1.	
anionic surfactants, non-ionic surfactants	
methylisothiazolinone, benzisothiazolinone, sodium pyrithione	

#### Additional information:

Any entry in the EC-column that begins with the number "9" is a Provisional List Number provided by ECHA pending publication of the official EC Inventory Number for the substance. See Section 15 for additional CAS number information for the substance.

For the wording of the listed risk phrases refer to section 16.

## SECTION 4: First aid measures

## 4.1 Description of first aid measures

General information: Remove soiled clothing

After inhalation: Supply fresh air; consult doctor in case of complaints.

After skin contact:

Generally the product does not irritate the skin.

Wash the areas of skin affected with water and a mild detergent.

After eye contact:

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

After swallowing: Do not induce vomiting; call for medical help immediately.

4.2 Most important symptoms and effects, both acute and delayed

No further relevant information available.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment in accordance with the doctor's assessment of the patient's condition. Symptomatic treatment.

# SECTION 5: Firefighting measures

## 5.1 Extinguishing media

Suitable extinguishing agents:

Foam

Fire-extinguishing powder

Carbon dioxide

Water spray

For safety reasons unsuitable extinguishing agents: Water with full jet

5.2 Special hazards arising from the substance or mixture

In case of fire, the following can be released:

Carbon monoxide (CO)

Sulphur oxides (SOx)



Printing date 12.09.2015 Version: 3 Revision: 24.02.2014

Trade name: SONAX Tyre Care

(Contd. of page 2)

## 5.3 Advice for firefighters

#### Protective equipment:

Do not inhale explosion gases or combustion gases.

Wear self-contained respiratory protective device.

Wear fully protective suit.

#### Additional information

Cool endangered receptacles with water spray.

Collect contaminated fire fighting water separately. It must not enter the sewage system.

#### SECTION 6: Accidental release measures

#### 6.1 Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation

Wear protective equipment. Keep unprotected persons away.

#### 6.2 Environmental precautions:

Do not allow to penetrate the ground/soil.

Do not allow to enter sewers/surface or ground water.

#### 6.3 Methods and material for containment and cleaning up:

Ensure adequate ventilation.

Absorb liquid components with liquid-binding material.

Dispose contaminated material as waste according to item 13.

#### 6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

## SECTION 7: Handling and storage

## 7.1 Precautions for safe handling Ensure good ventilation/exhaustion at the workplace.

#### Information about fire - and explosion protection:

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use.

Highly volatile, flammable constituents are released during processing.

Keep ignition sources away - Do not smoke.

Do not spray onto a naked flame or any incandescent material.

## 7.2 Conditions for safe storage, including any incompatibilities

#### Storage:

## Requirements to be met by storerooms and receptacles:

Prevent any seepage into the ground.

Observe official regulations on storing packagings with pressurised containers.

Information about storage in one common storage facility: Store away from foodstuffs.

## Further information about storage conditions:

Store receptacle in a well ventilated area.

Store in a cool place. Heat will increase pressure and may lead to the receptacle bursting.

Protect from heat and direct sunlight.

Protect from frost.

Recommended storage temperature: 20 °C.

7.3 Specific end use(s) No further relevant information available.

## SECTION 8: Exposure controls/personal protection

#### 8.1 Control parameters

#### Ingredients with limit values that require monitoring at the workplace:

#### 106-97-8 butane

WEL (Great Britain) Short-term value: 1810 mg/m³, 750 ppm

Long-term value: 1450 mg/m³, 600 ppm Carc (if more than 0.1% of buta-1.3-diene)

(Contd. on page 4)



Printing date 12.09.2015 Version: 3 Revision: 24.02.2014

Trade name: SONAX Tyre Care

(Contd. of page 3)

Additional information: The lists valid during the making were used as basis.

#### 8.2 Exposure controls

#### Suitable technical control devices

Ensure good ventilation. This can be achieved by localised extraction or general ventilation. If this is not sufficient to keep the concentration below the occupational exposure limit, suitable breathing protection is to be worn.

#### Personal protective equipment:

#### General protective and hygienic measures:

The usual precautionary measures are to be adhered to when handling chemicals.

Keep away from foodstuffs, beverages and feed.

Wash hands before breaks and at the end of work.

## Respiratory protection:

Not required in normal cases

If the occupational exposure limit is exceeded:

The following breathing protection is recommended:

Respiratory filter for organic gases and vapours (Type A)

Identification colour: Brown

[DIN EN 14387]

Protection of hands: Not required in normal cases Eye protection: Not required in normal cases

SECTION 9: Physical and chemical properties		
9.1 Information on basic physical and ch	remical properties	
General Information		
Appearance:		
Form:	Aerosol	
Colour:	White	
Odour:	Characteristic	
Odour threshold:	Not determined.	
Important information on protection of h		
environment, and on safety.	data of the content without propellant	
pH-value at 20 °C:	8.0 - 9.0	
Change in condition		
Melting point/Melting range:	Undetermined.	
Boiling point/Boiling range:	100 - 270 °C	
Flash point:	Not applicable.	
Flammability (solid, gaseous):	Not applicable.	
Ignition temperature:		
Decomposition temperature:	Not determined.	
Self-igniting:	Not determined.	
Danger of explosion:	Not determined.	
	In use, may form flammable/explosive vapour-air	
	mixture.	
Explosion limits:		
Lower:	Not determined.	
Upper:	Not determined.	
Vapour pressure:	Not determined.	
Density at 20 °C:	0.96 - 0.98 g/cm³	
Relative density	Not determined.	
Vapour density	Not determined.	
Evaporation rate	Not applicable.	



Printing date 12.09.2015 Version: 3 Revision: 24.02.2014

Trade name: SONAX Tyre Care

(Contd. of page 4)

	(	
Solubility in / Miscibility with water:	Fully miscible.	
	T dily Triboloio.	
Partition coefficient (n-octanol/water):	Not determined.	
Viscosity:		
Flow time at 20 °C	10 - 15 (DIN EN ISO 2431 / 4mm)	
Dynamic:	Not determined.	
Kinematic:	Not determined.	
9.2 Other information	No further relevant information available.	

## SECTION 10: Stability and reactivity

- 10.1 Reactivity No dangerous reactions known.
- 10.2 Chemical stability Stable under normal conditions.
- 10.3 Possibility of hazardous reactions Develops readily flammable gases/fumes.
- 10.4 Conditions to avoid

An increase in pressure may lead to bursting.

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use.

Keep ignition sources away - Do not smoke.

See Section 7 for information on safe handling.

10.5 Incompatible materials: strong oxidizing agents

10.6 Hazardous decomposition products: No dangerous decomposition products known.

## SECTION 11: Toxicological information

11.1 Information on toxicological effects There are no toxicological findings on this mixture.

Acute toxicity

LD/LC50 values relevant for classification:		
Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics		
Oral	LD50	>5000 mg/kg (rat) (OECD 401)
Dermal	LD50	>5000 mg/kg (rabbit) (OECD 402)
Inhalative	LC50/8h	>5000 mg/m³ (rat) (OECD 403)

## Primary irritant effect:

## Skin corrosion/irritation

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

## Serious eye damage/irritation

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

#### Respiratory or skin sensitisation

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

## Repeated dose toxicity

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

### CMR effects (carcinogenity, mutagenicity and toxicity for reproduction)

None of the ingredients are known to have effects which are carcinogenic, mutagenic or harmful to reproduction.

## SECTION 12: Ecological information

12.1 Toxicity There are no ecotoxicological data available on this mixture.

	,
Aquatic to	oxicity:
Hydrocari	bons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics
ELO 48 h	1000 mg/l (Daphnia magna)
ELO 72 h	1000 mg/l (Pseudokirchneriella subcapitata)
	Hydrocar ELO 48 h

(Contd. on page 6)



Printing date 12.09.2015 Version: 3 Revision: 24.02.2014

Trade name: SONAX Tyre Care

(Contd. of page 5)

LLO 96 h | 1000 mg/l (Oncorhynchus mykiss)

#### 12.2 Persistence and degradability

The surface-active substances contained in the product meet the requirement of the EU Detregent Regulation (EC/648/2004) for ultimate biodegradability for surfactants in detergents.

## Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics

Biodegradiation 69 % (-) (28d)

12.3 Bioaccumulative potential No further relevant information available.

12.4 Mobility in soil No further relevant information available.

Additional ecological information:

General notes: The product may not be released into the environment without control.

12.5 Results of PBT and vPvB assessment

**PBT:** Not applicable. **vPvB:** Not applicable.

12.6 Other adverse effects No further relevant information available.

## **SECTION 13: Disposal considerations**

#### 13.1 Waste treatment methods

Dangerous waste in accordance with the Directive on the List of Waste Materials

#### Recommendation

Must not be disposed together with household garbage. Do not allow product to reach sewage system. Waste must be disposed of while observing the local, official regulations.

#### European waste catalogue

Disposal / product + Disposal / contaminated packaging

15 01 10\* packaging containing residues of or contaminated by dangerous substances

## SECTION 14: Transport information

14.1 UN-Number

ADR, IMDG, IATA UN1950

14.2 UN proper shipping name

ADR 1950 AEROSOLS IMDG AEROSOLS

IATA AEROSOLS, flammable

### 14.3 Transport hazard class(es)

ADR



 Class
 2 5F Gases.

 Label
 2.1

IMDG, IATA



**Class** 2.1 **Label** 2.1

14.4 Packing group

ADR, IMDG, IATA Void

(Contd. on page 7)



Printing date 12.09.2015 Version: 3 Revision: 24.02.2014

Trade name: SONAX Tyre Care

(Contd. of page 6)

14.5 Environmental hazards: Marine pollutant: No

14.6 Special precautions for user Warning: Gases.

Transport/Additional information:

ADR

Limited quantities (LQ) 1L Transport category 2 Tunnel restriction code D

UN "Model Regulation": UN1950, AEROSOLS, 2.1

## SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture The following substance(s) in this product is (are) identified by CAS number either in countries not subject to the REACH regulation or in regulations not yet updated with the new naming convention for hydrocarbon solvents

Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, < 2% aromatics: CAS 64742-47-8

## National regulations:

#### Information about limitation of use:

Employment restrictions concerning pregnant and lactating women must be observed.

Employment restrictions concerning juveniles must be observed.

15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

## **SECTION 16: Other information**

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

### Relevant phrases

H220 Extremely flammable gas.

H280 Contains gas under pressure; may explode if heated.

H304 May be fatal if swallowed and enters airways.

R12 Extremely flammable.

R65 Harmful: may cause lung damage if swallowed.

R66 Repeated exposure may cause skin dryness or cracking

## Abbreviations and acronyms:

NOEL = No Observed Effect Level

NOEC = No Observed Effect Concentration

LC = letal Conentration

EC50 = half maximal effective conentraion

log POW = Octanol / water partition coefficient GHS: Globally Harmonized System of Classification and Labelling of Chemicals

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International

Carriage of Dangerous Goods by Road) IMDG: International Maritime Code for Dangerous Goods

INIDES: International valuations of the Initial Processing Stocks

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent IOELV = indicative occupational exposure limit values

Flam. Gas 1: Flammable gases, Hazard Category 1

Flam. Aerosol 1: Flammable aerosols, Hazard Category 1

Press. Gas C: Gases under pressure: Compressed gas Asp. Tox. 1: Aspiration hazard, Hazard Category 1

\* Data compared to the previous version altered.