

SAFETY DATA SHEET Kresto® Special ULTRA

This SDS is not mandated under REACH Regulation (EC) No 1907/2006 and is provided for information only.

SECTION 1: Identification of	f the substance/mixture and of the company/undertaking			
1.1. Product identifier				
Product name	Kresto® Special ULTRA			
Product number	KSP30ML, KSP250ML, KSP2LT, KSP4LTR, KSP30MLWW			
Internal identification	M 981/2			
1.2. Relevant identified uses of the substance or mixture and uses advised against				
Identified uses	Hand cleaner.			
1.3. Details of the supplier of	of the safety data sheet			
Supplier	SC Johnson Professional Ltd			
	Denby Hall Way			
	Denby			
	Derbyshire			
	DE5 8JZ			
	+44 (0) 1773 855100			
	sdsuk@scj.com			
1.4. Emergency telephone number				
Emergency telephone	Not Applicable Cosmetic Product			
SECTION 2: Hazards identi	fication			
2.1. Classification of the sub	ostance or mixture			
Classification (EC 1272/200	8)			
Physical hazards	Not Classified			
Health hazards	Not Classified			
Environmental hazards	Not Classified			
2.2. Label elements				
Hazard statements	NC Not Classified			
Labelling notes	This is a cosmetic product regulated by Regulation EC no 1223/2009 (as amended) and is thus exempt from the Safety Data Sheet requirements of Regulation EC no 1907/2006 (as amended). It is also exempt from the classification and labelling rules of the Classification, Labelling and Packaging Regulation (EC) No 1272/2008.			
2.3. Other hazards				
This product does not conta	in any substances classified as PBT or vPvB.			

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

INCI

DIMETHYL GLUTARATE LAURETH-6 JUGLANS REGIA SHELL POWDER (ASTOPON®) STEARALKONIUM BENTONITE ETHYLHEXYL STEARATE CELLULOSE ACETATE BUTYRATE TITANIUM DIOXIDE QUATERNIUM-18 BENTONITE PROPYLENE CARBONATE DIMETHYL SUCCINATE DIMETHYL ADIPATE SILICA PARFUM (FRAGRANCE)

SECTION 4: First aid measures

4.1. Description of first aid measures			
Inhalation	Not relevant. Unlikely route of exposure as the product does not contain volatile substances.		
Ingestion	Rinse mouth thoroughly with water. Get medical attention if any discomfort continues.		
Skin contact	Not relevant.		
Eye contact	Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Get medical attention promptly if symptoms occur after washing.		
4.2. Most important symptoms and effects, both acute and delayed			
Inhalation	No specific symptoms known.		
Ingestion	No specific symptoms known.		
Skin contact	No specific symptoms known.		
Eye contact	May cause temporary eye irritation.		
4.3. Indication of any immediate medical attention and special treatment needed			
Notes for the doctor	No specific recommendations.		
SECTION 5: Firefighting measurements	sures		
5.1. Extinguishing media			
Suitable extinguishing media	The product is not flammable. Use fire-extinguishing media suitable for the surrounding fire.		
5.2. Special hazards arising fr	om the substance or mixture		
Hazardous combustion products	No known hazardous decomposition products.		
5.3. Advice for firefighters			
Protective actions during firefighting	No specific firefighting precautions known.		
SECTION 6: Accidental release measures			
6.1. Personal precautions, protective equipment and emergency procedures			
6.1. Personal precautions, pro	stective equipment and emergency procedures		
6.1. Personal precautions, pro Personal precautions	otective equipment and emergency procedures Avoid contact with eyes.		

Environmental precautions Not considered to be a significant hazard due to the small quantities used.

6.3. Methods and material for	containment and cleaning up
Methods for cleaning up	Flush away spillage with plenty of water. Avoid contamination of ponds or watercourses with washing down water. Absorb spillage with non-combustible, absorbent material. Do not discharge into drains or watercourses or onto the ground.
6.4. Reference to other section	ns
Reference to other sections	For waste disposal, see Section 13.
SECTION 7: Handling and sto	rage
7.1. Precautions for safe hand	ling
Usage precautions	Avoid contact with eyes.
7.2. Conditions for safe storag	e, including any incompatibilities
Storage precautions	Stable at normal ambient temperatures.
7.3. Specific end use(s)	
Specific end use(s)	The identified uses for this product are detailed in Section 1.2.
SECTION 8: Exposure control	s/Personal protection
8.1. Control parameters	
Ingredient comments	None.
8.2. Exposure controls	
Appropriate engineering controls	Not relevant.
Eye/face protection	Not relevant.
Hygiene measures	Not relevant.
Respiratory protection	No specific recommendations.
SECTION 9: Physical and che	emical properties
9.1. Information on basic phys	ical and chemical properties
Appearance	Viscous liquid. Suspension.
Colour	Beige.
Odour	Perfume.
рН	No information available.
Melting point	<-15°C
Initial boiling point and range	>100°C @ 1013 mbar
Flash point	> 100 °C
Relative density	~ 1.131 @ 20°C
Solubility(ies)	Soluble in water.
Auto-ignition temperature	365°C
Viscosity	<22,000 mPa s @ 20°C
9.2. Other information	
Other information	None.

SECTION 10: Stability and reactivity				
10.1. Reactivity				
Reactivity	There are no known reactivity hazards associated with this product.			
10.2. Chemical stability				
Stability	Stable at normal ambient temperatures.			
10.3. Possibility of hazardous r	eactions			
Possibility of hazardous reactions	None known.			
10.4. Conditions to avoid				
Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.			
10.5. Incompatible materials				
Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.			
10.6. Hazardous decomposition	n products			
Hazardous decomposition products	Does not decompose when used and stored as recommended.			
SECTION 11: Toxicological info	ormation			
11.1. Information on toxicologic	cal effects			
General information	A qualified toxicologist has evaluated and approved this product by conducting a Product Safety Assessment as per the Cosmetic Regulation n EC no 1223/2009 (as amended). Based on knowledge of the properties of the components, adverse effects on human health are not to be expected in normal use. Customer complaint data demonstrates the product to be completely harmless to the skin. The 48h Single Patch Test results show the product to be non-irritant.			
Inhalation	No specific health hazards known.			
Ingestion	May cause discomfort if swallowed.			
Skin contact	Skin irritation should not occur when used as recommended.			
Eye contact	May cause temporary eye irritation.			
SECTION 12: Ecological information				
Ecotoxicity	Not regarded as dangerous for the environment.			
12.1. Toxicity				
12.2. Persistence and degrada	bility			
Persistence and degradability	The surfactant(s) contained in this product complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No. 648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them at their direct request, or at the request of a detergent manufacturer.			
Biological oxygen demand	378 mg/g			
Chemical oxygen demand	1525 mg/g			
12.3. Bioaccumulative potentia	1			

Bioaccumulative potential	No data available on bioaccumulation.	
12.4. Mobility in soil		
Mobility	The product is soluble in water.	
12.5. Results of PBT and vPv	B assessment	
Results of PBT and vPvB assessment	This product does not contain any substances classified as PBT or vPvB.	
12.6. Other adverse effects		
Other adverse effects	None known.	
SECTION 13: Disposal consid	lerations	
13.1. Waste treatment method		
General information	When handling waste, the safety precautions applying to handling of the product should be considered.	
Disposal methods	Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. Reuse or recycle products wherever possible.	
SECTION 14: Transport inform	nation	
Road transport notes	Not classified.	
Rail transport notes	Not classified.	
Sea transport notes	Not classified.	
Air transport notes	Not classified.	
14.1. UN number		
Not applicable.		
14.2. UN proper shipping nam		
Not applicable.		
14.3. Transport hazard class(es)	
Not applicable.		
14.4. Packing group		
Not applicable.		
14.5. Environmental hazards		
Environmentally hazardous su No.	ubstance/marine pollutant	
14.6. Special precautions for	user	
Not applicable.		
14.7. Transport in bulk accord	ing to Annex II of MARPOL and the IBC Code	
Transport in bulk according to Not applicable. Annex II of MARPOL 73/78 and the IBC Code		
SECTION 15: Regulatory info	rmation	
15.1 Sefety health and any in	opmontal regulations/logislation specific for the substance or mixture	

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

This is a cosmetic product regulated by Regulation EC no 1223/2009 (as amended) and is thus exempt from the Safety Data Sheet requirements of Regulation EC no 1907/2006 (as amended). It is also exempt from the classification and labelling rules of the Classification, Labelling and Packaging Regulation (EC) No 1272/2008.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision comments	New SDS Software
Revision date	08/01/2019
Revision	5
Supersedes date	12/01/2018
SDS number	20745

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.