

## **DATA SHEET**

DIN compensating cable KP 15 L-SIL-S 2x1,5

round

valid from:

01.12.2008

0153023

## **Application**

The compensating cable KP 15 L-SIL-S 2 x 1,5 mm<sup>2</sup> is a silicone insulated cable which transmits the thermoelectric voltage of PtRh/Pt thermocouples. It is for flexible use and fixed installation in dry rooms with low mechanical load. They may only be installed outdoors with UV- and humidity protection and in observation of the max. permitted temperature range. The steel wire armouring serves as mechanical protection.

Design

Conductor 1,5 mm<sup>2</sup> (48 x 0,20 mm)

Conductor material RCB/SCB alloying, accuracy class 2 according DIN 43722

Positive conductor: Cu (copper)

Negative conductor: CuNi (cupronickel)

Core insulation Silicone compound

Core identification Positive conductor: red

Negative conductor: white

Core layering Cores twisted together

Outer sheath Silicone compound, colour: white

Galvanized steel wire braiding with interweaved white identification thread Armouring

**Electrical properties** 

Limiting deviation class 2  $\pm$  60  $\mu$ V ( $\pm$  5,0  $\odot$ ) / me asuring point temperature +1000  $\odot$ 

Mechanical and thermal properties

Temperature range occasional flexing: -25 ℃ up t o +180 ℃

Minimum bending radius occasional flexing: 15 x cable diameter

flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2 **Flammability**