
MAGLITE[®]

INCANDESCENT D-Cell

Every Maglite® flashlight embodies a precise balance of refined optics, efficient power, durability and quality. Each Maglite® D-Cell flashlight includes two high intensity Xenon Lamps for enhanced brilliance and extended range.



Spare Lamp in Tail Cap

Packaging Options





Blister pack

Chipboard box

Features & Benefits





Available Colors



Black

Red









3D only

TECHNICAL SPECIFICATIONS

2-Cell D

- Type Full Size
- Lumens 27 Im
- Barrel Diameter 1.562 in. / 39.67 mm
- Batteries

(Alkaline) Not Included

- · Weight With Batteries 23 oz. / 674g
- Water-Resistant Yes
- Drop Resistance N/A
- Technology (Xenon) Incan
- Length 10 in. / 254 mm
- Run Time, High 8h30min
- Head Diameter

2.25 in. / 57 mm

- Rechargeable No
- Blister Size

12.88 H x 5 W x 2.25 D in.

· Chipboard Box Size -

10 H x 2.25 W x 2.25 D in.

3-Cell D

- Type Full Size
- Lumens 45 Im
- Barrel Diameter
- 1.562 in. / 39.67 mm
- Batteries

(Alkaline) Not Included

- · Weight With Batteries 30 oz. / 856g
- Water-Resistant Yes
- Drop Resistance N/A
- Technology (Krypton) Incan
- Length 12.344 in. / 313 mm
- Run Time, High 10h
- Head Diameter

2.25 in. / 57 mm

- Rechargeable No
- Blister Size

14.88 H x 5 W x 2.25 D in.

- Chipboard Box Size -
 - 12.38 H x 2.25 W x 2.25 D in.

4-Cell D

- Type Full Size
- Lumens 98 Im
- Barrel Diameter
- 1.562 in. / 39.67 mm
- Batteries

(Alkaline) Not Included

· Weight With Batteries

- 36 oz. / 1043g
- Water-Resistant Yes
- Drop Resistance N/A
- Technology (Xenon) Incan
- Length 14.719 in. / 375 mm
- Run Time, High 9h30min
- Head Diameter

2.25 in. / 57 mm

- Rechargeable No
- Blister Size

16.88 H x 5 W x 2.25 D in.

- Chinhoard Box Size -
- 14.75 H x 2.25 W x 2.25 D in.

5-Cell D

- Type Full Size
- Lumens 151 Im
- Barrel Diameter
- 1.562 in. / 39.67 mm
- Batteries

(Alkaline) Not Included

- · Weight With Batteries 43 oz. / 1233g
- Water-Resistant Yes
- Drop Resistance N/A
- Technology (Xenon) Incan
- Length 17.125 in. / 434 mm
- Run Time, High 9h15min
- Head Diameter

2.25 in. / 57 mm

- Rechargeable No
- Blister Size
- 19.25 H x 5 W x 2.25 D in.
- · Chipboard Box Size -
- 17.19 H x 2.25 W x 2.25 D in.

6-Cell D

- Type Full Size
- Lumens 136 Im Barrel Diameter
- 1.562 in. / 39.67 mm
- Batteries

(Alkaline) Not Included

· Weight With Batteries

50 oz. / 1417g

- Water-Resistant Yes
- Drop Resistance N/A
- Technology (Krypton) Incan
- Length 19.5 in. / 495 mm
- Run Time, High 11h
- Head Diameter

2.25 in. / 57 mm


- Rechargeable No
- Blister Size

21.50 H x 5 W x 2.25 D in.

· Chipboard Box Size -

19.56 H x 2.25 W x 2.25 D in.

MAG INSTRUMENT, INC. • 2001 South Hellman Ave., Ontario, CA 91761 909-947-1006 • 800-289-6241 • www.maglite.com • email: salesdesk@magmail.com





The Mag-Lite® flashlight is covered by U.S. Patent No. 5,749,645. Flashlight designed and manufactured in the U.S.A. Mag Instrument's factory is located in Ontario, California. Includes some imported components. The distinctive shapes, styles and overall appearances of all Mag® flashlights, and the circumferential inscription on the heads of all Mag® flashlights, are trademarks of Mag instrument. The circumferential inscription on the head of a flashlights signifies that it is an original Mag® flashlight and part of the Mag® flashlights, are trademarks of Mag instrument. The circumferential inscription on the head of a flashlight signifies that it is an original Mag® flashlight and part of the Mag® flashlights are trademark Registrations for the circumferential inscription and the shape, style and overall appearance of Mag® flashlights include Reg. Nos. 1,808,998, 2,074,795, 2,687,693, 2,745,460, 2,765,978 and 2,765,979. The ornamental patterns of knurling on Maglite® flashlights are trademarks of Mag Instrument (see U.S. Trademark Reg. No. 3,839,734). ©2017 MAG INSTRUMENT, INC.