

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	EPIC® H-B 24 TS	10123000 14.11.2013

Housing design H-B. The industry standard.
Ideal for many applications due to a wide range of housings and inserts



Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof



Info

Universal, robust metal housings size H-B 24

Application range

Plant engineering
Light & sound technology
Plastics industry

Product features

Hood, low version
Bolts for double lever
Side cable entry
Versions with neck

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-B 24 TS 29
PG:	29
Neck:	yes
Pieces / PU:	5
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Product Management	Document: EPIC® H-B 24 TS	1 / 2
--------------------	---------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	EPIC® H-B 24 TS	10123000 14.11.2013



Product Management	Document: EPIC® H-B 24 TS	2 / 2
--------------------	---------------------------	-------