



MINI MAGLITE® AA INCANDESCENT

Until its inception, no flashlight of this size incorporated the features, functions, and unique design elements of our Mini Maglite® AA flashlight. Now an icon of classic American design, and famous around the world for its brightness, quality, durability, and dependability.

Packaging Options







Blister pack

Blister holster pack

Presentation box

Features & Benefits







Available Colors











TECHNICAL SPECIFICATIONS



2-Cell AA

- Type Compact
- Lumens 14 Im
- Beam Distance 96m
- Peak Beam Intensity 2305cd
- Barrel Diameter .719 in. / 18 mm
- Batteries (Alkaline) Included
- Weight With Batteries 3.78 oz. / 107.16g
- Water-Resistant Yes
- Drop Resistance 1m
- Technology (Xenon) Incandescent
- Length 5.75 in. / 146 mm
- Run Time, High 5h15m
- Head Diameter 1 in. / 25.4 mm
- Rechargeable No
- Blister Size 8.88 H x 4.88 W x 1.38 D in.
- Pres. Box Size 6.66 H x 3.25 W x 1.25 D in.



MAG INSTRUMENT, INC. • 2001 South Hellman Ave., Ontario, CA 91761 909-947-1006 • 800-289-6241 • www.maglite.com • email: salesdesk@magmail.com



^{*} Under Mag Instrument's Continuous Product Improvement strategy, we do make in-line changes to existing products that can impact performance. The ANSI test results shown here are current as this spec sheet goes to press. Consult product packaging/labeling for any updated performance figures.