

ML125° Rechargeable System



The Maglite® ML125® can be CUSTOM-CONFIGURED for fastest access to the particular user's most-frequently-used functions. Four different function sets are available (General, Outdoor, Law Enforcement and Military). Using Mag's familiar QuickClik™ system the user can, within the chosen function set, access different functional modes in different sequences. Five different functional modes are available (in different sequences depending on the chosen function set): Full Power, PowerSave; Momentary On/Off; Strobe; and SOS Signal. The ML125® is a DUAL-POWER flashlight. It will operate on the environmentally friendly NiMH rechargeable battery that is supplied or, alternatively, it can run on three C-cell alkaline batteries. Some owners use both, powering the flashlight with alkalines while the NiMH battery is recharging in the supplied charging cradle.

Dual Power: Runs on either the included NiMH rechargeable battery or 3 C-cell ALKALINE batteries



Packaging Options



Chipboard Box

Features & Benefits









Available Colors



Black

TECHNICAL SPECIFICATIONS





ML125® Rechargeable

- Type Rechargeable
- Lumens 186 Im (NiMH) 193 Im (Alkaline)
- Beam Distance 258m (NiMH) / 273m (Alkaline)
- Peak Beam Intensity 16725cd (NiMH) / 18581cd (Alkaline)
- Barrel Diameter 1.199 in. / 30.455 mm
- Batteries (NiMH) Included
- Weight With Batteries 18.4 oz. / 521.63g
- Water-Resistant Yes
- Drop Resistance 1m
- Technology **LED**
- Length 11.104 in. / 282.042 mm
- Run Time, High/Low 8h30m/30h (NiMH) / 25h/72h (Alkaline)
- Head Diameter 1.977 in. / 50.216 mm
- Rechargeable Yes
- Chipboard Box Size 9.125 H x 14.125 W x 2.5 D in.



MAG INSTRUMENT, INC. • 2001 South Hellman Ave., Ontario, CA 91761 909-947-1006 • 800-289-6241 • www.maglite.com • email: salesdesk@magmail.com



