


125 Serial ATA Mobile Rack

User's Manual

---Features of product ---

- SATA to SATA interface Support SATA-I, SATA-II, SATA-III
- High performance transfer rate up to 1.5Gbps, 3Gbps, 6Gbps
- Twin power design: 15pin power & 4pin power
- Customizing design – Easy HDD Installation
- 8cm cooling heat dissipation
- Push On/Off Power Control
- Patent balance handle – No skew In/Out
- Support Hot plug & hot swappable
- Cableless HDD connection
- 2 LED for Power & HDD access
- Support SATA RAID 0,1,5(Need extra RAID control card)
- Dim: 185(L) x 146(W) x 42(H)mm
- Color for choice: black
- Weight : 0.4kg




---Safety lock--- (see picture A)




LOCK

Picture A




OPEN

---Front panel--- (see picture B)



---Back View --- (Picture C)



No.1--- (POWER SW): Power ON/OFF.

No.2--- Power LED: Power on, LED indicates Green.

No.3--- HDD Access LED : Yellow blinking for Accessing(No indication, if not accessing)

No.4--- (POWER1): 15pin Power connector

No.5--- 4pin Power connector

No.6--- 7pin Serial ATA Signal connector

No.7--- HD LED SWITCH (Enable/Disable)

- 1) DIP Switch set to ENABLE – The front HDD accessing LED can work normal (Yellow color for accessing and no indication if there is no accessing)
- 2) DIP Switch to DISABLE—No LED indication for the front HDD accessing (*this function is designed for some special HDDs which are not recognized under normal HDD indication status but when it is set to DISABLE, the HDD can work; however, the LED indication function is invalid. This is the special design to make those special HDDs can work but without LED indication).