



MATERIAL SAFETY DATA SHEET

1. Product and Company Identification

Material name CB323 Series
Use of the preparation Inkjet printing
Version # 04
Revision date 08-08-2008
CAS # Mixture
Manufacturer information Hewlett-Packard Company
1000 NE Circle Boulevard
Corvallis, OR 97330-4239 US
(Direct) 1-503-494-7199
(Toll-free within the US) 1-800-457-4209

Hewlett-Packard health effects line
(Toll-free within the US) 1-800-457-4209
(Direct) 1-503-494-7199

General information telephone number
HP Customer Care Line 1-800-474-6836
(Toll-free) 1-800-474-6836
(Direct) 1-208-323-2551

Date prepared Aug 08, 2008
MSDS number 305569

2. Hazards Identification

Emergency overview Contact with skin and eyes may result in irritation.

Acute health effects
Any potential hazards are presumed to be due to exposure to the components.

Potential health effects
Routes of exposure Potential routes of overexposure to this product are skin and eye contact
Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions.
Complete toxicity data are not available for this specific formulation

Chronic health effects None known.

Carcinogenicity None of the components present in this formulation at concentrations equal to or greater than 0.1% are listed by EU, MAK, IARC, NTP or OSHA.

3. Composition / Information on Ingredients

Component/substance	CAS number	% by weight
Water	7732-18-5	68.3324499999999
1,5-pentanediol	111-29-5	< 10
1-(2-hydroxyethyl)-2-pyrrolidone	3445-11-2	< 10
Ethyl alkyldiol	Proprietary	< 10
Metal nitrate # <@1>	Proprietary	< 10
Substituted phthalocyanine salt #5	Proprietary	< 10
Aliphatic diol	629-11-8	< 2.5
Phenylenediamine derivative	Proprietary	< 2.5

Composition comments This ink supply contains an aqueous ink formulation.
This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).



MATERIAL SAFETY DATA SHEET

4. First Aid Measures

First aid procedures

Eye contact	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.
Skin contact	Wash affected areas thoroughly with mild soap and water. If irritation persists get medical attention.
Inhalation	Move to fresh air. If symptoms persist, get medical attention.
Ingestion	If ingestion of a large amount does occur, seek medical attention.

5. Fire Fighting Measures

Flash point and method	> 200 °F (> 93.3 °C); Pensky-Martens Closed Cup
Hazardous combustion products	Refer to section 10.
Flammable properties	None known.
Extinguishing media	
Suitable extinguishing media	CO2, water, dry chemical, or foam
Unsuitable extinguishing media	None known.
Unusual fire and explosion hazard	None known.
Special firefighting procedures	None established.

6. Accidental Release Measures

Personal precautions	Wear appropriate personal protective equipment.
Environmental precautions	Do not let product enter drains. Do not flush into surface water or sanitary sewer system.
Other information	Soak up with inert absorbent material. Slowly vacuum or sweep the material into a bag or other sealed container. Dispose of in compliance with federal, state, and local regulations. See also section 13 Disposal considerations.

7. Handling and Storage

Handling	Avoid contact with skin, eyes and clothing.
Storage	Keep out of the reach of children. Keep away from excessive heat or cold.

8. Exposure Controls / Personal Protection

Exposure guidelines	Exposure limits have not been established for this product.
Personal protective equipment	
General	Use personal protective equipment to minimize exposure to skin and eye.
General hygiene considerations	Handle in accordance with good industrial hygiene and safety practice.

9. Physical & Chemical Properties

Color	Cyan/Blue
Odor threshold	Not available.
Physical state	Not available.
Form	liquid
pH	7.2 - 7.4
Melting point	Not available.
Freezing point	Not available.
Boiling point	Not determined



MATERIAL SAFETY DATA SHEET

Flash point	> 200 °F (> 93.3 °C); Pensky-Martens Closed Cup
Evaporation rate	Not determined
Flammability	Not available.
Flammability limits in air, upper, % by volume	Not available.
Flammability limits in air, lower, % by volume	Not Determined
Vapor pressure	Not determined
Vapor density	1 (air = 1.0)
Specific gravity	Not determined
Relative density	Not available.
Solubility in water	Soluble in water
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not Determined
Decomposition temperature	Not available.
VOC	3 % w/w

10. Chemical Stability & Reactivity Information

Chemical stability	Stable under recommended storage conditions.
Incompatible materials	Incompatible with strong bases and oxidizing agents.
Hazardous decomposition products	Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons.
Possibility of hazardous reactions	Will not occur.

11. Toxicological Information

Not available.

12. Ecological Information

Aquatic toxicity	LC50/96h/Fathead minnows =463 mg/L Static acute toxicity (trout), survival (100 mg/L) = 100% Static acute toxicity (trout), survival (10 mg/L) = 100%
Persistence and degradability	Not available.

13. Disposal Considerations

Disposal instructions	Dispose of in compliance with federal, state, and local regulations. HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit http://www.hp.com/recycle .
-----------------------	---

14. Transport Information

IATA

Proper shipping name	Not Applicable
Packing group	None

15. Regulatory Information

US federal regulations	US TSCA 12(b): Does not contain listed chemicals.
------------------------	---



MATERIAL SAFETY DATA SHEET

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: De minimis concentration

Metal nitrate # <@1> (Proprietary) 1.0 % N511

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

Metal nitrate # <@1> (Proprietary) N511 Listed.

CERCLA (Superfund) reportable quantity

None

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories Immediate Hazard - No
Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No

Section 302 extremely hazardous substance No

Section 311 hazardous chemical No

International regulations

All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

State regulations**US - New Jersey Community RTK (EHS Survey): Listed substance**

Metal nitrate # <@1> (Proprietary) Substance no. 3722

US - New Jersey Community RTK (EHS Survey): Reportable threshold

Metal nitrate # <@1> (Proprietary) 500 LBS

US - Pennsylvania RTK - Hazardous Substances: Listed substance

Metal nitrate # <@1> (Proprietary) Listed.

16. Other Information

HMIS® ratings Health: 1
Flammability: 1
Physical hazard: 0

NFPA ratings Health: 1
Flammability: 1
Instability: 0

Issue date Aug 8 2008 3:02PM

Revision 4

Disclaimer This Safety Data Sheet document is provided without charge to customers of Hewlett-Packard Company. Data is the most current known to Hewlett-Packard Company at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.



MATERIAL SAFETY DATA SHEET

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds