

U.I. Lapp GmbH	DATASHEET	
	EPIC® MC Module: RJ45	10345300 14.11.2013

The mixed assembly guarantees high flexibility. For applications in mechanical and plant engineering, for printing machines and slide-in technology.

The mix of different functions in one plug guarantees high flexibility

Assembly of individual connectors, suitable for different applications



Automation



Industrial machinery and plant engineering



Wind Energy



Info

Power and signal modules can be used together in one housing

Application range

Plant engineering

Control engineering

Remark





Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	MCB 8 RJ45
Version:	female
Contacts:	4 + 8
Pieces / PU:	5
Rated voltage (V):	max. 600 V/max. 125 V
Rated current (A):	max. 10 A/max. 1.5 A
Contacts:	Copper alloy, gold-plated
Number of contacts:	4 Power + 8 Data
Termination methods:	Power: crimp termination: 0.14 - 2.5 mm ² , Data: IDC/piercing termination: Cat5, AWG 24-26
Cycle of mechanical operation:	100
Temperature range:	-20 °C až +85 °C
Degree of soiling:	3

Product Management	Document: EPIC® MC Module: RJ45	1 / 2
--------------------	---------------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 LAPP GROUP
	EPIC® MC Module: RJ45	10345300 14.11.2013



Product Management	Document: EPIC® MC Module: RJ45	2 / 2
--------------------	---------------------------------	-------