



# SAFETY DATA SHEET

## 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

**Identification of the preparation** HP LaserJet Q2612A-L-AD Print Cartridge

**Use of the Substance/Preparation** This product is a toner preparation that is used in HP LaserJet M1005mfp/1010/1012/1015/1018/1020/1020 plus/1022/M1319mfp/3015/3020/3030/3050/3050Z/3052/3055 series printers.

**Version #** 09

**Revision date** 16-Jul-2010

**Company identification** Hewlett-Packard GmbH  
Herrenberger Str. 140  
71034 Böblingen, Deutschland  
Telephone 07031 140

Hewlett-Packard health effects line  
(Toll-free within the US) 1-800-457-4209  
(Direct) 1-503-494-7199  
HP Customer Care Line  
(Toll-free within the US) 1-800-474-6836  
(Direct) 1-208-323-2551  
Email: hpcustomer.inquiries@hp.com  
Poison Information Centre telephone number +49 089 1 92 40

## 2. HAZARDS IDENTIFICATION

### Acute health effects

**Skin contact** Unlikely to cause skin irritation.

**Eye contact** May cause transient slight irritation.

**Inhalation** Minimal respiratory tract irritation may occur with exposure to large amounts of toner dust.

**Ingestion** Low acute toxicity. Ingestion is a minor route of entry for intended use of this product.

### Potential health effects

**Routes of exposure** Potential routes of exposure under normal use conditions are skin, eye contact and inhalation.

Ingestion is not expected to be a primary route of exposure for this product under normal use conditions.

**Chronic health effects** Prolonged inhalation of excessive amounts of any dust may cause lung damage. Use of this product as intended does not result in inhalation of excessive amounts of dust.

**Carcinogenicity** None of the ingredients have been classified as carcinogens according to EU, IARC, MAK, NTP, OSHA or ACGIH.

**Other information** This product is not classified as hazardous according to OSHA CFR 1910.1200 or EU Directive 1999/45/EC, as amended.

This preparation contains no component classified as Persistent, Bioaccumulative, and Toxic (PBT) or very Persistent and very Bioaccumulative (vPvB) as defined under Regulation (EC) 1907/2006.

**Classification** Not classified.

**Physical hazards** Not classified as a physical hazard.

**Health hazards** Not classified as a health hazard.

**Environmental hazards** Not classified as an environmental hazard.

## 3. COMPOSITION/INFORMATION ON INGREDIENTS

| Components                 | CAS #        | Percent | EC-No.    | Classification |
|----------------------------|--------------|---------|-----------|----------------|
| Styrene acrylate copolymer | Trade secret | < 55    |           |                |
| Iron oxide                 | 1317-61-9    | < 50    | 215-277-5 |                |
| Amorphous silica           | 7631-86-9    | < 3     | 231-545-4 |                |

## 4. FIRST AID MEASURES

**Inhalation** Move person to fresh air immediately. If irritation persists, consult a physician.

|                     |  |
|---------------------|--|
| <b>Skin contact</b> | Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.   |
| <b>Eye contact</b>  | Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists, consult a physician. |
| <b>Ingestion</b>    | Rinse mouth with water. Drink one to two glasses of water. If symptoms occur, consult a physician.   |

---

## 5. FIRE-FIGHTING MEASURES

|  |   |
|--|---|
| <b>Flash point</b>   | Not applicable  |
| <b>Fire fighting equipment/instructions</b>                          | If fire occurs in the printer, treat as an electrical fire.   |
| <b>Suitable extinguishing media</b>                                  | CO2, water, or dry chemical   |
| <b>Extinguishing media which must not be used for safety reasons</b> | None known.   |
| <b>Unusual fire &amp; explosion hazards</b>                          | Like most organic material in powder form, toner can form explosive dust-air mixtures when finely dispersed in air. |
| <b>Specific methods</b>  | None established.   |
| <b>Hazardous combustion products</b>                                 | Carbon monoxide and carbon dioxide.   |

---

## 6. ACCIDENTAL RELEASE MEASURES

|                                  |   |
|----------------------------------|---|
| <b>Personal precautions</b>      | Minimise dust generation and accumulation.  |
| <b>Environmental precautions</b> | Do not flush into surface water or sanitary sewer system. See also section 13 Disposal considerations.  |
| <b>Other information</b>         | Slowly vacuum or sweep the material into a bag or other sealed container. If a vacuum is used, the motor must be rated as dust explosion-proof. Clean remainder with a damp cloth or vacuum cleaner. Fine powder can form explosive dust-air mixtures. Dispose of in compliance with federal, state, and local regulations. |

---

## 7. HANDLING AND STORAGE

|                 |  |
|-----------------|--|
| <b>Handling</b> | Keep out of the reach of children. Avoid inhalation of dust and contact with skin and eyes. Use with adequate ventilation. Keep away from excessive heat, sparks, and open flames. |
| <b>Storage</b>  | Keep out of the reach of children. Keep tightly closed and dry. Store away from strong oxidizers. Store at room temperature.   |

---

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Exposure limit values

#### Germany

| Components                   | Type | Value        | Form                |
|------------------------------|------|--------------|---------------------|
| Amorphous silica (7631-86-9) | AGW  | 4.0000 mg/m3 | Inhalable fraction. |

|                                 |   |
|---------------------------------|---|
| <b>Additional exposure data</b> | USA OSHA (TWA/PEL): 15 mg/m3 (Total Dust), 5 mg/m3 (Respirable Fraction)<br>ACGIH (TWA/TLV): 10 mg/m3 (Inhalable Particulate), 3 mg/m3 (Respirable Particulate)<br>Amorphous silica: USA OSHA (TWA/PEL): 20 mppcf 80 (mg/m3)/%SiO2, ACGIH (TWA/TLV): 10 mg/m3<br>TRGS 900 (Luftgrenzwert) - 10 mg/m3 (Einatembare partikel), 3 mg/m3 (Alveolengängige fraktion)<br>UK WEL: 10 mg/m3 (Respirable Dust), 5 mg/m3 (Inhalable Dust) |
| <b>Exposure controls</b>        | Use in a well ventilated area.  |

### Occupational exposure controls

|                |   |
|----------------|---|
| <b>General</b> | No personal respiratory protective equipment required under normal conditions of use. |
|----------------|---|

---

## 9. PHYSICAL AND CHEMICAL PROPERTIES

|                       |                     |
|-----------------------|---------------------|
| <b>Appearance</b>     | Fine powder         |
| <b>Physical state</b> | Solid               |
| <b>Form</b>           | solid               |
| <b>Color</b>          | Black.              |
| <b>Odor</b>           | Slight plastic odor |

|   |   |
|---|---|
| <b>Odour threshold</b>                                | Not available.  |
| <b>pH</b>   | Not applicable  |
| <b>Boiling point</b>                                  | Not applicable  |
| <b>Flash point</b>                                    | Not applicable  |
| <b>Flammability limits in air, upper, % by volume</b> | Not available.  |
| <b>Flammability limits in air, lower, % by volume</b> | Not flammable   |
| <b>Vapor pressure</b>                                 | Not applicable  |
| <b>Relative density</b>                               | Not available.  |
| <b>Solubility (water)</b>                             | Negligible in water. Partially soluble in toluene and xylene. |
| <b>Partition coefficient (n-octanol/water)</b>        | Not available   |
| <b>Viscosity</b>                                      | Not applicable  |
| <b>Vapor density</b>                                  | Not available.  |
| <b>Evaporation rate</b>                               | Not available.  |
| <b>Melting point</b>                                  | Not available.  |
| <b>Freezing point</b>                                 | Not available.  |
| <b>Auto-ignition temperature</b>                      | Not applicable  |
| <b>Specific gravity</b>                               | 1.5 (H <sub>2</sub> O = 1)                                    |
| <b>Softening point</b>                                | 100 °C (212 °F)   |
| <b>Percent volatile</b>                               | 0 % estimated   |
| <b>VOC</b>  | Not available.  |
| <b>Other information</b>                              | Decomposition temperature: > 200 °C                           |

---

## 10. STABILITY AND REACTIVITY

|   |   |
|---|---|
| <b>Conditions to avoid</b>              | Imaging Drum: Exposure to light         |
| <b>Hazardous decomposition products</b> | Carbon monoxide and carbon dioxide.     |
| <b>Stability</b>                        | Stable under normal storage conditions. |
| <b>Materials to avoid</b>               | Strong oxidizers                        |
| <b>Hazardous polymerization</b>         | Will not occur.                         |

---

## 11. TOXICOLOGICAL INFORMATION

|  |   |
|--|---|
| <b>Oral toxicity</b>                     | LD50/oral/rat >2000mg/kg; (OECD 401); Not harmful.. Not classified for acute oral toxicity according to EU Directive 67/548/EEC and 1999/45/EC.                 |
| <b>Carcinogenicity</b>                   | None of the ingredients have been classified as carcinogens according to EU, IARC, MAK, NTP or OSHA.  |
| <b>Inhalation toxicity</b>               | No information available.<br><br>Not classified for acute inhalation toxicity according to EU Directive 67/548/EEC and 1999/45/EC.                              |
| <b>Serious eye damage/eye irritation</b> | Not classified as irritant, according to OSHA Hazard Communication Standard (HCS) and EU Directive 67/548/EEC and as amended.                                   |
| <b>Skin sensitization</b>                | Not classified as irritant, according to OSHA Hazard Communication Standard (HCS) and EU Directive 67/548/EEC and as amended.                                   |
| <b>Chronic toxicity</b>                  | No information available.   |
| <b>Sensitization</b>                     | Not classified as a sensitizer according to EU Directive 67/548/EEC and as amended, and OSHA HCS (US).  |
| <b>Mutagenicity</b>                      | Negative, does not indicate mutagenic potential (Ames Test: Salmonella typhimurium)   |
| <b>Reproductivity</b>                    | Not classified as toxic according to EU Directive 67/548/EEC and as amended, California Prop. 65, and DFG (Germany).  |
| <b>Further information</b>               | Complete toxicity data are not available for this specific formulation<br>Refer to Section 2 for potential health effects and Section 4 for first aid measures. |

---

## 12. ECOLOGICAL INFORMATION

---

### 13. DISPOSAL CONSIDERATIONS

**Disposal instructions** Do not shred toner cartridge, unless dust-explosion prevention measures are taken. Finely dispersed particles may form explosive mixtures in air. Dispose of in compliance with federal, state, and local regulations.

HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

---

### 14. TRANSPORT INFORMATION

**Further information** 168 or more of these cartridges shipped together in a single package (e.g., box, container), by air, are regulated as a magnetized material. These requirements do not apply to single or dual pack cartridges contained in an original HP package and shrink wrapped on a pallet for shipment by air.

**ADR**

Not regulated as dangerous goods.

**IATA**

**Proper shipping name** Magnetized Material  
**UN number** 2807

**IMDG**

Not regulated as dangerous goods.

**RID**

Not regulated as dangerous goods.

---

### 15. REGULATORY INFORMATION

**Labeling**

**Contains** Amorphous silica, Iron oxide, Styrene acrylate copolymer

**EC Label** This product does not require a label according to EU Directive 1999/45/EC.

**Regulatory information** All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

---

### 16. OTHER INFORMATION

**Other information** This MSDS was prepared in compliance with EU Directive 91/155/EEC as amended by 2001/58/EC.

**Disclaimer** This Safety Data Sheet document is provided without charge to customers of Hewlett-Packard Company. Data is the most current known to Hewlett-Packard Company at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

**Issue date** 16-Jul-2010

**This data sheet contains changes from the previous version in section(s):** PHYSICAL AND CHEMICAL PROPERTIES: Color  
TOXICOLOGICAL INFORMATION: Further information  
ECOLOGICAL INFORMATION: Ecotoxicity  
TRANSPORT INFORMATION: Further information

**Manufacturer information** Hewlett-Packard Company  
11311 Chinden Boulevard  
Boise, ID 83714 USA  
(Direct) 1-503-494-7199  
(Toll-free within the US) 1-800-457-4209

## Explanation of abbreviations

|               |   |
|---------------|---|
| <b>ACGIH</b>  | American Conference of Governmental Industrial Hygienists           |
| <b>CAS</b>    | Chemical Abstracts Service  |
| <b>CERCLA</b> | Comprehensive Environmental Response Compensation and Liability Act |
| <b>CFR</b>    | Code of Federal Regulations   |
| <b>COC</b>    | Cleveland Open Cup  |
| <b>DOT</b>    | Department of Transportation  |
| <b>EPCRA</b>  | Emergency Planning and Community Right-to-Know Act (aka SARA)       |
| <b>IARC</b>   | International Agency for Research on Cancer                         |
| <b>NIOSH</b>  | National Institute for Occupational Safety and Health               |
| <b>NTP</b>    | National Toxicology Program   |
| <b>OSHA</b>   | Occupational Safety and Health Administration                       |
| <b>PEL</b>    | Permissible Exposure Limit  |
| <b>RCRA</b>   | Resource Conservation and Recovery Act                              |
| <b>REC</b>    | Recommended   |
| <b>REL</b>    | Recommended Exposure Limit  |
| <b>SARA</b>   | Superfund Amendments and Reauthorization Act of 1986                |
| <b>STEL</b>   | Short-term exposure limit   |
| <b>TCLP</b>   | Toxicity Characteristics Leaching Procedure                         |
| <b>TLV</b>    | Threshold Limit Value   |
| <b>TSCA</b>   | Toxic Substances Control Act  |
| <b>VOC</b>    | Volatile Organic Compounds  |