Innovative metal and plastic housing design
Housing in plastic or metal version. For power supply in the smallest possible space



Industrial machinery and plant engineering

Mechanical resistance

Robust

Waterproof

Info
Compact, robust metal housings size H-A 3

Application range
Machine and equipment manufacturing
Control engineering
Electronic laboratory

Product features
Hood
Bolts for single lever
Side cable entry
Versions with / without cable gland

Remark
Photographs are not to scale and do not represent detailed images of the respective products.


PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-A 3 Ts M20
M:	20
Material:	Zinc die-casting
Colour:	grey
Cable gland:	yes
Cable clamping range:	3 - 13,5
Dimensions incl. cable gland:	43
Pieces / PU:	10
Material:	Housing: powder-coated zinc die-casting, grey Lever: zinc-plated steel
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.





PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.