

UN38.3 Lithium Ion Battery Test Summary	
1	<p>Cell, Battery or Product Model Number</p> <p>Product Name: Li Polymer Battery Model Name: 643463</p>
2	<p>Cell, Battery, or product manufacturer's contact information</p> <p>Company Name: ICON ENERGY SYSTEM (SHENZHEN) CO.,LTD Address: 5F AB Block, Jinmeiwei Second Industrial Park, Guanlan Hi-tech Industrial Park, No.4 Guanqing Road, Shangkeng Community, Guanlan Street, Longhua New District, Shenzhen Tel: +86-755-6182 8818 E-mail: ldrao@highpowertech.com http: www.highpowertech.com</p>
3	<p>UN38.3 Test Laboratory</p> <p>Name: Waltek Services(Shenzhen) Co., Ltd Address: 1/F, Fukang Building ,West Baima Rd, Songgang Street, Baoan District Shenzhen Guangdong, China Tel:+86-755-83551033 E-mail: info@waltek.com.cn http: WWW.waltek.com.cn</p>
4	<p>Cell or Battery Description</p> <p>Cell or Battery: Battery Cell or Battery Type: Lithium ion Watt-hour rating or Lithium Content: 7.4V,1500mAh, 11.1Wh Completed Cell or Battery Weight: 181g Unique Test Report ID Number: WTS18S01100863-1B Physical Description (appearance): Black and square Date of test report: January 19, 2018</p>
5	<p>UN38.3 List of Tests Completed:</p> <p>Test T.1: Altitude simulation Test T.2: Thermal test Test T.3: Vibration Test T.4: Shock Test T.5: External short circuit Test T.6: Impact/Crush Test T.7: Overcharge Test T.8: Forced discharge Test results: All passed</p>
6	<p>Reference to assembled battery testing requirements, if applicable (i.e., 38.3.3 (f)and 38.3.3 (g)).</p> <p>Not Applicable</p>

7	<p>Reference to the revised edition of the Manual of Tests and Criteria used and to amendments thereto, if any: Recommendations on the TRANSPORT OF DANGEROUS GOODS, Manual of Test and Criteria, PART III, section 38.3 Lithium metal and lithium ion batteries, the sixth revised edition (ST/SG/AC.10/11/Rev.6).</p>
8	<p>Signature with name and title of signatory as an indication of the validity of information provided:</p> <p>Name: </p> <p>Department: Quality Assurance Department</p> <p>Title: Senior Supervisor</p> 