## DATASHEET



## EPIC® H-B 10 SDR-BO

10036000 14.11.2013

Housing design H-B. The industry standard.

The smallest housing with single and double lever. The right housing is available for every application





Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info Universal, robust metal housings size H-B 10

#### **Application range**

Plant engineering Light & sound technology Plastics industry

#### **Product features**

Surface-mount base, low version Bolts for double lever 1 cable entry Metal cover

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

#### **Technical Data**

Article:	H-B 10 SDR-BO 16
PG:	16
Pieces / PU:	10
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Product Management	Document: EPIC® H-B 10 SDR-BO	1 / 2
DN 0404 /01 00 10	©2012 Lapp Group Tochnical changes reconved	






# DATASHEET



## EPIC® H-B 10 SDR-BO

10036000

14.11.2013



Product Management	Document: EPIC® H-B 10 SDR-BO	2/2
PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved Photographs are not to scale and do not represent detailed images of the respective products.		