



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017

TOOLCRAFT

Silikonspray 400 ml

Material number 886532

Page: 1 of 11

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name: TOOLCRAFT Silikonspray 400 ml

1.2 Relevant identified uses of the substance or mixture and uses advised against

General use: Lubricating agent/Lubricants

1.3 Details of the supplier of the safety data sheet

Company name: Conrad Electronic SE
Street/POB-No.: Klaus-Conrad-Str. 1
Postal Code, city: 92240 Hirschau
Germany
E-mail: quality-control@conrad.de
Telephone: +49 (0)9604 / 40 - 8988
Telefax: +49 (0)9604 / 40 - 8936

1.4 Emergency telephone number

Telefon: +49 (0) 89 – 19240 (24 h)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to EC regulation 1272/2008 (CLP)

Aerosol 1; H222; H229 Extremely flammable aerosol. Pressurised container: May burst if heated.
Aquatic Chronic 3; H412 Harmful to aquatic life with long lasting effects.

2.2 Label elements

Labelling (CLP)



Signal word:

Danger

Hazard statements:	H222	Extremely flammable aerosol.
	H229	Pressurised container: May burst if heated.
	H412	Harmful to aquatic life with long lasting effects.

**TOOLCRAFT****SAFETY DATA SHEET**

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017**Silikonspray 400 ml**

Material number 886532

Page: 2 of 11

Precautionary statements:

P102	Keep out of reach of children.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P261	Avoid breathing vapours/spray.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P501	Dispose of contents/container to hazardous or special waste collection point.

2.3 Other hazards

Exposure to temperatures exceeding 50 °C will increase pressure: resulting in danger of bursting or explosion.

Potentially explosive mixtures may form if adequate ventilation is not provided.

Results of PBT and vPvB assessment:

No data available

SECTION 3: Composition / information on ingredients

3.1 Substances: not applicable

3.2 Mixtures

Chemical characterisation: Mixture of the substances listed below with non-hazardous additions.

Hazardous ingredients:

Ingredient	Designation	Content	Classification
REACH 01-2119475515-33-xxxx EC No. 927-510-4	Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics	2.5 - 10 %	Flam. Liq. 2; H225. Skin Irrit. 2; H315. STOT SE 3; H336. Asp. Tox. 1; H304. Aquatic Chronic 2; H411.
REACH 01-2119475514-35-xxxx EC No. 921-024-6 CAS 64742-49-0	Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, <5% n-hexane	2.5 - 10 %	Flam. Liq. 2; H225. Skin Irrit. 2; H315. STOT SE 3; H336. Asp. Tox. 1; H304. Aquatic Chronic 2; H411.
EC No. 200-857-2 CAS 75-28-5	Isobutane	25 - 50 %	Flam. Gas 1; H220. Liquef. Gas; H280.
EC No. 200-827-9 CAS 74-98-6	Propane	25 - 50 %	Flam. Gas 1; H220. Liquef. Gas; H280.
EC No. 203-448-7 CAS 106-97-8	n-Butane, pure	2.5 - 10 %	Flam. Gas 1; H220. Liquef. Gas; H280.

Full text of H- and EUH-statements: see section 16.



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017

TOOLCRAFT

Silikonspray 400 ml

Material number 886532

Page: 3 of 11

SECTION 4: First aid measures

4.1 Description of first aid measures

In case of inhalation: Move victim to fresh air, put at rest and loosen restrictive clothing. Seek medical aid in case of troubles.

Following skin contact: Wash with generous amount of water and soap. Immediately remove any contaminated clothing, shoes or stockings. In case of skin reactions, consult a physician.

After eye contact: Immediately flush eyes with plenty of flowing water for 10 to 15 minutes holding eyelids apart. Subsequently consult an ophthalmologist.

After swallowing: Swallowing is not regarded as a possible way of exposition.

4.2 Most important symptoms and effects, both acute and delayed

No data available

4.3 Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media:

Foam, extinguishing powder, carbon dioxide.

Extinguishing media which must not be used for safety reasons:

High power water jet

5.2 Special hazards arising from the substance or mixture

Extremely flammable. Vapours form potentially explosive mixtures with air. Heavier than air, they proceed at floor level and may backflash over great distances when ignited.

May form dangerous gases and vapours in case of fire. Furthermore, there may develop: Aldehydes, carbon monoxide and carbon dioxide.

5.3 Advice for firefighters

Special protective equipment for firefighters:

Wear self-contained positive pressure breathing apparatus and full firefighting protective clothing. Do not breathe fumes.

Additional information: Hazchem-Code: -

Heating will lead to pressure increase: Danger of bursting and explosion.

Cool endangered containers with water spray and, if possible, remove from danger zone.

Fire residuals and contaminated extinguishing water must be disposed of in accordance with the regulations of the local authorities.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Eliminate all ignition sources if safe to do so.

Provide adequate ventilation. Do not breathe vapour/aerosol.

Wear appropriate protective equipment. Avoid contact with skin and eyes.



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017

TOOLCRAFT

Silikonspray 400 ml

Material number 886532

Page: 4 of 11

6.2 Environmental precautions

Do not allow to penetrate into soil, waterbodies or drains. In case of release, notify competent authorities.

6.3 Methods and material for containment and cleaning up

Take up with non-flammable, liquid binding material (e.g. sand/earth/diatomaceous earth/vermiculit) and perform disposal according to instructions.

Additional information: Use explosion-proof equipment and non-sparking tools/utensils.

6.4 Reference to other sections

Refer additionally to section 8 and 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advices on safe handling: Provide adequate ventilation, and local exhaust as needed.

Do not breathe vapour/aerosol. Avoid contact with skin and eyes.

Wear appropriate protective equipment.

Precautions against fire and explosion:

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use. Do not spray on naked flames or any incandescent material.

Use only non-sparking tools. Keep away from sources of ignition - No smoking.

Take precautionary measures against static discharges.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storerooms and containers:

Keep container tightly closed in a cool, well-ventilated place. Protect from heat and direct sunlight.

Hints on joint storage: Keep away from food, drink and animal feedingstuffs.

Do not store together with combustible or self-igniting materials or any highly flammable solids.

7.3 Specific end use(s)

No information available.



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017

TOOLCRAFT

Silikonspray 400 ml

Material number 886532

Page: 5 of 11

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limit values:

CAS No.	Designation	Type	Limit value
-	Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics	Great Britain:WEL-TWA	1200 mg/m ³ (> or = C7, Normal and branched chain alkanes)
		Great Britain:WEL-TWA	800 mg/m ³ (> or = C7, Cycloalkanes)
64742-49-0	Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, <5% n-hexane	Great Britain:WEL-TWA	1800 mg/m ³ (C5-C6 alkenes)
74-98-6	Propane	Ireland: 8 hours	1000 ppm
106-97-8	n-Butane, pure	Great Britain: WEL-STEL	1810 mg/m ³ ; 750 ppm (Carc, only applies if Butane contains more than 0.1% of buta-1,3-diene)
		Great Britain:WEL-TWA	1450 mg/m ³ ; 600 ppm (Carc, only applies if Butane contains more than 0.1% of buta-1,3-diene)
		Ireland: 8 hours	1000 ppm

DNEL/DMEL:

Information about Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

Systemic effects:

DNEL Long-term, workers, dermal: 300 mg/kg bw/d

DNEL Long-term, workers, inhalative: 2085 mg/m³

DNEL Long-term, consumers, oral: 149 mg/kg bw/d

DNEL Long-term, consumers, dermal: 149 mg/kg bw/d

DNEL Long-term, consumers, inhalative: 447 mg/m³

Information about Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, <5% n-hexane:

Systemic effects:

DNEL Long-term, workers, dermal: 773 mg/kg bw/d

DNEL Long-term, workers, inhalative: 2035 mg/m³

DNEL Long-term, consumers, oral: 669 mg/kg bw/d

DNEL Long-term, consumers, dermal: 669 mg/kg bw/d

DNEL Long-term, consumers, inhalative: 608 mg/m³

8.2 Exposure controls

Provide good ventilation and/or an exhaust system in the work area.



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017

TOOLCRAFT

Silikonspray 400 ml

Material number 886532

Page: 6 of 11

Personal protection equipment

Occupational exposure controls

- Respiratory protection: Respiratory protection must be worn whenever the WEL levels have been exceeded. Use filter type AX (= against vapours of low boiling organic substances) according to EN 14387. Observe the wear time limits according GefStoffV in combination with the rules for using respiratory protection apparatus (BGR 190). If higher concentrations occur: Wear self-contained breathing apparatus.
- Hand protection: Protective gloves according to EN 374. Glove material: Nitrile rubber - Layer thickness: ≥ 0.45 mm Breakthrough time: ≥ 240 min Observe glove manufacturer's instructions concerning penetrability and breakthrough time.
- Eye protection: Tightly sealed goggles according to EN 166.
- Body protection: Wear suitable protective clothing.
- General protection and hygiene measures: Keep away from heat sources, sparks and open flames. Do not breathe vapour/aerosol. Use only in well-ventilated areas. Change contaminated clothing. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Wash hands before breaks and after work.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance:	Form: Aerosol Colour: colourless
Odour:	similar to benzene
Odour threshold:	No data available
pH value:	No data available
Melting point/freezing point:	No data available
Initial boiling point and boiling range:	not applicable
Flash point/flash point range:	not applicable
Evaporation rate:	No data available
Flammability:	Extremely flammable.
Explosion limits:	No data available
Vapour pressure:	No data available
Vapour density:	No data available
Density:	at 20 °C: 0.58 g/mL
Water solubility:	not or slightly miscible
Partition coefficient: n-octanol/water:	No data available
Auto-ignition temperature:	No data available
Decomposition temperature:	No data available
Viscosity, kinematic:	No data available
Explosive properties:	Product is not explosive. Potentially explosive vapour/air mixtures may form.
Oxidizing characteristics:	No data available



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017

TOOLCRAFT

Silikonspray 400 ml

Material number 886532

Page: 7 of 11

9.2 Other information

Ignition temperature: > 200 °C

SECTION 10: Stability and reactivity

10.1 Reactivity

Extremely flammable aerosol.
Vapours can form explosive mixtures with air.

10.2 Chemical stability

Product is stable under normal storage conditions.

10.3 Possibility of hazardous reactions

Container under pressure.
Heating will lead to pressure increase: Danger of bursting and explosion.

10.4 Conditions to avoid

Keep away from heat sources, sparks and open flames.
Protect from direct exposure to sunlight and temperatures exceeding 50 °C.

10.5 Incompatible materials

None known

10.6 Hazardous decomposition products

In case of fire may be liberated: Aldehydes, carbon monoxide and carbon dioxide.

Thermal decomposition: No data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Toxicological effects:

- Acute toxicity (oral): Lack of data.
- Acute toxicity (dermal): Lack of data.
- Acute toxicity (inhalative): Lack of data.
- Skin corrosion/irritation: Based on available data, the classification criteria are not met.
- Eye damage/irritation: Based on available data, the classification criteria are not met.
- Sensitisation to the respiratory tract: Based on available data, the classification criteria are not met.
- Skin sensitisation: Based on available data, the classification criteria are not met.
- Germ cell mutagenicity/Genotoxicity: Lack of data.
- Carcinogenicity: Lack of data.
- Reproductive toxicity: Lack of data.
- Effects on or via lactation: Lack of data.
- Specific target organ toxicity (single exposure): Lack of data.
- Specific target organ toxicity (repeated exposure): Lack of data.
- Aspiration hazard: Lack of data.



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017

TOOLCRAFT

Silikonspray 400 ml

Material number 886532

Page: 8 of 11

Other information: Information about Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:
LD50 Rat, oral: > 5840 mg/kg (read across)
LD50 Rat, dermal: > 2800 mg/kg (read across)
LC50 Rat, inhalative: > 23.3 mg/L/4h (OECD 403, read across)
Information about Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, <5% n-hexane:
LD50 Rat, oral: > 5840 mg/kg (read across)
LD50 Rat, dermal: > 2800 mg/kg (read across)
LC50 Rat, inhalative: > 25.2 mg/L/4h
Information about Isobutane:
LC50 Rat, inhalative: > 50 mg/L/4h
Information about Propane:
LC50 Rat, inhalative: 20 mg/L/4h
Information about Butane:
LC50 Rat, inhalative: 658 mg/L/4h

Symptoms

Vapours in high concentrations have anaesthetic effect.
After contact with skin: Mucous membrane irritation.

SECTION 12: Ecological information

12.1 Toxicity

Aquatic toxicity: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
Information about Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:
Algae toxicity:
EL50 Pseudokirchneriella subcapitata (green algae): 12 mg/L/72h (OECD 201, read across)
Daphnia toxicity:
EL50 Daphnia magna (Big water flea): 3 mg/L/48h (OECD 202, read across)
Fish toxicity:
LLC50 Oncorhynchus mykiss: > 13.4 mg/L/96h (OECD 203)
Information about Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, <5% n-hexane:
Algae toxicity:
EL50 Pseudokirchneriella subcapitata (green algae): 10 - 30 mg/L/72h (OECD 201)
Daphnia toxicity:
EC50 Daphnia magna (Big water flea): 3 mg/L/48h (OECD 202)
Fish toxicity:
LLC50 Oncorhynchus mykiss: > 11.4 mg/L/96h (OECD 203)

12.2. Persistence and degradability

Further details: No data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water:
No data available

12.4 Mobility in soil

No data available



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017

TOOLCRAFT

Silikonspray 400 ml

Material number 886532

Page: 9 of 11

12.5 Results of PBT and vPvB assessment

No data available

12.6 Other adverse effects

General information: Do not allow to enter into ground-water, surface water or drains.
Avoid spills and leaks. Very small amounts contaminates drinking water.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product

Recommendation: Special waste. Do not open with force or incinerate, even when empty.
Dispose of waste according to applicable legislation.
Do not dispose of with household waste.

Contaminated packaging

Waste key number: 15 01 04 = Metallicpackaging
Recommendation: Empty carefully and completely, if possible.
Dispose of waste according to applicable legislation.

SECTION 14: Transport information

14.1 UN number

ADR/RID, IMDG, IATA-DGR:
UN 1950

14.2 UN proper shipping name

ADR/RID, IMDG: UN 1950, AEROSOLS
IATA-DGR: UN 1950, AEROSOLS, flammable

14.3 Transport hazard class(es)

ADR/RID: Class 2, Code: 5F
IMDG: Class 2, Subrisk-, see SP63
IATA-DGR: Class 2.1



14.4 Packing group

ADR/RID, IATA-DGR: not applicable
IMDG: -

14.5 Environmental hazards

Marine pollutant: NO



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017

TOOLCRAFT

Silikonspray 400 ml

Material number 886532

Page: 10 of 11

14.6 Special precautions for user

Land transport (ADR/RID)

Warning board: ADR: UN number UN 1950
RID: Kemmler-number 23, UN number UN 1950

Hazard label: 2.1

Special provisions: 190 327 344 625

Limited quantities: 1 L

EQ: E0

Contaminated packaging - Instructions: P207 LP200

Contaminated packaging - Special provisions: PP87 RR6 L2

Special provisions for packing together: MP9

Tunnel restriction code: D

Sea transport (IMDG)

EmS: F-D, S-U

Special provisions: 63, 190, 277, 327, 344, 381, 959

Limited quantities: See SP277

Excepted quantities: E0

Contaminated packaging - Instructions: P207, LP200

Contaminated packaging - Provisions: PP87, L2

IBC - Instructions: -

IBC - Provisions: -

Tank instructions - IMO: -

Tank instructions - UN: -

Tank instructions - Provisions: -

Stowage and handling: SW1 SW22

Segregation: SG69

Properties and observations: -

Segregation group: none

Air transport (IATA)

Hazard label: Flamm. gas

Excepted Quantity Code: E0

Passenger and Cargo Aircraft: Ltd.Qty.: Pack.Instr. Y203 - Max. Net Qty/Pkg. 30kg G

Passenger and Cargo Aircraft: Pack.Instr. 203 - Max. Net Qty/Pkg. 75 kg

Cargo Aircraft only: Pack.Instr. 203 - Max. Net Qty/Pkg. 150kg

Special provisions: A145 A167 A802

Emergency Response Guide-Code (ERG): 10L

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

No data available

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations - Great Britain

Hazchem-Code: -
No data available



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (REACH) and Regulation (EU) No. 2015/830

Revision date: 2/1/2017
Version: 8
Language: en-GB,IE
Date of print: 28/2/2017

TOOLCRAFT

Silikonspray 400 ml

Material number 886532

Page: 11 of 11

National regulations - EC member states

Volatile organic compounds (VOC):

93.09 % by weight = 538.7 g/L

15.2 Chemical Safety Assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information

Further information

Wording of the H-phrases under paragraph 2 and 3:

- H220 = Extremely flammable gas.
- H222 = Extremely flammable aerosol.
- H225 = Highly flammable liquid and vapour.
- H229 = Pressurised container: May burst if heated.
- H280 = Contains gas under pressure; may explode if heated.
- H304 = May be fatal if swallowed and enters airways.
- H315 = Causes skin irritation.
- H336 = May cause drowsiness or dizziness.
- H411 = Toxic to aquatic life with long lasting effects.
- H412 = Harmful to aquatic life with long lasting effects.

Reason of change: ADR/RID 2017, IMDG 2017

Date of first version: 27/5/2013

Department issuing data sheet

Contact person: see section 1: Dept. responsible for information

For abbreviations and acronyms, see: ECHA Guidance on information requirements and chemical safety assessment, chapter R.20 (Table of terms and abbreviations).

The information in this data sheet has been established to our best knowledge and was up-to-date at time of revision. It does not represent a guarantee for the properties of the product described in terms of the legal warranty regulations.