



Material Safety Data Sheet

1. Identification of the substance/mixture and of the company/undertaking

Product:	Epoxy Resin L
Manufacturer:	Conrad Electronic SE
Address:	Klaus-Conrad-Str. 1, D-92240 Hirschau
Telephone:	+49 (0) 9604 / 40 - 8988
Date of issue:	25.02.2019

1.1. Product identifier

Epoxy Resin L

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture

Epoxy resin products, low in solvents, sensitising

2. Hazards identification

2.1. Classification of the substance or mixture

Regulation (EC) No. 1272/2008

Hazard categories: Skin corrosion/irritation: Skin Irrit. 2
 Serious eye damage/eye irritation: Eye Irrit. 2
 Respiratory or skin sensitisation: Skin Sens. 1
 Hazardous to the aquatic environment: Aquatic Chronic 2

Hazard Statements: Causes skin irritation.
 May cause an allergic skin reaction.
 Causes serious eye irritation.
 Toxic to aquatic life with long lasting effects.

2.2. Label elements Regulation (EC) No. 1272/2008

Hazard components for labelling


Epoxy resin (number average molecular weight <= 700), reaction product: bisphenol-A-(epichlorhydrin)

Bisphenol-F-Epoxy resin

1,6-Bis(2,3-epoxypropoxy)hexane

Signal word: Warning

Pictograms:





Material Safety Data Sheet

4. First aid measures

4.1. Description of first aid measures

General information

Take off immediately all contaminated clothing.

After inhalation

Provide fresh air. If breathing is irregular or stopped, administer artificial respiration. Medical treatment necessary.

After contact with skin

After contact with skin, wash immediately with polyethylene glycol, followed by plenty of water. Take off immediately all contaminated clothing and wash it before reuse. If skin irritation occurs.

After contact with eyes

After contact with the eyes, rinse with water with the eyelids open for a sufficient length of time, then consult an ophthalmologist immediately.

After ingestion

Seek medical advice immediately.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

5. Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂), Extinguishing powder, Water spray jet.

Unsuitable extinguishing media

Full water jet

5.2. Special hazards arising from the substance or mixture

The product itself does not burn. In case of fire may be liberated: Gases/vapours, toxic.

5.3. Advice for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing. Full protection suit.

Additional information Suppress gases/vapours/mists with water spray jet. Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water.



Material Safety Data Sheet

6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Use personal protection equipment.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Do not allow to enter the soil or subsoil.

6.3. Methods and material for containment and cleaning up

Absorb with liquid-binding material (e.g. sand, diatomaceous earth, acid- or universal binding agents). Treat the recovered material as prescribed in the section on waste disposal.

6.4. Reference to other sections

Carefully cleaning scene of an accident.

7. Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

The usual precautions when handling chemicals must be observed.

Advice on protection against fire and explosion

No special fire protection measures are necessary.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep/Store only in original container. Provide for retaining containers, eg. floor pan without outflow.

Advice on storage compatibility

Store separately from foodstuffs.

Further information on storage conditions

Keep receptacles tightly sealed.

7.3. Specific end use(s)

The product does not contain any relevant quantities of substances with workplace-related limit values to be monitored.



Material Safety Data Sheet

8. Exposure controls/personal protection

8.1. Control parameters

8.2. Exposure controls



Protective and hygiene measures

Remove contaminated, saturated clothing immediately. Draw up and observe skin protection programme. Wash hands and face before breaks and after work and take a shower if necessary. When using do not eat or drink.

Eye/face protection

Suitable eye protection: goggles.

Hand protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. The quality of the protective gloves resistant to chemicals must be chosen as a function of the specific working place concentration and quantity of hazardous substances. For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

Suitable material: FKM (fluoro rubber), NBR (Nitrile rubber) Thickness of the glove material: > 0,5mm

Skin protection

Wear suitable protective clothing.

Respiratory protection

In case of inadequate ventilation wear respiratory protection. ABEK-P2



Material Safety Data Sheet

9. Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	Yellowish
Odour:	Characteristic
pH-Value:	not determined

Changes in the physical state

Melting point:	not determined
Initial boiling point and boiling range:	200 °C
Flash point:	150 °C

Flammability

Solid:	not applicable
Gas:	not applicable
Lower explosion limits:	not determined
Upper explosion limits:	not determined

Auto-ignition temperature

Solid:	not applicable
Gas:	not applicable
Decomposition temperature:	not determined

Oxidizing properties

Not oxidising.

Vapour pressure:	1 hPa (at 20 °C)
Density (at 23 °C):	1,1 g/cm ³ ISO 2811-2
Water solubility:	The study does not need to be conducted because the substance is known to be insoluble in water.
Solubility in other solvents:	not determined
Partition coefficient:	not determined
Viscosity / dynamic:	875 mPa·s ISO 3219 (at 23 °C)
Vapour density:	not determined
Evaporation rate:	not determined

9.2. Other information

Solid content:	not determined
----------------	----------------



Material Safety Data Sheet

10. Stability and reactivity

10.1. Reactivity

No hazardous reaction when handled and stored according to provisions.

10.2. Chemical stability

No decomposition when stored and handled properly

10.3. Possibility of hazardous reactions

Reaction with strong oxidising agents Alkalis (alkalis). Acids

10.4. Conditions to avoid

The product does not contain any relevant quantities of substances with workplace-related limit values to be monitored.

10.5. Incompatible materials

Keep away from oxidising agents.

10.6. Hazardous decomposition products

No decomposition when stored and handled properly. In case of fire may be liberated: toxic and caustic gases and vapours

11. Toxicological information

11.1. Information on toxicological effects

Acute toxicity

CAS No.	Chemical name			
	Exposure route	Dose	Species	Source
25068-38-6	Epoxy resin (number average molecular weight <= 700), reaction product: bisphenol-A-(epichlorhydrin)			
	oral	LD50 11400 mg/kg	Rat	GESTIS
	dermal	LD50 > 22800 mg/kg	Rabbit	GESTIS
16096-31-4	1,6-Bis(2,3-epoxypropoxy)hexane			
	oral	LD50 3010 mg/kg	Rat	OECD 401
	dermal	LD50 > 2000 mg/kg	Rat	OECD 402
28064-14-4	Phenol, polymer with formaldehyde, glycidyl ether			
	oral	LD50 > 2000 mg/kg	Rat	
	dermal	LD50 > 2000 mg/kg	Rat	

Additional information on tests

The mixture is classified as hazardous according to regulation (EC) No 1272/2008 [CLP].



Material Safety Data Sheet

12. Ecological information

12.1. Toxicity

CAS No.	Chemical name				
	Aquatic toxicity	Dose	[h] [d]	Spe Species	Source
25068-38-6	Epoxy resin (number average molecular weight <= 700), reaction product: bisphenol-A-(epichlorhydrin)				
	Acute fish toxicity	LC50 4,4 mg/l	96 h	Oncorhynchus mykiss (Rainbow trout)	EPA-660/3-75-009
	Acute algae toxicity	ErC50 9,4 mg/l	72 h	Scenedesmus capricornutum	EPA-660/3-75-009
	Acute crustacea toxicity	EC50 2,8 mg/l	48 h	Daphnia magna	OECD 202
	Acute bacteria toxicity	(> 100 mg/l)	3 h	Activated sludge	
16096-31-4	1,6-Bis(2,3-epoxypropoxy)hexane				
	Acute fish toxicity	LC50 30 mg/l	96 h	Oncorhynchus mykiss (Rainbow trout)	OECD 203
	Acute crustacea toxicity	EC50 39 - 57 mg/l	48 h	Daphnia magna	OECD 202

12.2. Persistence and degradability

The product does not contain any relevant quantities of substances with workplace-related limit values to be monitored.

CAS No.	Chemical name			
	Method	Value	d	Source
	Evaluation			
25068-38-6	Epoxy resin (number average molecular weight <= 700), reaction product: bisphenol-A-(epichlorhydrin)			
	OECD 301F	5%	28	Manufacturer
	Not readily biodegradable (according to OECD criteria)			
	OECD 301B	6-12%	28	Manufacturer
	Not readily biodegradable (according to OECD criteria)			
16096-31-4	1,6-Bis(2,3-epoxypropoxy)hexane			
	OECD 301D	47%	28	Manufacturer
	Readily biodegradable (according to OECD criteria).			

12.3. Bioaccumulative potential

The product does not contain any relevant quantities of substances with workplace-related limit values to be monitored.

Partition coefficient n-octanol/water

CAS No.	Chemical name	Log Pow
25068-38-6	Epoxy resin (number average molecular weight <= 700), reaction product: bisphenol-A-(epichlorhydrin)	3,24

BCF

CAS No.	Chemical name	BCF	Species	Source
25068-38-6	Epoxy resin (number average molecular weight <= 700), reaction product: bisphenol-A-(epichlorhydrin)	31		Quantitative structure-activity relationship (QSAR)
16096-31-4	1,6-Bis(2,3-epoxypropoxy)hexane	3,57		



Material Safety Data Sheet

12.4. Mobility in soil

The product does not contain any relevant quantities of substances with workplace-related limit values to be monitored.

12.5. Results of PBT and vPvB assessment

Not applicable

12.6. Other adverse effects

No information available.

Further information

Do not allow to enter into surface water or drains. Do not allow to enter into soil/subsoil.

13. Disposal considerations

13.1. Waste treatment methods

Advice on disposal

Do not allow to enter into surface water or drains. Do not allow to enter into soil/subsoil. Dispose of waste according to applicable legislation.

Waste disposal number of waste from residues/unused products

080299

WASTES FROM THE MANUFACTURE, FORMULATION, SUPPLY AND USE (MFSU) OF COATINGS (PAINTS, VARNISHES AND VITREOUS ENAMELS), ADHESIVES, SEALANTS AND PRINTING INKS; wastes from MFSU of other coatings (including ceramic materials); wastes not otherwise specified

Waste disposal number of used product

080299

WASTES FROM THE MANUFACTURE, FORMULATION, SUPPLY AND USE (MFSU) OF COATINGS (PAINTS, VARNISHES AND VITREOUS ENAMELS), ADHESIVES, SEALANTS AND PRINTING INKS; wastes from MFSU of other coatings (including ceramic materials); wastes not otherwise specified

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself. Dispose of waste according to applicable legislation.



Material Safety Data Sheet

14. Transport information

Land transport (ADR/RID)

14.1. UN number:	UN 3082
14.2. UN proper shipping name:	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Epoxydharz)
14.3. Transport hazard class(es):	9
14.4. Packing group:	III
Hazard label:	9
Classification code:	M6
Special Provisions:	274 335 601
Limited quantity:	5 L
Transport category:	3
Hazard No:	90
Tunnel restriction code:	E



Other applicable information (land transport)

E1

Inland waterways transport (ADN)

14.1. UN number:	UN 3082
14.2. UN proper shipping name:	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Epoxydharz)
14.3. Transport hazard class(es):	9
14.4. Packing group:	III
Hazard label:	9
Classification code:	M6
Special Provisions:	274 335 601
Limited quantity:	5 L



Other applicable information (inland waterways transport)

E1



Material Safety Data Sheet

Marine transport (IMDG)

14.1. UN number:	UN 3082
14.2. UN proper shipping name:	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (epoxy resin)
14.3. Transport hazard class(es):	9
14.4. Packing group:	III
Hazard label:	9
Marine pollutant:	Yes
Special Provisions:	274, 335
Limited quantity:	5 L
EmS:	F-A, S-F



Other applicable information (marine transport)

E1

Air transport (ICAO-TI/IATA-DGR)

14.1. UN number:	UN 3082
14.2. UN proper shipping name:	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (epoxy resin)
14.3. Transport hazard class(es):	9
14.4. Packing group:	III
Hazard label:	9
Special Provisions:	A97 A158
Limited quantity Passenger:	30 kg G
IATA-packing instructions-Passenger:	964
IATA-max. quantity - Passenger:	450 L
IATA-packing instructions - Cargo:	964
IATA-max. quantity – Cargo:	450 L



Other applicable information (air transport)

E1

Passenger-LQ: Y964

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: yes

Danger releasing substance: Epoxy resin (number average molecular weight <= 700), reaction product:
bisphenol-A-(epichlorhydrin)

14.6. Special precautions for user

No information available.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable



Material Safety Data Sheet

15. Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulatory information

Employment restrictions: Observe restrictions to employment for juvenils according to the 'juvenile work protection guideline' (94/33/EC).

Water contaminating class (D): 2 - clearly water contaminating

15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

16. Other information

Abbreviations and acronyms

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service

LC50: Lethal concentration, 50%

LD50: Lethal dose, 50%

Relevant H and EUH statements (number and full text)

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H411 Toxic to aquatic life with long lasting effects.

H412 Harmful to aquatic life with long lasting effects.

EUH205 Contains epoxy constituents. May produce an allergic reaction.

Further Information

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)