

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>Power H-S</b>	<b>10407900</b> <b>14.11.2013</b>

Power inserts  
Fast and easy assembly  
Very high current transfer  
Lower space requirement  
Axial screw termination for assembly without special tool




Wide clamping range



Industrial machinery and plant engineering



Temperature-resistant



#### Info

Very high current transfer in a small space  
Axial screw termination for assembly without special tool

#### Application range

Mechanical engineering  
Plant engineering  
Renewable energy

#### Remark






Photographs are not to scale and do not represent detailed images of the respective products.

#### Technical Data

Article:	H-S 4+2xPE BAS
Version:	female
Contacts:	4 + PE
PU:	10
Rated voltage (V):	1000
Rated impulse voltage:	8 kV
Rated current (A):	65
Contact resistance:	< 1 mOhm
Number of contacts:	4 + PE
Termination methods:	Axial screw termination 2.5 mm <sup>2</sup> ... 10.0 mm <sup>2</sup>
Material:	PC, polycarbonate
Cycle of mechanical operation:	500
Temperature range:	-40°C ... +125°C
Degree of soiling:	3

Product Management	Document: Power H-S	1 / 2
--------------------	---------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 <b>LAPP GROUP</b>
	<b>Power H-S</b>	10407900 14.11.2013



Product Management	Document: Power H-S	2 / 2
--------------------	---------------------	-------