

Page 1/10

Safety data sheet according to 1907/2006/EC, Article 31

inting date 13.03.2019	Version number 54	Revision: 13.03.20
SECTION 1: Identification of the	substance/mixture and of the company/un	ndertaking
1.1 Product identifier		
Trade name	tesa 60022 Spray Glue EXTRA STRONG	
 Article number: 1.2 Relevant identified uses of the substance or mixture and uses advised against Application of the substance / the mixture 1.3 Manufacturer/Supplier: 	tesa 60022 (500ml) No further relevant information available. Adhesives tesa SE	Tel.: +49-40-88899-1
	Hugo-Kirchberg-Strasse 1 D-22848 Norderstedt Germany	
Informing department:	tesa SE, quality management/environment/occup Dirk.Lamm@tesa.com, Tel.: +49-40-88899-2977	
 1.4 Emergency telephone number: 	tesa SE, Hugo-Kirchberg-Str. 1, D-22848 Norder Security Center Phone +49-40-88899-0 or +49-40-88899-9111	rstedt
	Deutschland: Giftinformationszentrum-Nord (GIZ-Nord) Pharmakologisch-toxikologisches Servicezentrur Toxikologie der Universitätsmedizin Göttingen, Georg-August-Universität, Göttingen Tel: 0551/19240 (24-Stunden erreichbar) Tel: 0551/383180 (für medizinisches Fachpersor	-
	Oesterreich, Wien (Vienna): Vergiftungsinformationszentrale (Poisons Inform Allgemeines KrankenhausWaehringer Geurtel 18 Telephone: +43 1 40 400 2222 Fax: +43 1 40 400 4225 E-mail: viz@meduniwien.ac.at Web site: www.giftinfo.org	
	Schweiz, Zurich: Centre Suisse d'Information Toxicologique (Swiss Toxicological Information Centre) Freiestrasse 16, CH-8032 Zurich Telephone: +41 44 251 66 66 Emergency telephone: +41 44 251 51 51 (1 Liechtenstein) Fax: +41 44 252 88 33 E-mail: info@toxi.ch Web site: http://www.toxi.ch	45 from within Switzerland a
	UNITED KINGDOM: The UK National Poisons Emergency number is London: Emergency 24 hour telephone: +44 (0)20 7188 0 Guy's & St Thomas' Poisons Unit Medical Toxicology Information Services Mary Sheridan House, Guy's Hospital, Great Max	0100



Page 2/10

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.03.2019

Version number 54

Revision: 13.03.2019

Trade name tesa 60022 Spray Glue EXTRA STRONG

		(Contd. of page
SECTION 2: I	Hazards ident	ification
		tance or mixture egulation (EC) No 1272/2008
	_	
GHS	02 flame	
Aerosol 1	H222-H229	Extremely flammable aerosol. Pressurised container: May burst if heated.
GHS	07	
Skin Irrit. 2	H315	Causes skin irritation.
Eye Irrit. 2	H319	Causes serious eye irritation.
STOT SE 3	H336	May cause drowsiness or dizziness.
Asp. Tox. 1	H304	May be fatal if swallowed and enters airways.
Aquatic Chronic		Harmful to aquatic life with long lasting effects.
2.2 Label elem	ents	
	ording to Regul	
(EC) No 1272/2		The product is classified and labelled according to the CLP regulation.
Hazard pictogi	rams	
		GHS02 GHS07
Signal word		Danger
	nining compone	
labelling:		64742-49-0 Naphtha (petroleum), hydrotreated light (Note P) methyl acetate
		cyclohexane
		n-hexane
Hazard statem	ents	H222-H229 Extremely flammable aerosol. Pressurised container: May burst heated.
		H315 Causes skin irritation.
		H319 Causes serious eye irritation.
		H336 May cause drowsiness or dizziness.H412 Harmful to aquatic life with long lasting effects.
Precautionary	statements	P102 Keep out of reach of children.
-		P210 Keep away from heat, hot surfaces, sparks, open flames a
		other ignition sources. No smoking. P211 Do not spray on an open flame or other ignition source.
		P251 Do not pierce or burn, even after use.
		P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minute
		Remove contact lenses, if present and easy to do. Contine rinsing.
		P405 Store locked up.
		P410+P412 Protect from sunlight. Do not expose to temperature
		exceeding 50 °C/122 °F. P501 Dispose of contents/container in accordance with loca
2.3 Other haza	rds	regional/national/international regulations. The preparation contains no elualable organic halogene compounds, whic increases the AOX values
Results of PB1	Г and vPvB ass	
PBT:		Not classified
		(Contd. on page



Printing date 13.03.2019

Version number 54

Revision: 13.03.2019

(Contd. of page 2)

Page 3/10

Trade name tesa 60022 Spray Glue EXTRA STRONG

· vPvB:

Not classified

SECTION 3: Composition/information on ingredients

· 3.2 Chemical characterisation:	Mixtures
· Description:	Mixt

Mixture consisting of the following components.

Dangerous components:		
CAS: 79-20-9 EINECS: 201-185-2 Reg.nr.: 01-2119459211-47-xxxx	methyl acetate Flam. Liq. 2, H225 Eye Irrit. 2, H319; STOT SE 3, H336	<50%
CAS: 106-97-8 EINECS: 203-448-7 Reg.nr.: 01-2119474691-32-xxxx	butane, pure Flam. Gas 1, H220 Acute Tox. 3, H331 Press. Gas (Comp.), H280	<25%
CAS: 74-98-6 EINECS: 200-827-9 Reg.nr.: 01-2119486944-21-xxxx	propane liquefied Flam. Gas 1, H220 Press. Gas (Comp.), H280	<25%
EINECS: 265-151-9 Reg.nr.: 01-2119486291-36-xxxx	 64742-49-0 Naphtha (petroleum), hydrotreated light (Note P) Flam. Liq. 2, H225 Asp. Tox. 1, H304 Aquatic Chronic 2, H411 Skin Irrit. 2, H315; STOT SE 3, H336 	<25%
CAS: 141-78-6 EINECS: 205-500-4 Reg.nr.: 01-2119475103-46-XXXX	ethyl acetate ♦ Flam. Liq. 2, H225 ♦ Eye Irrit. 2, H319; STOT SE 3, H336	<2.5%
CAS: 75-28-5 EINECS: 200-857-2 Reg.nr.: 01-2119485395-27-xxxx	isobutane ♦ Flam. Gas 1, H220 Press. Gas (Comp.), H280	<2.5%
CAS: 110-82-7 EINECS: 203-806-2 Reg.nr.: 01-2119463273-41-XXXX	cyclohexane Flam. Liq. 2, H225 Asp. Tox. 1, H304 Aquatic Acute 1, H400; Aquatic Chronic 1, H410 Skin Irrit. 2, H315; STOT SE 3, H336	<2.5%
CAS: 110-54-3 EINECS: 203-777-6 Reg.nr.: 01-2119480412-44-xxxx	n-hexane Flam. Liq. 2, H225 Repr. 2, H361f; STOT RE 2, H373; Asp. Tox. 1, H304 Aquatic Chronic 2, H411	<1%

detergents / Labelling for contents not applicable · Additional information

For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

 General information 	Instantly remove any clothing soiled by the product.
 After inhalation 	In case of unconsciousness bring patient into stable side position for transport.
 After skin contact 	Instantly wash with water and soap and rinse thoroughly.
· After eye contact	Rinse opened eye for several minutes under running water. If symptoms persist, consult doctor.
· After swallowing	In case of persistent symptoms consult physician.
· 4.2 Most important symptoms and	
effects, both acute and delayed	Dazedness
	May cause drowsiness.
	(Contd. on page 4)



Printing date 13.03.2019 Version number 54 Revision: 13.03.2019 Trade name tesa 60022 Spray Glue EXTRA STRONG (Contd. of page 3) · 4.3 Indication of any immediate medical attention and special treatment needed If swallowed, gastric irrigation with added, activated carbon. **SECTION 5: Firefighting measures** · 5.1 Extinguishing media · Suitable extinguishing agents CO2, extinguishing powder or water jet. Fight larger fires with water jet or alcoholresistant foam. · 5.2 Special hazards arising from the substance or mixture Can be released in case of fire: Nitrogen oxide (NOx) Carbon monoxide (CO) Under certain fire conditions, traces of other toxic gases cannot be excluded. 5.3 Advice for firefighters · Protective equipment: Put on breathing apparatus. Do not inhale explosion gases or combustion gases. Cool endangered containers with water spray jet. · Additional information

SECTION 6: Accidental release measures

- 6.1 Personal precautions, protective equipment and emergency procedures
- · 6.2 Environmental precautions:



Wear protective equipment. Keep unprotected persons away.

Prevent product from reaching sewage system or water bodies.

Inform resposible authorities in case of spilling into water or sewage system.

-,
bose of contaminated material as waste according to item 13.
ure adequate ventilation.
Section 7 for information on safe handling
Section 8 for information on personal protection equipment.
Section 13 for information on disposal.

SECTION 7: Handling and storage

· 7.1 Precautions for safe handling

• Information about protection against explosions and fires:

Keep away from heat and direct sunlight. Ensure good ventilation/exhaustion at the workplace.

Do not spray on flames or red-hot objects.



Keep ignition sources away - Do not smoke.

Beware: Container is pressurized. Keep away from direct sun exposure and temperatures over 50°C. Do not open by force or throw into fire even after use.

- · 7.2 Conditions for safe storage, including any incompatibilities
- · Storage
- Requirements to be met by storerooms and containers:

 Information about storage in one common storage facility: Observe official regulations on storing packagings with pressurised containers. Storage location and storage conditions must comply with the rules for handling and storage of substances and preparations of the WGK 3. Any site-specific regulatory requirements must be fulfilled.

Store away from flammable substances.



Page 5/10

Safety data sheet according to 1907/2006/EC, Article 31

	according to 1907/2006/EC, Article 31	
inting date 13.03.2019	Version number 54	Revision: 13.03.2019
ade name tesa 60022 Spray Glue EX	(TRA STRONG	
		(Contd. of page 4
Further information about storage		
conditions:	Keep container tightly sealed.	
· 7.3 Specific end use(s)	No further relevant information available.	
SECTION 8: Exposure controls	personal protection	
· Additional information about desig	in	
of technical systems:	No further data; see item 7.	
8.1 Control parameters		
· Components with critical values th	at require monitoring at the workplace:	
79-20-9 methyl acetate		
WEL Short-term value: 770 mg/m ³ , 2 Long-term value: 616 mg/m ³ , 2		
106-97-8 butane, pure		
WEL Short-term value: 1810 mg/m ³ , Long-term value: 1450 mg/m ³ ,		
Carc (if more than 0.1% of but		
141-78-6 ethyl acetate	100	
WEL Short-term value: 1468 mg/m ³ , Long-term value: 734 mg/m ³ , 2		
110-82-7 cyclohexane		
WEL Short-term value: 1050 mg/m ³ , Long-term value: 350 mg/m ³ , 1		
110-54-3 n-hexane		
WEL Long-term value: 72 mg/m ³ , 20) ppm	
· Additional information:	The lists that were valid during the compilation were	e used as basis.
8.2 Exposure controls		
 Personal protective equipment 		
General protective and hygienic		
measures	The usual precautionary measures should be chemicals.	adhered to in handling the
	Keep away from foodstuffs, beverages and food.	
	Instantly remove any contaminated garments.	
	Wash hands before breaks and at the end of the w	ork.
Proothing oquinmont	Avoid contact with the eyes and skin. Not necessary if room is well-ventilated.	
Breathing equipment:	Use breathing filter A2	
	In case of short term exposure use res	spiratory protection. In case o
	intensive or longer exposure use res independent from ambient air.	piratory protection equipment
Protection of hands:		
	Solvent resistant gloves	
	Protective gloves. The glove material has to be impermeal	ble and resistant to the product
	the substance/ the preparation.	
	Selection of the glove material on co	
	times, rates of diffusion and the degrada	ation
Material of gloves	Nitrile rubber, NBR	
Penetration time of glove material	use solvent stable gloves. The exact break trough time has to be found o	ut by the manufacturer of the
Eye protection:	protective gloves and has to be observed.	



Safety glasses



Page 6/10

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.03.2019

Version number 54

Revision: 13.03.2019

(Contd. of page 5)

Trade name tesa 60022 Spray Glue EXTRA STRONG

· Body protection:

Protective work clothing.

SECTION 9: Physical and chemical properties

• 9.1 Information on basic physical and chemical properties	
General Information	
 Appearance: Form: 	Assess
Colour:	Aerosol
· Smell:	Light yellow Solvent-like
· Odour threshold:	Not determined.
· pH-value:	Not determined.
· Change in condition	
Melting point/freezing point:	Not determined
Initial boiling point and boiling range	:-44 °C
· Flash point:	-97 °C
· Inflammability (solid, gaseous)	Not applicable.
 Ignition temperature: 	245 °C
· Decomposition temperature:	Not determined.
· Self-inflammability:	Product is not selfigniting.
· Explosive properties:	Not determined.
 Critical values for explosion: 	
Lower:	1 Vol %
Upper:	16 Vol %
· Steam pressure at 20 °C:	8,300 hPa
· Density at 20 °C	0.72 g/cm ³
	Not determined
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not applicable.
• Solubility in / Miscibility with	
Water:	Not miscible or difficult to mix
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity:	
dynamic:	Not determined.
kinematic:	Not determined.
· Solvent content:	
Organic solvents:	78.4 %
Solids content:	20.0 %
 9.2 Other information 	No further relevant information available.

SECTION 10: Stability and reactivity

 10.1 Reactivity 10.2 Chemical stability 	No further relevant information available.	
Thermal decomposition / condition to be avoided: 10.3 Possibility of hazardous	s No decomposition if used according to specifications.	
reactions · 10.4 Conditions to avoid	No dangerous reactions known No further relevant information available.	



Page 7/10

Safety data sheet according to 1907/2006/EC, Article 31

rinting date 13.03.2019		Version number 54 Revision: 13.0	
ade name tesa 60022 S	pray Glue E	KTRA STRONG	
• 10.5 Incompatible mat		No further relevant information available.	(Contd. of page
 10.6 Hazardous decomposition products: 		No dangerous decomposition products known	
SECTION 11: Toxico	ological info	ormation	
 11.1 Information on to Acute toxicity 	xicological	effects Based on available data, the classification criteria are	not met.
· LD/LC50 values that a	re relevant f		
		ydrotreated light (Note P)	
	,000 mg/kg (l		
	,000 mg/kg (l	-	
Inhalative LC50/4h 5		,	
110-82-7 cyclohexane	5 ()		
-	2,705 mg/kg	(rat)	
Primary irritant effect:			
Skin corrosion/irritatio		Causes skin irritation.	
Serious eye damage/ii		Causes serious eye irritation.	
Respiratory or skin se		Based on available data, the classification criteria are	not met.
		genicity and toxicity for reproduction)	
 Germ cell mutagenicit Carcinogenicity 	y	Based on available data, the classification criteria are Based on available data, the classification criteria are	
Reproductive toxicity		Based on available data, the classification criteria are	
STOT-single exposure	•	May cause drowsiness or dizziness.	not met.
STOT-repeated expos		Based on available data, the classification criteria are	not met.
Aspiration hazard		May be fatal if swallowed and enters airways.	
SECTION 12: Ecolog	gical inform	nation	
· 12.1 Toxicity			
· Aquatic toxicity:		No further relevant information available.	
12.2 Persistence and o	degradability	No further relevant information available.	
· 12.3 Bioaccumulative		No further relevant information available.	
 12.4 Mobility in soil 		No further relevant information available.	
Ecotoxical effects:			
· Remark:		Harmful to fish	
 Additional ecological According to recipe content 			
following heavy metal			
compounds according			
guideline NO. 76/464 E		Free of heavy metals (Pb, Cd, Hg, Cr6+)	
5	-	Free of Polybrominated Biphenyls (PBBs) and Polyl (PBDEs) according to RoHS Directive.	prominated Diphenyl Ethe
· General notes:		Do not allow undiluted product or large quantities of water bodies or sewage system.	of it to reach ground wate
		Water danger class 3 (Self-assessment): extremely ha	
		Do not allow product to reach ground water, water boo in small quantities.	ales of sewage system, ev
		Danger to drinking water if even extremely small quan Harmful to aquatic organisms	tities leak into soil.
· 12.5 Results of PBT a	nd vPvB ass	· · ·	
· PBT:		Not applicable.	
· vPvB:		Not applicable.	
· 12.6 Other adverse eff	ects	No further relevant information available.	
			(Contd. on page



Page 8/10

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.03.2019

Version number 54

Revision: 13.03.2019

Trade name tesa 60022 Spray Glue EXTRA STRONG

(Contd. of page 7)

SECTION 13: Disposal considerations

- · 13.1 Waste treatment methods
- · Recommendation



Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

Must be specially treated under adherence to official regulations.

requirements. The obove mentioned classification is only one possible proposal.

· European waste catalogue (recommendation)		
16 05 04*	gases in pressure containe	ers (including halons) containing hazardous substances
HP 3	Flammable	
HP 4	Irritant - skin irritation and e	eye damage
HP 5	Specific Target Organ Toxicity (STOT)/Aspiration Toxicity	
HP 14	Ecotoxic	
· Additiona	· Additional information about the	
Europear	waste catalogue:	The assignment of a waste key number according to EC Decision 2000/532/EC in connection with EU Directive 75/442/EC has to follow specific industry

· Uncleaned packagings:

· Recommendation:

Disposal according to official regulations.

Recommended cleaning agent: ethyl acetate

SECTION 14: Transport information	
· 14.1 UN-Number · ADR, IMDG, IATA	UN1950
 · 14.2 UN proper shipping name · ADR, IMDG · IATA 	AEROSOLS AEROSOLS, flammable
· 14.3 Transport hazard class(es)	
· ADR	
· Class · Label	2 5F Gases. 2.1
· IMDG, IATA	
· Class	2.1
· Label	2.1
· 14.4 Packing group · ADR, IMDG, IATA	Void
 • 14.5 Environmental hazards: • Marine pollutant: 	No
 14.6 Special precautions for user Page: 	Warning: Gases. -
	(Contd. on page GB



Printing date 13.03.2019

Version number 54

Revision: 13.03.2019

Page 9/10

GB —

Trade name tesa 60022 Spray Glue EXTRA STRONG

	(Contd. of page 8)
· EMS Number: · Stowage Code · Segregation Code	 F-D,S-U SW1 Protected from sources of heat. SW22 For AEROSOLS with a maximum capacity of 1 litre: Category A. For AEROSOLS with a capacity above 1 litre: Category B. For WASTE AEROSOLS: Category C, Clear of living quarters. SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.
 14.7 Transport in bulk according to Annex II of Marpa and the IBC Code 	ol Not applicable.
· Transport/Additional information:	Limited quantity regulations concerning ADR and IMDG for packages up to 30 kg (gross weight). ID 8000 Consumer commoditiy for airtransport of finished goods in packages up to 30 kg possible (gross weight). DOT: ORM-D consumer commoditiy for road transport inside US
 ADR Limited quantities (LQ) Excepted quantities (EQ) Transport category Tunnel restriction code 	1L Code: E0 Not permitted as Excepted Quantity 2 D
 IMDG Limited quantities (LQ) Excepted quantities (EQ) 	1L Code: E0 Not permitted as Excepted Quantity
· UN "Model Regulation":	UN 1950 AEROSOLS, 2.1

SECTION 15: Regulatory information

 \cdot 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Directive 2012/18/EU	
 Named dangerous substances - ANNEX I 	None of the ingredients is listed.
Seveso category Qualifying quantity (tonnes) for the	P3a FLAMMABLE AEROSOLS
application of lower-tier	450.4
requirements · Qualifying quantity (tonnes) for the	150 t
application of upper-tier requirements	500 t
· REGULATION (EC) No 1907/2006 ANNEX XVII	Conditions of restriction: 3, 57
 National regulations 	
\cdot Information about limitation of use:	Employment restrictions concerning young persons must be observed.
 Decree to be applied in case of technical fault: 	Critical quantity values according to the regulations on accidents should be adhered to. (Contd. on page 10)
	(Cond. of page 10)



Printing date 13.03.2019

Version number 54


Revision: 13.03.2019

(Contd. of page 9)

Page 10/10

Trade name tesa 60022 Spray Glue EXTRA STRONG

· Technical instructions (air):



· Water hazard class:

· 15.2 Chemical safety assessment:

Water danger class 3 (Self-assessment): extremely hazardous for water. A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This data is based on our present knowledge. However, they shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

* Data compared to the previous version altered.

GB -