

Page 1 of 8 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II Revision date / version: 13.06.2017 / 0007 Replacing version dated / version: 21.08.2015 / 0006 Valid from: 13.06.2017 PDF print date: 10.03.2021 Bio Saegekettenoel

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

അ

Bio Saegekettenoel

1.2 Relevant identified uses of the substance or mixture and uses advised against Relevant identified uses of the substance or mixture:

Lubricating oil Sector of use [SU]: SU 3 - Industrial uses: Uses of substances as such or in preparations at industrial sites SU21 - Consumer uses: Private households (=general public = consumers) SU22 - Professional uses: Public domain (administration, education, entertainment, services, craftsmen) Chemical product category [PC]: PC24 - Lubricants, greases, release products Process category [PROC]: PROC10 - Roller application or brushing PROC13 - Treatment of articles by dipping and pouring Article Categories [AC]: AC99 - Not required. Environmental Release Category [ERC]: ERC 4 - Use of non-reactive processing aid at industrial site (no inclusion into or onto article) ERC 8d - Widespread use of non-reactive processing aid (no inclusion into or onto article, outdoor) Uses advised against: No information available at present.

1.3 Details of the supplier of the safety data sheet

LIQUI MOLY GmbH Jerg-Wieland-Str. 4 89081 Ulm-Lehr Tel.: (+49) 0731-1420-0 Fax: (+49) 0731-1420-88

Qualified person's e-mail address: info@chemical-check.de, k.schnurbusch@chemical-check.de Please DO NOT use for requesting Safety Data Sheets.

1.4 Emergency telephone number

Emergency information services / official advisory body:

Telephone number of the company in case of emergencies:

+49 (0) 700 / 24 112 112 (LMR)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture Classification according to Regulation (EC) 1272/2008 (CLP) The mixture is not classified as dangerous in the terms of the Regulation (EC) 1272/2008 (CLP).

2.2 Label elements
Labeling according to Regulation (EC) 1272/2008 (CLP)
Not applicable
2.3 Other hazards



Page 2 of 8 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II Revision date / version: 13.06.2017 / 0007 Replacing version dated / version: 21.08.2015 / 0006 Valid from: 13.06.2017 PDF print date: 10.03.2021 Bio Saegekettenoel

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006 (< 0,1 %). The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC)

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006 (< 0, 1 %).

SECTION 3: Composition/information on ingredients

3.1 Substances

n.a. **3.2 Mixtures**

ആ

Registration number (REACH)	
Index	
EINECS, ELINCS, NLP	
CAS	
content %	
Classification according to Regulation (EC) 1272/2008 (CLP)	

SECTION 4: First aid measures

4.1 Description of first aid measures

First-aiders should ensure they are protected!

Never pour anything into the mouth of an unconscious person!

Inhalation

Supply person with fresh air and consult doctor according to symptoms.

Skin contact

Remove polluted, soaked clothing immediately, wash thoroughly with plenty of water and soap, in case of irritation of the skin (flare), consult a doctor.

Eye contact

Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

Ingestion

Rinse the mouth thoroughly with water.

Do not induce vomiting - give copious water to drink. Consult doctor immediately.

4.2 Most important symptoms and effects, both acute and delayed

If applicable delayed symptoms and effects can be found in section 11 and the absorption route in section 4.1.

with long-term contact: Drying of the skin.

In certain cases, the symptoms of poisoning may only appear after an extended period / after several hours.

4.3 Indication of any immediate medical attention and special treatment needed

Indications for the physician: Ingestion:

Vaseline oil may be given for medical purposes.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media CO2 Dry extinguisher Water jet spray Large fire: Alcohol resistant foam Unsuitable extinguishing media High volume water jet 5.2 Special hazards arising from the substance or mixture



Page 3 of 8 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II Revision date / version: 13.06.2017 / 0007 Replacing version dated / version: 21.08.2015 / 0006 Valid from: 13.06.2017 PDF print date: 10.03.2021 Bio Saegekettenoel

In case of fire the following can develop: Oxides of carbon Toxic pyrolysis products.

5.3 Advice for firefighters

അ

In case of fire and/or explosion do not breathe fumes. Protective respirator with independent air supply. Cool container at risk with water. Dispose of contaminated extinction water according to official regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

No special measures required. Avoid contact with eyes or skin. Avoid formation of oil mist. If applicable, caution - risk of slipping.

6.2 Environmental precautions

If leakage occurs, dam up. Resolve leaks if this possible without risk.

Prevent from entering drainage system.

Prevent surface and ground-water infiltration, as well as ground penetration.

6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent, sand, diatomaceous earth, sawdust) and dispose of according to Section 13.

6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

SECTION 7: Handling and storage

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

7.1 Precautions for safe handling

7.1.1 General recommendations

Avoid formation of oil mist.

Do not heat to temperatures close to flash point. Avoid long lasting or intensive contact with skin. Eating, drinking, smoking, as well as food-storage, is prohibited in work-room. Do not carry cleaning cloths soaked in product in trouser pockets. Observe directions on label and instructions for use.

7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work. Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

7.2 Conditions for safe storage, including any incompatibilities

Not to be stored in gangways or stair wells.

Store product closed and only in original packing. Store at room temperature. Store in a dry place.

7.3 Specific end use(s)

No information available at present.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

8.2 Exposure controls 8.2.1 Appropriate engineering controls



Page 4 of 8 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II Revision date / version: 13.06.2017 / 0007 Replacing version dated / version: 21.08.2015 / 0006 Valid from: 13.06.2017 PDF print date: 10.03.2021 Bio Saegekettenoel

Ensure good ventilation. This can be achieved by local suction or general air extraction. If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn. Applies only if maximum permissible exposure values are listed here.

8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable. Wash hands before breaks and at end of work. Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection: Tight fitting protective goggles with side protection (EN 166).

Skin protection - Hand protection: Normally not necessary. With long-term contact: Chemical resistant protective gloves (EN 374). If applicable Protective Neoprene® / polychloroprene gloves (EN 374). Protective nitrile gloves (EN 374). Protective hand cream recommended.

Skin protection - Other: Protective working garments (e.g. safety shoes EN ISO 20345, long-sleeved protective working garments).

Respiratory protection: Normally not necessary.

Thermal hazards:

ആ

If applicable, these are included in the individual protective measures (eye/face protection, skin protection, respiratory protection).

Additional information on hand protection - No tests have been performed.

In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents. Selection of materials derived from glove manufacturer's indications.

Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account. Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.

In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use. The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

8.2.3 Environmental exposure controls

No information available at present.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	Green
Odour:	Characteristic
Odour threshold:	Not determined
pH-value:	Not determined
Melting point/freezing point:	Not determined
Initial boiling point and boiling range:	Not determined
Flash point:	>230 °C (ISO 2592 (Cleveland, open cup))
Evaporation rate:	Not determined
Flammability (solid, gas):	Not determined
Lower explosive limit:	Not determined
Upper explosive limit:	Not determined
Vapour pressure:	Not determined
Vapour density (air = 1):	Not determined
Density:	~0,92 g/cm3 (15°C, DIN 51757)
Bulk density:	Not determined



Page 5 of 8 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II Revision date / version: 13.06.2017 / 0007 Replacing version dated / version: 21.08.2015 / 0006 Valid from: 13.06.2017 PDF print date: 10.03.2021 Bio Saegekettenoel

Solubility(ies):

œ

Water solubility: Partition coefficient (n-octanol/water): Auto-ignition temperature: Decomposition temperature: Viscosity: Explosive properties: Oxidising properties:

9.2 Other information

Miscibility: Fat solubility / solvent: Conductivity: Surface tension: Solvents content: Not determined Insoluble, product floats. Not determined Not determined 90-110 mm2/s (40°C, DIN 51532) Not determined Not determined

Not determined Not determined Not determined Not determined Not determined

SECTION 10: Stability and reactivity

10.1 Reactivity

See also Subsection 10.2 to 10.6. The product has not been tested.

10.2 Chemical stability

See also Subsection 10.1 to 10.6. Stable with proper storage and handling.

10.3 Possibility of hazardous reactions

See also Subsection 10.1 to 10.6. No decomposition if used as intended.

10.4 Conditions to avoid

See also section 7.

10.5 Incompatible materials

See also section 7. No dangerous reactions are known. Avoid contact with strong oxidizing agents.

10.6 Hazardous decomposition products

See also Subsection 10.1 to 10.5. See also section 5.2 No decomposition when used as directed.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Possibly more information on health effects, see Section 2.1 (classification).

Bio Saegekettenoel						
Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:						n.d.a.
Acute toxicity, by dermal route:						n.d.a.
Acute toxicity, by inhalation:						n.d.a.
Skin corrosion/irritation:						n.d.a.
Serious eye damage/irritation:						n.d.a.
Respiratory or skin						n.d.a.
sensitisation:						
Germ cell mutagenicity:						n.d.a.
Carcinogenicity:						n.d.a.
Reproductive toxicity:						n.d.a.
Specific target organ toxicity -						n.d.a.
single exposure (STOT-SE):						
Specific target organ toxicity -						n.d.a.
repeated exposure (STOT-RE):						
Aspiration hazard:						n.d.a.
Symptoms:						n.d.a.



Classification according to calculation procedure.

Page 6 of 8 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II Revision date / version: 13.06.2017 / 0007 Replacing version dated / version: 21.08.2015 / 0006 Valid from: 13.06.2017 PDF print date: 10.03.2021 Bio Saegekettenoel

Other information:

œ

SECTION 12: Ecological information

Possibly more information on environmental effects, see Section 2.1 (classification).

Bio Saegekettenoel							
Toxicity / effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
12.1. Toxicity to fish:							n.d.a.
12.1. Toxicity to daphnia:							n.d.a.
12.1. Toxicity to algae:							n.d.a.
12.2. Persistence and						OECD 301 B	Readily
degradability:						(Ready	biodegradable
						Biodegradability -	Mechanical
						Co2 Evolution	precipitation
						Test)	possible.
12.3. Bioaccumulative							n.d.a.
potential:							
12.4. Mobility in soil:							n.d.a.
12.5. Results of PBT							n.d.a.
and vPvB assessment							
12.6. Other adverse							n.d.a.
effects:							

SECTION 13: Disposal considerations

13.1 Waste treatment methods

For the substance / mixture / residual amounts

Soaked polluted cloths, paper or other organic materials represent a fire hazard and should be controlled, collected and disposed of. EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product.

Owing to the user's specific conditions for use and disposal, other waste codes may be

allocated under certain circumstances. (2014/955/EU)

13 02 07 readily biodegradable engine, gear and lubricating oils

Recommendation:

Sewage disposal shall be discouraged.

Pay attention to local and national official regulations.

Implement substance recycling.

E.g. suitable incineration plant.

For contaminated packing material

Pay attention to local and national official regulations.

Empty container completely.

Uncontaminated packaging can be recycled.

Dispose of packaging that cannot be cleaned in the same manner as the substance.

SECTION 14: Transport information

General statements	n.a.
Transport by road/by rail (ADR/RID)	11.a.
14.2. UN proper shipping name:	
14.3. Transport hazard class(es):	n.a.
14.4. Packing group:	n.a.
Classification code:	n.a.
LQ:	n.a.
14.5. Environmental hazards:	Not applicable



Page 7 of 8 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II Revision date / version: 13.06.2017 / 0007 Replacing version dated / version: 21.08.2015 / 0006 Valid from: 13.06.2017 PDF print date: 10.03.2021 Bio Saegekettenoel

Tunnel restriction code:

അ

Transport by sea (IMDG-code)

14.2. UN proper shipping name:	
14.3. Transport hazard class(es):	n.a.
14.4. Packing group:	n.a.
Marine Pollutant:	n.a
14.5. Environmental hazards:	Not applicable
Transport by air (IATA)	
14.2. UN proper shipping name:	
14.3. Transport hazard class(es):	n.a.
14.4. Packing group:	n.a.
14.5. Environmental hazards:	Not applicable

14.6. Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Non-dangerous material according to Transport Regulations.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Observe restrictions:

General hygiene measures for the handling of chemicals are applicable.

Directive 2010/75/EU (VOC):

15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

SECTION 16: Other information

0 %

Revised sections:

15

Classification and processes used to derive the classification of the mixture in accordance with the ordinance (EG) 1272/2008 (CLP):

Not applicable

The following phrases represent the posted Hazard Class and Risk Category Code (GHS/CLP) of the product and the constituents (specified in Section 2 and 3).

Any abbreviations and acronyms used in this document:

according, according to acc., acc. to ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road) AOX Adsorbable organic halogen compounds approx. approximately Art., Art. no. Article number ASTM ASTM International (American Society for Testing and Materials) Acute Toxicity Estimate ATE BAM Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany) BAuA Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany) BSEF The International Bromine Council body weight bw CAS **Chemical Abstracts Service** Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances CI P and mixtures)



-(6)
Page 8 of 8
0
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 13.06.2017 / 0007
Replacing version dated / version: 21.08.2015 / 0006 Valid from: 13.06.2017
PDF print date: 10.03.2021
Bio Saegekettenoel
CMR carcinogenic, mutagenic, reproductive toxic
DMEL Derived Minimum Effect Level
DNEL Derived No Effect Level
dw dry weight
e.g. for example (abbreviation of Latin 'exempli gratia'), for instance
EC European Community
ECHA European Chemicals Agency
EEC European Economic Community
EINECS European Inventory of Existing Commercial Chemical Substances
ELINCS European List of Notified Chemical Substances
EN European Norms
EPA United States Environmental Protection Agency (United States of America)
etc. et cetera
EU European Union
EVAL Ethylene-vinyl alcohol copolymer
Fax. Fax number
gen. general
GHS Globally Harmonized System of Classification and Labelling of Chemicals
GWP Global warming potential
IARC International Agency for Research on Cancer
IATA International Air Transport Association
IBC (Code) International Bulk Chemical (Code)
IMDG-code International Maritime Code for Dangerous Goods
incl. including, inclusive
IUCLID International Uniform Chemical Information Database
IUPAC International Union for Pure Applied Chemistry
LC50 Lethal Concentration to 50 % of a test population
LD50 Lethal Dose to 50% of a test population (Median Lethal Dose)
LQ Limited Quantities
MARPOL International Convention for the Prevention of Marine Pollution from Ships
n.a. not applicable
n.av. not available
n.c. not checked
n.d.a. no data available
OECD Organisation for Economic Co-operation and Development
org. organic
PBT persistent, bioaccumulative and toxic
PE Polyethylene
PNEC Predicted No Effect Concentration
ppm parts per million
PVC Polyvinylchloride
REACHRegistration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration,
Evaluation, Authorisation and Restriction of Chemicals)
REACH-IT List-No. 9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List
Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.
RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International
Carriage of Dangerous Goods by Rail)
SVHC Substances of Very High Concern
Tel. Telephone
UN RTDG United Nations Recommendations on the Transport of Dangerous Goods
VOC Volatile organic compounds
vPvB very persistent and very bioaccumulative
wwt wet weight
The statements made here should describe the product with regard to the necessary safety precautions - they are
not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge.
No responsibility.
These statements were made by: Chamical Chack CmbH, Chamical Chack Platz 1-7, D-32830 Stainhaim, Tal : : : 40, 5233, 04, 17, 0, Eav:
Chemical Check GmbH, Chemical Check Platz 1-7, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax:
40 5223 04 17 00

+49 5233 94 17 90

C by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.