

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Batterie-Pol-Fett

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture:

Lubricating grease

Uses advised against:

No information available at present.

1.3 Details of the supplier of the safety data sheet

LIQUI MOLY GmbH
Jerg-Wieland-Str. 4
89081 Ulm-Lehr
Tel.: (+49) 0731-1420-0
Fax: (+49) 0731-1420-88

Qualified person's e-mail address: info@chemical-check.de, k.schnurbusch@chemical-check.de Please DO NOT use for requesting Safety Data Sheets.

1.4 Emergency telephone number

Emergency information services / official advisory body:

Telephone number of the company in case of emergencies:

+49 (0) 700 / 24 112 112 (LMR)
+1 872 5888271 (LMR)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) 1272/2008 (CLP)

The mixture is not classified as dangerous in the terms of the Regulation (EC) 1272/2008 (CLP).

2.2 Label elements

Labeling according to Regulation (EC) 1272/2008 (CLP)

Not applicable

2.3 Other hazards

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006 (< 0,1 %).

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006 (< 0,1 %).

The mixture does not contain any substance with endocrine disrupting properties (< 0,1 %).

SECTION 3: Composition/information on ingredients

3.1 Substances

Page 2 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 18.08.2022 / 0016
 Replacing version dated / version: 21.07.2022 / 0015
 Valid from: 18.08.2022
 PDF print date: 07.09.2022
 Batterie-Pol-Fett

n.a.

3.2 Mixtures

---	---
Registration number (REACH)	---
Index	---
EINECS, ELINCS, NLP, REACH-IT List-No.	---
CAS	---
content %	---
Classification according to Regulation (EC) 1272/2008 (CLP), M-factors	---

SECTION 4: First aid measures

4.1 Description of first aid measures

First-aiders should ensure they are protected!
 Never pour anything into the mouth of an unconscious person!

Inhalation

Remove person from danger area.
 Supply person with fresh air and consult doctor according to symptoms.

Skin contact

Wipe off residual product carefully with a soft, dry cloth.
 Remove polluted, soaked clothing immediately, wash thoroughly with plenty of water and soap, in case of irritation of the skin (flare), consult a doctor.

Eye contact

Remove contact lenses.
 Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

Ingestion

Rinse the mouth thoroughly with water.
 Do not induce vomiting. Consult doctor immediately.

4.2 Most important symptoms and effects, both acute and delayed

If applicable delayed symptoms and effects can be found in section 11 and the absorption route in section 4.1.
 In certain cases, the symptoms of poisoning may only appear after an extended period / after several hours.

The following may occur:
 Drying of the skin.

Dermatitis (skin inflammation)

4.3 Indication of any immediate medical attention and special treatment needed

Symptomatic treatment.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

CO2
 Foam
 Dry extinguisher

Unsuitable extinguishing media

Water

5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop:

Oxides of carbon
 Oxides of sulphur
 Oxides of nitrogen
 Toxic gases

5.3 Advice for firefighters

For personal protective equipment see Section 8.
 In case of fire and/or explosion do not breathe fumes.
 Protective respirator with independent air supply.
 According to size of fire

Page 3 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 18.08.2022 / 0016
Replacing version dated / version: 21.07.2022 / 0015
Valid from: 18.08.2022
PDF print date: 07.09.2022
Batterie-Pol-Fett

Full protection, if necessary.
Cool container at risk with water.
Dispose of contaminated extinction water according to official regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

6.1.1 For non-emergency personnel

In case of spillage or accidental release, wear personal protective equipment as specified in section 8 to prevent contamination.
Ensure sufficient ventilation, remove sources of ignition.
Avoid dust formation with solid or powder products.
Leave the danger zone if possible, use existing emergency plans if necessary.
Avoid contact with eyes or skin.
If applicable, caution - risk of slipping.

6.1.2 For emergency responders

See section 8 for suitable protective equipment and material specifications.

6.2 Environmental precautions

If leakage occurs, dam up.
Resolve leaks if this possible without risk.
Prevent surface and ground-water infiltration, as well as ground penetration.
Prevent from entering drainage system.
If accidental entry into drainage system occurs, inform responsible authorities.

6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent) and dispose of according to Section 13.
Or:

Pick up mechanically and dispose of according to Section 13.

6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

SECTION 7: Handling and storage

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

7.1 Precautions for safe handling

7.1.1 General recommendations

Avoid contact with eyes.
Avoid long lasting or intensive contact with skin.
Do not carry cleaning cloths soaked in product in trouser pockets.
Eating, drinking, smoking, as well as food-storage, is prohibited in work-room.
Observe directions on label and instructions for use.

7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.
Wash hands before breaks and at end of work.
Keep away from food, drink and animal feedingstuffs.
Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

7.2 Conditions for safe storage, including any incompatibilities

Not to be stored in gangways or stair wells.
Store product closed and only in original packing.
Store in a well ventilated place.
Store in a dry place.
Do not store over 45°C.

7.3 Specific end use(s)

No information available at present.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

GB

Page 4 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 18.08.2022 / 0016
 Replacing version dated / version: 21.07.2022 / 0015
 Valid from: 18.08.2022
 PDF print date: 07.09.2022
 Batterie-Pol-Fett

WEL-TWA: 5 mg/m3 (Mineral oil, excluding metal working fluids, ACGIH)	WEL-STEL: ---	---
Monitoring procedures: - Draeger - Oil Mist 1/a (67 33 031)		
BMGV: ---	Other information: ---	

GB WEL-TWA = Workplace Exposure Limit - Long-term exposure limit (8-hour TWA (= time weighted average) reference period) EH40. AGW = "Arbeitsplatzgrenzwert" (workplace limit value, Germany).
 (8) = Inhalable fraction (Directive 2017/164/EU, Directive 2004/37/CE). (9) = Respirable fraction (Directive 2017/164/EU, Directive 2004/37/CE). (11) = Inhalable fraction (Directive 2004/37/CE). (12) = Inhalable fraction. Respirable fraction in those Member States that implement, on the date of the entry into force of this Directive, a biomonitoring system with a biological limit value not exceeding 0,002 mg Cd/g creatinine in urine (Directive 2004/37/CE). | WEL-STEL = Workplace Exposure Limit - Short-term exposure limit (15-minute reference period).
 (8) = Inhalable fraction (2017/164/EU, 2017/2398/EU). (9) = Respirable fraction (2017/164/EU, 2017/2398/EU). (10) = Short-term exposure limit value in relation to a reference period of 1 minute (2017/164/EU). | BMGV = Biological monitoring guidance value EH40. BGW = "Biologischer Grenzwert" (biological limit value, Germany) | Other information: Sen = Capable of causing occupational asthma. Sk = Can be absorbed through skin. Carc = Capable of causing cancer and/or heritable genetic damage.
 ** = The exposure limit for this substance is repealed through the TRGS 900 (Germany) of January 2006 with the goal of revision.
 (13) = The substance can cause sensitisation of the skin and of the respiratory tract (Directive 2004/37/CE), (14) = The substance can cause sensitisation of the skin (Directive 2004/37/CE).

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Ensure good ventilation. This can be achieved by local suction or general air extraction.
 If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn.
 Applies only if maximum permissible exposure values are listed here.
 Suitable assessment methods for reviewing the effectiveness of protection measures adopted include metrological and non-metrological investigative techniques.
 These are specified by e.g. EN 14042.
 EN 14042 "Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents".

8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.
 Wash hands before breaks and at end of work.
 Keep away from food, drink and animal feedingstuffs.
 Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:
 With danger of contact with eyes.
 Tight fitting protective goggles with side protection (EN 166).

Skin protection - Hand protection:
 Protective nitrile gloves (EN ISO 374).
 Minimum layer thickness in mm:
 0,4
 Permeation time (penetration time) in minutes:
 240
 Protective hand cream recommended.
 The breakthrough times determined in accordance with EN 16523-1 were not obtained under practical conditions.
 The recommended maximum wearing time is 50% of breakthrough time.

Skin protection - Other:
 Protective working garments (e.g. safety shoes EN ISO 20345, long-sleeved protective working garments).

Respiratory protection:
 Normally not necessary.

Thermal hazards:
 Not applicable

Additional information on hand protection - No tests have been performed.
 In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents.
 Selection of materials derived from glove manufacturer's indications.

Page 5 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 18.08.2022 / 0016
 Replacing version dated / version: 21.07.2022 / 0015
 Valid from: 18.08.2022
 PDF print date: 07.09.2022
 Batterie-Pol-Fett

Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account. Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.

In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use. The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

8.2.3 Environmental exposure controls

No information available at present.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state:	Paste, liquid.
Colour:	Pink
Odour:	Not determined
Melting point/freezing point:	There is no information available on this parameter.
Boiling point or initial boiling point and boiling range:	There is no information available on this parameter.
Flammability:	There is no information available on this parameter.
Lower explosion limit:	There is no information available on this parameter.
Upper explosion limit:	There is no information available on this parameter.
Flash point:	>150 °C
Auto-ignition temperature:	There is no information available on this parameter.
Decomposition temperature:	There is no information available on this parameter.
pH:	Mixture is non-soluble (in water).
Kinematic viscosity:	>20,5 mm ² /s (40°C, There is no information available on this parameter.)
Solubility:	Insoluble
Partition coefficient n-octanol/water (log value):	Does not apply to mixtures.
Vapour pressure:	There is no information available on this parameter.
Density and/or relative density:	<1000 kg/m ³ (25°C)
Relative vapour density:	There is no information available on this parameter.
Particle characteristics:	Does not apply to liquids.

9.2 Other information

Explosives:	Product is not explosive.
Oxidizing solids:	No

SECTION 10: Stability and reactivity

10.1 Reactivity

The product has not been tested.

10.2 Chemical stability

Stable with proper storage and handling.

10.3 Possibility of hazardous reactions

No dangerous reactions are known.

10.4 Conditions to avoid

See also section 7.

Strong heat

10.5 Incompatible materials

See also section 7.

Avoid contact with strong oxidizing agents.

10.6 Hazardous decomposition products

See also section 5.2

No decomposition when used as directed.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Possibly more information on health effects, see Section 2.1 (classification).

Page 6 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 18.08.2022 / 0016
 Replacing version dated / version: 21.07.2022 / 0015
 Valid from: 18.08.2022
 PDF print date: 07.09.2022
 Batterie-Pol-Fett

Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:	ATE	4340,10	mg/kg			calculated value
Acute toxicity, by dermal route:	ATE	4340,10	mg/kg			calculated value
Acute toxicity, by inhalation:						n.d.a.
Skin corrosion/irritation:						n.d.a.
Serious eye damage/irritation:						n.d.a.
Respiratory or skin sensitisation:						n.d.a.
Germ cell mutagenicity:						n.d.a.
Carcinogenicity:						n.d.a.
Reproductive toxicity:						n.d.a.
Specific target organ toxicity - single exposure (STOT-SE):						n.d.a.
Specific target organ toxicity - repeated exposure (STOT-RE):						n.d.a.
Aspiration hazard:						n.d.a.
Symptoms:						n.d.a.

11.2. Information on other hazards

Batterie-Pol-Fett						
Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes
Endocrine disrupting properties:						Does not apply to mixtures.
Other information:						No other relevant information available on adverse effects on health.

SECTION 12: Ecological information

Possibly more information on environmental effects, see Section 2.1 (classification).

Batterie-Pol-Fett							
Toxicity / effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
12.1. Toxicity to fish:							n.d.a.
12.1. Toxicity to daphnia:							n.d.a.
12.1. Toxicity to algae:							n.d.a.
12.2. Persistence and degradability:							Isolate as much as possible with an oil separator.
12.3. Bioaccumulative potential:							Concentration in organisms possible.
12.4. Mobility in soil:							n.d.a.
12.5. Results of PBT and vPvB assessment							n.d.a.
12.6. Endocrine disrupting properties:							Does not apply to mixtures.
12.7. Other adverse effects:							No information available on other adverse effects on the environment.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

For the substance / mixture / residual amounts

Soaked polluted cloths, paper or other organic materials represent a fire hazard and should be controlled, collected and disposed of.

Page 7 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 18.08.2022 / 0016
 Replacing version dated / version: 21.07.2022 / 0015
 Valid from: 18.08.2022
 PDF print date: 07.09.2022
 Batterie-Pol-Fett

EC disposal code no.:
 The waste codes are recommendations based on the scheduled use of this product.
 Owing to the user's specific conditions for use and disposal, other waste codes may be
 allocated under certain circumstances. (2014/955/EU)
 13 08 99 wastes not otherwise specified

Recommendation:
 Sewage disposal shall be discouraged.
 Pay attention to local and national official regulations.
 E.g. dispose at suitable refuse site.
 E.g. suitable incineration plant.

For contaminated packing material

Pay attention to local and national official regulations.
 Empty container completely.
 Uncontaminated packaging can be recycled.
 Dispose of packaging that cannot be cleaned in the same manner as the substance.

SECTION 14: Transport information

General statements

14.1. UN number or ID number: n.a.

Transport by road/by rail (ADR/RID)

14.2. UN proper shipping name:
 14.3. Transport hazard class(es): n.a.
 14.4. Packing group: n.a.
 Classification code: n.a.
 LQ: n.a.
 14.5. Environmental hazards: Not applicable
 Tunnel restriction code:

Transport by sea (IMDG-code)

14.2. UN proper shipping name:
 14.3. Transport hazard class(es): n.a.
 14.4. Packing group: n.a.
 Marine Pollutant: n.a.
 14.5. Environmental hazards: Not applicable

Transport by air (IATA)

14.2. UN proper shipping name:
 14.3. Transport hazard class(es): n.a.
 14.4. Packing group: n.a.
 14.5. Environmental hazards: Not applicable

14.6. Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

14.7. Maritime transport in bulk according to IMO instruments

Non-dangerous material according to Transport Regulations.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Observe restrictions:
 General hygiene measures for the handling of chemicals are applicable.

Directive 2010/75/EU (VOC): 0 %

15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

SECTION 16: Other information

Revised sections: 7, 9, 13, 15

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 18.08.2022 / 0016
 Replacing version dated / version: 21.07.2022 / 0015
 Valid from: 18.08.2022
 PDF print date: 07.09.2022
 Batterie-Pol-Fett

Classification and processes used to derive the classification of the mixture in accordance with the ordinance (EG) 1272/2008 (CLP):

Not applicable

The following phrases represent the posted Hazard Class and Risk Category Code (GHS/CLP) of the product and the constituents (specified in Section 2 and 3).

Key literature references and sources for data:

Regulation (EC) No 1907/2006 (REACH) and Regulation (EC) No 1272/2008 (CLP) as amended.
 Guidelines for the preparation of safety data sheets as amended (ECHA).
 Guidelines on labelling and packaging according to the Regulation (EG) Nr. 1272/2008 (CLP) as amended (ECHA).
 Safety data sheets for the constituent substances.
 ECHA Homepage - Information about chemicals.
 GESTIS Substance Database (Germany).
 German Environment Agency "Rigoletto" information site on substances that are hazardous to water (Germany).
 EU Occupation Exposure Limits Directives 91/322/EEC, 2000/39/EC, 2006/15/EC, 2009/161/EU, (EU) 2017/164, (EU) 2019/1831, each as amended.
 National Lists of Occupational Exposure Limits for each country as amended.
 Regulations on the transport of hazardous goods by road, rail, sea and air (ADR, RID, IMDG, IATA) as amended.

Any abbreviations and acronyms used in this document:

acc., acc. to according, according to
 ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)
 AOX Adsorbable organic halogen compounds
 approx. approximately
 Art., Art. no. Article number
 ASTM ASTM International (American Society for Testing and Materials)
 ATE Acute Toxicity Estimate
 BAM Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany)
 BAuA Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)
 BCF Bioconcentration factor
 BSEF The International Bromine Council
 bw body weight
 CAS Chemical Abstracts Service
 CLP Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures)
 CMR carcinogenic, mutagenic, reproductive toxic
 DMEL Derived Minimum Effect Level
 DNEL Derived No Effect Level
 DOC Dissolved organic carbon
 dw dry weight
 e.g. for example (abbreviation of Latin 'exempli gratia'), for instance
 EbCx, EyCx, EbLx (x = 10, 50) Effect Concentration/Level of x % on reduction of the biomass (algae, plants)
 EC European Community
 ECHA European Chemicals Agency
 ECx, ELx (x = 0, 3, 5, 10, 20, 50, 80, 100) Effect Concentration/Level for x % effect
 EEC European Economic Community
 EINECS European Inventory of Existing Commercial Chemical Substances
 ELINCS European List of Notified Chemical Substances
 EN European Norms
 EPA United States Environmental Protection Agency (United States of America)
 ErCx, EµCx, ErLx (x = 10, 50) Effect Concentration/Level of x % on inhibition of the growth rate (algae, plants)
 etc. et cetera
 EU European Union
 EVAL Ethylene-vinyl alcohol copolymer
 Fax. Fax number
 gen. general

Page 9 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 18.08.2022 / 0016
 Replacing version dated / version: 21.07.2022 / 0015
 Valid from: 18.08.2022
 PDF print date: 07.09.2022
 Batterie-Pol-Fett

GHS Globally Harmonized System of Classification and Labelling of Chemicals
 GWP Global warming potential
 Koc Adsorption coefficient of organic carbon in the soil
 Kow octanol-water partition coefficient
 IARC International Agency for Research on Cancer
 IATA International Air Transport Association
 IBC (Code) International Bulk Chemical (Code)
 IMDG-code International Maritime Code for Dangerous Goods
 incl. including, inclusive
 IUCLID International Uniform Chemical Information Database
 IUPAC International Union for Pure Applied Chemistry
 LC50 Lethal Concentration to 50 % of a test population
 LD50 Lethal Dose to 50% of a test population (Median Lethal Dose)
 Log Koc Logarithm of adsorption coefficient of organic carbon in the soil
 Log Kow, Log Pow Logarithm of octanol-water partition coefficient
 LQ Limited Quantities
 MARPOL International Convention for the Prevention of Marine Pollution from Ships
 n.a. not applicable
 n.av. not available
 n.c. not checked
 n.d.a. no data available
 NIOSH National Institute for Occupational Safety and Health (USA)
 NLP No-longer-Polymer
 NOEC, NOEL No Observed Effect Concentration/Level
 OECD Organisation for Economic Co-operation and Development
 org. organic
 OSHA Occupational Safety and Health Administration (USA)
 PBT persistent, bioaccumulative and toxic
 PE Polyethylene
 PNEC Predicted No Effect Concentration
 ppm parts per million
 PVC Polyvinylchloride
 REACH Registration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)
 REACH-IT List-No. 9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.
 RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)
 SVHC Substances of Very High Concern
 Tel. Telephone
 TOC Total organic carbon
 UN RTDG United Nations Recommendations ON the Transport of Dangerous Goods
 VOC Volatile organic compounds
 vPvB very persistent and very bioaccumulative
 wwt wet weight

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge.

No responsibility.

These statements were made by:

**Chemical Check GmbH, Chemical Check Platz 1-7, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax:
 +49 5233 94 17 90**

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.