

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.03.2019

Version number 109

Revision: 13.03.2019

* SECTION 1: Identification of the substance/mixture and of the company/undertaking

• 1.1 Product identifier

• Trade name **tesa Alleskleber / All purpose glue**

• Article number: tesa 57007, 57012, 57013, 57015

• 1.2 Relevant identified uses of the substance or mixture and uses advised against

No further relevant information available.

• Application of the substance / the mixture

Adhesives

• 1.3 Manufacturer/Supplier:

tesa SE
Hugo-Kirchberg-Strasse 1
D-22848 Norderstedt
Germany

Tel.: +49-40-88899-101

• Informing department:

tesa SE, quality management/environment/occupational safety, Dr. Dirk Lamm
Dirk.Lamm@tesa.com, Tel.: +49-40-88899-2977

• 1.4 Emergency telephone number:

tesa SE, Hugo-Kirchberg-Str. 1, D-22848 Norderstedt
Security Center Phone +49-40-88899-0
or +49-40-88899-9111

* SECTION 2: Hazards identification

• 2.1 Classification of the substance or mixture

• Classification according to Regulation (EC) No 1272/2008



GHS02 flame

Flam. Liq. 2 H225 Highly flammable liquid and vapour.



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

• 2.2 Label elements

• Labelling according to Regulation (EC) No 1272/2008

• Hazard pictograms

The product is classified and labelled according to the CLP regulation.



GHS02



GHS07

• Signal word

Danger

• Hazard-determining components of labelling:

acetone

• Hazard statements

H225 Highly flammable liquid and vapour.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

• Precautionary statements

P101

If medical advice is needed, have product container or label at hand.

P102

Keep out of reach of children.

P103

Read label before use.

P210

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P241

Use explosion-proof [electrical/ventilating/lighting] equipment.

(Contd. on page 2)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.03.2019

Version number 109

Revision: 13.03.2019

Trade name tesa Alleskleber / All purpose glue

(Contd. of page 1)

P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P405 Store locked up.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

2.3 Other hazards

The preparation contains no eluable organic halogene compounds, which increases the AOX values

Results of PBT and vPvB assessment

PBT: Not classified




vPvB: Not classified

* SECTION 3: Composition/information on ingredients

3.2 Chemical characterisation: Mixtures

Description: Solution of Polyvinylacetate in:
Solution of Polyvinylacetate

Dangerous components:

CAS: 67-64-1 EINECS: 200-662-2 Reg.nr.: 01-2119471330-49-XXXX	acetone	 Flam. Liq. 2, H225  Eye Irrit. 2, H319; STOT SE 3, H336	<50%
CAS: 64-17-5 EINECS: 200-578-6 Reg.nr.: 01-2119457610-43-XXXX	ethanol	 Flam. Liq. 2, H225	<25%

SVHC

Free of any SVHC substances or < 0.1 %

Regulation (EC) No 648/2004 on detergents / Labelling for contents

not applicable

Additional information

For the wording of the listed hazard phrases refer to section 16.

* SECTION 4: First aid measures

4.1 Description of first aid measures

General information

Instantly remove any clothing soiled by the product.

After inhalation

Supply fresh air; consult physician in case of symptoms.

After skin contact

Instantly wash with water and soap and rinse thoroughly.

After eye contact

Rinse opened eye for several minutes under running water. If symptoms persist, consult doctor.

After swallowing

In case of persistent symptoms consult physician.

4.2 Most important symptoms and effects, both acute and delayed

Dazedness

May cause drowsiness.

Danger

Condition may deteriorate with alcohol consumption.

4.3 Indication of any immediate medical attention and special treatment needed

No further relevant information available.

* SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing agents

CO2, extinguishing powder or water jet. Fight larger fires with water jet or alcohol-resistant foam.

5.2 Special hazards arising from the substance or mixture

Can be released in case of fire:

Nitrogen oxide (NOx)

Carbon monoxide (CO)

Under certain fire conditions, traces of other toxic gases cannot be excluded.

(Contd. on page 3)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.03.2019

Version number 109

Revision: 13.03.2019

Trade name tesa Alleskleber / All purpose glue

(Contd. of page 2)

· 5.3 Advice for firefighters

· Protective equipment:


Put on breathing apparatus.
Do not inhale explosion gases or combustion gases.

* SECTION 6: Accidental release measures

· 6.1 Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation
Wear protective equipment. Keep unprotected persons away.

· 6.2 Environmental precautions:



Prevent material from reaching sewage system, holes and cellars.

Dilute with much water.

· 6.3 Methods and material for containment and cleaning up:

Apply absorbing material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose of contaminated material as waste according to item 13.
Ensure adequate ventilation.

· 6.4 Reference to other sections

See Section 7 for information on safe handling
See Section 8 for information on personal protection equipment.
See Section 13 for information on disposal.

* SECTION 7: Handling and storage

· 7.1 Precautions for safe handling

Ensure that suitable extractors are available on processing machines
Ensure good ventilation/exhaustion at the workplace.
Prevent formation of aerosols.

· Information about protection against explosions and fires:



Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.
Handle only outside or in explosion protected rooms.
Fumes can combine with air to form an explosive mixture.

· 7.2 Conditions for safe storage, including any incompatibilities

· Storage

· Requirements to be met by storerooms and containers:

Store in cool location.

· Information about storage in one common storage facility:

void
void

· Further information about storage conditions:

Keep container tightly sealed.
Store in cool, dry conditions in well sealed containers.
Store only outside or in explosion proof rooms.
Storing flammable liquids the National regulations have to be fulfilled!
3 (flammable liquids)
No further relevant information available.

· Storage class

· 7.3 Specific end use(s)

* SECTION 8: Exposure controls/personal protection

· Additional information about design of technical systems:

No further data; see item 7.

(Contd. on page 4)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.03.2019

Version number 109

Revision: 13.03.2019

Trade name tesa Alleskleber / All purpose glue

(Contd. of page 3)

· 8.1 Control parameters

· Components with critical values that require monitoring at the workplace:

67-64-1 acetone	
WEL	Short-term value: 3620 mg/m ³ , 1500 ppm Long-term value: 1210 mg/m ³ , 500 ppm
64-17-5 ethanol	
WEL	Long-term value: 1920 mg/m ³ , 1000 ppm

· Additional information:

The lists that were valid during the compilation were used as basis.

· 8.2 Exposure controls

· Personal protective equipment

· General protective and hygienic measures

The usual precautionary measures should be adhered to in handling the chemicals.

Keep away from foodstuffs, beverages and food.

Instantly remove any contaminated garments.

Wash hands before breaks and at the end of the work.

Avoid contact with the eyes.

· Breathing equipment:



In case of short term exposure use respiratory protection. In case of intensive or longer exposure use respiratory protection equipment independent from ambient air.

· Protection of hands:



Not required.

Protective gloves.

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· Material of gloves

· Penetration time of glove material

use solvent stable gloves.

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· Eye protection:



Safety glasses

Safety glasses recommended during refilling.

· Body protection:

Protective work clothing.

* SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Appearance:

Form:

Liquid

Colour:

Transparent

· Smell:

Acetone-like

· Odour threshold:

Not determined.

· pH-value:

Not determined.

· Change in condition

Melting point/freezing point:

Not determined

Initial boiling point and boiling range: 55.8-56.6 °C

· Flash point:

-19 °C

(Contd. on page 5)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.03.2019

Version number 109

Revision: 13.03.2019

Trade name tesa Alleskleber / All purpose glue

(Contd. of page 4)

· Inflammability (solid, gaseous)	Not applicable.
· Ignition temperature:	425 °C
· Decomposition temperature:	Not determined.
· Self-inflammability:	Product is not selfigniting.
· Explosive properties:	Product is not explosive. However, formation of explosive air/steam mixtures is possible.
· Critical values for explosion: Lower: Upper:	2.6 Vol % 15 Vol %
· Steam pressure at 20 °C:	247 hPa
· Density at 20 °C	0.80556 g/cm ³
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not determined.
· Solubility in / Miscibility with Water:	Soluble
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity: dynamic at 20 °C: kinematic:	6,000 mPas Not determined.
· Solvent content: Organic solvents: Water:	62.5 % 5.0 %
· Solids content:	32.5 %
· 9.2 Other information	No further relevant information available.

* SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known

* SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Causes serious eye irritation.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.

(Contd. on page 6)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.03.2019

Version number 109

Revision: 13.03.2019

Trade name tesa Alleskleber / All purpose glue

(Contd. of page 5)

- **STOT-single exposure** May cause drowsiness or dizziness.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

* SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **According to recipe contains the following heavy metals and compounds according to EC guideline NO. 76/464 EC:** Free of heavy metals (Pb, Cd, Hg, Cr6+)
Free of Polybrominated Biphenyls (PBBs) and Polybrominated Diphenyl Ethers (PBDEs) according to RoHS Directive.
- **General notes:** Do not allow undiluted product or large quantities of it to reach ground water, water bodies or sewage system.
Water hazard class 1 (Self-assessment): slightly hazardous for water.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

* SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**



Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

Must be specially treated under adherence to official regulations.

· **European waste catalogue (recommendation)**

08 04 09*	waste adhesives and sealants containing organic solvents or other hazardous substances
HP 3	Flammable
HP 4	Irritant - skin irritation and eye damage
HP 5	Specific Target Organ Toxicity (STOT)/Aspiration Toxicity

· **Additional information about the European waste catalogue:**

The assignment of a waste key number according to EC Decision 2000/532/EC in connection with EU Directive 75/442/EC has to follow specific industry requirements. The above mentioned classification is only one possible proposal.

- **Uncleaned packagings:**
- **Recommendation:** Disposal according to official regulations.
empty bottle totally
- **Recommended cleaning agent:** Water, if necessary with cleaning agent.
Acetone
iso-Propanole
Ethanol

* SECTION 14: Transport information

- **14.1 UN-Number**
- **ADR, IMDG, IATA** UN1133

(Contd. on page 7)

GB

Safety data sheet

according to 1907/2006/EC, Article 31



Printing date 13.03.2019

Version number 109

Revision: 13.03.2019

Trade name tesa Alleskleber / All purpose glue

(Contd. of page 6)

· 14.2 UN proper shipping name · ADR · IMDG, IATA		ADHESIVES, (vapour pressure at 50°C not more than 110 kPa) ADHESIVES
· 14.3 Transport hazard class(es) · ADR 		3 (F1) Flammable liquids. 3
· IMDG, IATA 		3 Flammable liquids. 3
· 14.4 Packing group · ADR, IMDG, IATA		II
· 14.5 Environmental hazards: · Marine pollutant:		No
· 14.6 Special precautions for user · Page: · EMS Number: · Stowage Category		Warning: Flammable liquids. 33 F-E,S-D B
· 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code		Not applicable.
· Transport/Additional information: · ADR · Limited quantities (LQ) · Excepted quantities (EQ)		5L Code: E2 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 500 ml
· Transport category · Tunnel restriction code		2 D/E
· IMDG · Limited quantities (LQ) · Excepted quantities (EQ)		5L Code: E2 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 500 ml
· UN "Model Regulation":		UN 1133 ADHESIVES (VAPOUR PRESSURE AT 50°C NOT MORE THAN 110 KPA), 3, II

* SECTION 15: Regulatory information

- 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
 - Directive 2012/18/EU
 - Named dangerous substances - ANNEX I
- None of the ingredients is listed.

(Contd. on page 8)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 13.03.2019

Version number 109

Revision: 13.03.2019

Trade name tesa Alleskleber / All purpose glue

(Contd. of page 7)

- **Seveso category** P5c FLAMMABLE LIQUIDS
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 5,000 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 50,000 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3
- **National regulations**
- **Additional classification according to Decree on Hazardous Materials, Annex III:** Carcinogenic hazardous material group III (dangerous)
- **Information about limitation of use:** Employment restrictions concerning young persons must be observed.
- **Decree to be applied in case of technical fault:** Critical quantity values according to the regulations on accidents should be adhered to.
- **Technical instructions (air):**

Class	Share in %
III	62.7
- **Water hazard class:** Water hazard class 1 (Self-assessment): slightly hazardous for water.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

* SECTION 16: Other information

This data is based on our present knowledge. However, they shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases** H225 Highly flammable liquid and vapour.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.
- **Department issuing data specification sheet:** tesa SE, Quality Management/Environment/Safety
- **Contact:** tesa SE: Dr. D. Lamm, Phone: +49-40-88899-2977, Email: dirk.lamm@tesa.com
tesa SE: Dr. A. Koeth, Phone: +49-40-88899-3938, Email: anja.koeth@tesa.com
- **Abbreviations and acronyms:** ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
PBT: Persistent, Bioaccumulative and Toxic
SVHC: Substances of Very High Concern
vPvB: very Persistent and very Bioaccumulative
Flam. Liq. 2: Flammable liquids – Category 2
Eye Irrit. 2: Serious eye damage/eye irritation – Category 2
STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
- *** Data compared to the previous version altered.**