



DATA SHEET	01550XX
DIN extension cable KEL Y XX x 1,5	valid from : 01.12.2008

Application

The extension cables KEL Version Y XX x 1,5 mm² are multi-cored PVC insulated cables which transmit the thermoelectric voltage of Fe/CuNi thermocouples. They are for flexible use and fixed installation in dry and damp rooms with medium mechanical load. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

Design

Conductor	1,5 mm ² (48 x 0,20 mm)
Conductor material	LX alloying, accuracy class 2 according DIN 43722 Positive conductor: Fe (iron) Negative conductor: CuNi (cupronickel)
Core insulation	PVC compound
Core identification	Positive conductor: red Negative conductor: blue
Core layering	Cores twisted together
Outer sheath	PVC compound, colour: blue

Electrical properties

Limiting deviation class 2 ± 140 µV (± 2,5 °C) / m measuring point temperature +500 °C

Mechanical and thermal properties

Temperature range	fixed installed: -40 °C upto + 80 °C occasional flexing: -5 °C up to +70 °C
Minimum bending radius	occasional flexing: 12 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Originator: Frank Hörtnagl / PD-KL Approved: Werner Körner / TE	Document: DB0155001EN	page 1 of 1
--	----------------------------	-------------